



PRODUCT-DETAILS

TYB232M

CABLE TIE 18LB 8IN NAT NYL WORK BOX



General Information

Extended Product Type	TYB232M
Product ID	7TCG009020R0054
EAN	5414363435440
Catalog Description	CABLE TIE 18LB 8IN NAT NYL WORK BOX
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 202mm (8.0 Inches), Width of 2.3mm (0.09 Inches), Thickness of 1.10mm (0.04 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), Workbench Box Packaging

Ordering

EAN	5414363435440
UPC	786209892744
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Width	0.1 in 2.54 mm
Product Net Depth / Length	8 in 203.2 mm

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	4 in 102 mm
Package Level 1 Height	8 in 203 mm
Package Level 1 Depth / Length	4 in 102 mm
Package Level 2 Units	8000 piece
Package Level 2 Width	10 in 254 mm
Package Level 2 Height	9 in 229 mm
Package Level 2 Depth / Length	20 in 508 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Bundle Diameter	0.06 to 2.01 in 1.5 to 51 mm
Color	Natural
Effective Date	20080226
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Product Name	OTHER PLASTICS ITEMS
Product Type	High Performance
Special Functions	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Standards	UL E49405
Tensile Strength	18 lb 80 N
Thickness	0.04 in 1 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000570
Declaration of Conformity - CE	9AKK107492A9841
Instructions and Manuals	TYB232M
REACH Declaration	9AKK107992A8781
RoHS Information	9AKK107991A8366

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703

WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

