

PRODUCT-DETAILS

YLD-12-225-BC

CABLE TIE 12X225MM SS LADR BLK COAT



General Information

Extended Product Type	YLD-12-225-BC
Product ID	7TCG009450R0211
EAN	5414363124986
Catalog Description	CABLE TIE 12X225MM SS LADR BLK COAT
Long Description	Ladder Type 316 Stainless Steel Cable Tie, Black Polyester Coating for Temperatures up to 150 Degrees Celsius (304 F), Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 225mm (8.86 Inches), Width of 12.0mm (0.472 Inches), Thickness of 0.46mm (0.018 Inches), Tensile Strength Rating of 890 Newtons (200.1 pounds)

Ordering

EAN	5414363124986
UPC	786210936024
Country of Origin	India (IN)
Customs Tariff Number	7326908688
Selling Unit of Measure	each

Dimensions

Product Net Width	0.472 in 12 mm
Product Net Depth / Length	8.86 in 225 mm

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	11 in 279 mm
Package Level 1 Height	0.6 in 15 mm
Package Level 1 Depth / Length	5.9 in 150 mm
Package Level 2 Units	2500 piece
Package Level 2 Width	5.9 in 150 mm
Package Level 2 Height	12.2 in 310 mm
Package Level 2 Depth / Length	11 in 279 mm

Additional Information

Bundle Diameter	0.787 to 2.36 in 20 to 60 mm
Color	Black
Effective Date	20040806
Lock Type	Ladder Type
Material	316 Stainless Steel
Product Name	STAINLESS STEEL CABLE TIE
Product Type	Stainless Steel
RoHS Date	9AKK108466A7851
Tensile Strength	200 lb 890 N
Thickness	0.018 in 0.46 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	YLD-12-225-BC
Declaration of Conformity - CE	9AKK107492A9838
Instructions and Manuals	YLD-12-225-BC
REACH Declaration	9AKK108466A7850
RoHS Information	9AKK108466A7851

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5043 >> Ladder Ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

