

PRODUCT-DETAILS

YLD-7-610-BC

CABLE TIE 7X610MM SS LADDR BLK COAT



General Information

Extended Product Type	YLD-7-610-BC
Product ID	7TCG009450R0225
EAN	5414363124917
Catalog Description	CABLE TIE 7X610MM SS LADDR BLK COAT
Long Description	Ladder Type 316 Stainless Steel Cable Tie, Black Polyester Coating for Temperatures up to 150 Degrees Celsius (304 F), Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 610mm (24.015 Inches), Width of 7.0mm (0.275 Inches), Thickness of 0.41mm (0.016 Inches), Tensile Strength Rating of 445 Newtons (100 Pounds)

Ordering

EAN	5414363124917
UPC	786210935959
Country of Origin	India (IN)
Customs Tariff Number	7326908688
Selling Unit of Measure	each

Dimensions

Product Net Width	0.275 in 7 mm
Product Net Depth / Length	24.015 in 610 mm

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	16.9 in 429 mm
Package Level 1 Height	0.4 in 10 mm
Package Level 1 Depth / Length	9.1 in 231 mm
Package Level 2 Units	1500 piece
Package Level 2 Width	7.9 in 201 mm
Package Level 2 Height	13.8 in 351 mm
Package Level 2 Depth / Length	15.7 in 399 mm

Additional Information

Bundle Diameter	0.787 to 7.28 in 20 to 185 mm
Color	Black
Effective Date	20040806
Lock Type	Ladder Type
Material	316 Stainless Steel
Product Name	STAINLESS STEEL CABLE TIE
Product Type	Stainless Steel
RoHS Date	9AKK108466A7851
Tensile Strength	100 lb 445 N
Thickness	0.016 in 0.41 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	YLD-7-610-BC
Declaration of Conformity - CE	9AKK107492A9838
Instructions and Manuals	YLD-7-610-BC
REACH Declaration	9AKK108466A7850
RoHS Information	9AKK108466A7851

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5043 >> Ladder Ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

