

PRODUCT-DETAILS

# YLS-7.9-1400A

## CABLE TIE 250LB 55IN 304SS BALL-LCK



### General Information

|                       |                                                                                                                                                                                                                                                                                                                                                                                              |
|-----------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Extended Product Type | YLS-7.9-1400A                                                                                                                                                                                                                                                                                                                                                                                |
| Product ID            | 7TCG009420R0116                                                                                                                                                                                                                                                                                                                                                                              |
| EAN                   | 5414363072782                                                                                                                                                                                                                                                                                                                                                                                |
| Catalog Description   | CABLE TIE 250LB 55IN 304SS BALL-LCK                                                                                                                                                                                                                                                                                                                                                          |
| Long Description      | Ball-Lock 304 Stainless Steel Cable Tie, Uncoated, for Temperatures up to 300 Degrees Celsius (572 F) for Indoor and Outdoor Applications, Suitable for High Temperature Environments, UL/EN/CSA62275 Type 2S Rated for AH-1 Plenum, Length of 1400mm (55.12 Inches), Width of 7.9mm (0.311 Inches), Thickness of 0.26mm (0.01 Inches), Tensile Strength Rating of 1110 Newtons (250 pounds) |

### Ordering

|                         |               |
|-------------------------|---------------|
| E-Number (Finland)      | 1381431       |
| EAN                     | 5414363072782 |
| UPC                     | 786210748948  |
| Country of Origin       | India (IN)    |
| Customs Tariff Number   | 7326908688    |
| Selling Unit of Measure | each          |

### Dimensions

|                            |                     |
|----------------------------|---------------------|
| Product Net Width          | 0.311 in<br>7.9 mm  |
| Product Net Depth / Length | 55.12 in<br>1400 mm |

## Container Information

|                                |                   |
|--------------------------------|-------------------|
| Package Level 1 Units          | 100 piece         |
| Package Level 1 Width          | 9.1 in<br>231 mm  |
| Package Level 1 Height         | 0.6 in<br>15 mm   |
| Package Level 1 Depth / Length | 16.9 in<br>429 mm |
| Package Level 2 Units          | 500 piece         |
| Package Level 2 Width          | 5.9 in<br>150 mm  |
| Package Level 2 Height         | 9.4 in<br>239 mm  |
| Package Level 2 Depth / Length | 22 in<br>559 mm   |
| Package Level 3 Units          | 1000 piece        |
| Package Level 3 Width          | 13 in<br>330 mm   |
| Package Level 3 Height         | 10.8 in<br>274 mm |
| Package Level 3 Depth / Length | 22.8 in<br>579 mm |

## Additional Information

|                   |                                                                                                                                    |
|-------------------|------------------------------------------------------------------------------------------------------------------------------------|
| Application       | For Temperatures up to 300 Degrees Celsius (572 F) for Indoor and Outdoor Applications, Suitable for High Temperature Environments |
| Brand / Label     | Ty-Rap                                                                                                                             |
| Color             | Metallic                                                                                                                           |
| Effective Date    | 20010412                                                                                                                           |
| Lock Type         | Ball-Lock                                                                                                                          |
| Material          | 304 Stainless Steel                                                                                                                |
| Product Name      | STAINLESS STEEL CABLE TIE                                                                                                          |
| Product Type      | Stainless Steel                                                                                                                    |
| RoHS Date         | 9AKK108466A7851                                                                                                                    |
| Special Functions | Uncoated                                                                                                                           |
| Tensile Strength  | 250 lb<br>1110 N                                                                                                                   |
| Thickness         | 0.01 in<br>0.25 mm                                                                                                                 |

## Certificates and Declarations (Document Number)

|                                   |                 |
|-----------------------------------|-----------------|
| Data Sheet, Technical Information | YLS-7.9-1400A   |
| Instructions and Manuals          | YLS-7.9-1400A   |
| REACH Declaration                 | 9AKK108466A7850 |
| RoHS Information                  | 9AKK108466A7851 |

## Classifications

|        |                      |
|--------|----------------------|
| ETIM 6 | EC000046 - Cable tie |
| ETIM 7 | EC000046 - Cable tie |
| ETIM 8 | EC000046 - Cable tie |
| UNSPSC | 39121703             |

|                                    |                              |
|------------------------------------|------------------------------|
| WEEE Category                      | Product Not in WEEE Scope    |
| IDEA Granular Category Code (IGCC) | 5046 >> Stainless Steel Ties |

**Categories**

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

