

Socket Set

2526MR

Metal case size (mm) :
244 x 118 x 37 (0.038 cuft)



2526MR

2526SR

1/4"



2526SR

26
PC.

KT NO.	Contents		Kg 1.30 1 / 18	
2526MR	2335M	4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 13	2779-55G	2221-02 2221-04
	2235M	4, 5, 5.5, 6, 7, 8, 9, 10, 11, 13		
2526SR	2335S	5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 15/32, 1/2	2792	2813
	2235S	5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2		

2031MR

Metal case size (mm) :
280 x 130 x 41 (0.053 cuft)

KT NO.	Contents		Kg 1.60 1 / 15	
2031MR	2330M	4, 4.5, 5, 6, 7, 8, 9, 10, 11, 12, 13	2779-55G	2221-03 2221-06
	2335M	4, 4.5, 5, 6, 7, 8, 9, 10, 11, 12, 13		
2531MR	2335M	4, 4.5, 5, 6, 7, 8, 9, 10, 11, 12, 13	2179DF	2571-45
	2335M	4, 4.5, 5, 6, 7, 8, 9, 10, 11, 12, 13		

2531MR

1/4"



31
PC.

2030CR

Metal case size (mm) :
244 x 118 x 37 (0.038 cuft)



30
PC.

2530CR

1/4"

KT NO.	Contents		Kg 1.30 1 / 18	
2030CR	2330M	4, 4.5, 5, 6, 7, 8, 9, 10, 11, 12	2769-55F	2792
	2330S	5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2		
2530CR	2335M	4, 4.5, 5, 6, 7, 8, 9, 10, 11, 12	2571-45	2452-05F
	2335S	5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2		

2539MR

1/4"

Metal case size (mm) :
280 x 130 x 41 (0.053 cuft)



39
PC.

Contents		Kg 1.61 1 / 15	
2335M	4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13	2779-55G	2179DF
2375M	E4, E5, E6, E7, E8		
2033	T8, T9, T10, T15, T20, T25, T27, T30, T40	2571-45	2221-02 2221-04
2035	H3, H4, H5, H6, H7, H8, H10		
2779-55G		2571-45	2792
2179DF			



HAND SOCKET & ACCESSORIES