

## Accessory

KT No. &amp; D1

2453

1/4"

- Flexible handle
- Action degree -180°
- New pattern design added in firm and powerful elements
- New forge technologies I-Beam shank offers 15% lightweight
- DIN 3122



2452DK

| KT NO.   | Overall length<br>inch | mm  |    |          |
|----------|------------------------|-----|----|----------|
| 2453-05F | 5                      | 130 | 71 | 15 / 270 |
| 2452DK   | renewal kits           |     |    |          |

- Material - chrome vanadium alloy steel
- Finishing - polished, chrome plated & black phosphate sunk

2571

1/4"

- Sliding T-handle
- DIN 3122



| KT NO.  | Overall length<br>inch | mm  |    |          |
|---------|------------------------|-----|----|----------|
| 2571-45 | 4-1/2                  | 115 | 44 | 12 / 192 |



KT No. &amp; D1

2141

2142

1/4"

- Bit holder
- DIN 3122



2141



2142

| KT NO. | Size<br>inch | Overall length<br>mm |      |          |
|--------|--------------|----------------------|------|----------|
| 2141   | 1/4          | 25                   | 14.0 | 20 / 320 |
| 2142   | 1/4          | 25                   | 15   | 20 / 320 |

## Socket Rail Set

2509MR

1/4"

- Socket rail 150mmL

9  
PC.

| Contents |                              |      |    |
|----------|------------------------------|------|----|
| 2335M    | 4, 5, 6, 7, 8, 9, 10, 11, 13 | 0.17 | 40 |
| 8720609  |                              |      |    |

## Socket Rail Set

2509SR

1/4"

- Socket rail 150mmL

9  
PC.

| Contents |                                                    |      |    |
|----------|----------------------------------------------------|------|----|
| 2335S    | 5/32, 3/16, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2 | 0.17 | 40 |
| 8720609  |                                                    |      |    |

2513MR

1/4"

- Socket rail 240 mmL

13  
PC.

| Contents |                                                |      |        |
|----------|------------------------------------------------|------|--------|
| 2335M    | 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14 | 0.23 | 6 / 60 |
| 8721114  |                                                |      |        |

2513MRD1

1/4"

- Socket rail 508 mmL

13  
PC.

| Contents  |                                                |      |    |
|-----------|------------------------------------------------|------|----|
| 2335M     | 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14 | 0.34 | 50 |
| 8720813D1 |                                                |      |    |

2311MR

1/4"

- Socket rail 240 mmL

13  
PC.

| Contents |                                                |      |        |
|----------|------------------------------------------------|------|--------|
| 2235M    | 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14 | 0.46 | 6 / 60 |
| 8721114  |                                                |      |        |

2127PR

1/4"

- Socket rail 130mmL
- For hex head screw
- H : 37mm

7  
PC.

| Contents |                             |      |    |
|----------|-----------------------------|------|----|
| 2035     | H3, H4, H5, H6, H7, H8, H10 | 0.15 | 50 |
| 8720507  |                             |      |    |