

# Wheel Nut Impact Socket Set

## 4405MXL 1/2"

- Thin wall impact socket set with plastic sleeve
- Durable outer sleeve protects polished wheels and lug nuts

Contents

1.20 kg / 1 / 20

|                                                                                   |                                                                                   |          |       |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|----------|-------|
|  |  | 495517MX | 17 mm |
|  |  | 495519MX | 19 mm |
|  |  | 495521MX | 21 mm |




3 PC.

Blow case size (mm) :  
206 x 147 x 50 (0.053 cuft)

## Insert Adapter


### 34505102R

| KT NO.    | mm     | mm      | L1 mm | L mm | kg   | 1 / 20   |
|-----------|--------|---------|-------|------|------|----------|
| 34505102R | 9 x 12 | 14 x 18 | 20.5  | 45.5 | 82.2 | 12 / 144 |



### 34505201R

| KT NO.    | mm      | mm     | L1 mm | L mm | kg    | 1 / 20   |
|-----------|---------|--------|-------|------|-------|----------|
| 34505201R | 14 x 18 | 9 x 12 | 33.5  | 49.5 | 131.8 | 12 / 144 |




## Hook Wrench Head & Set

### 345042M

- Square drive size: 14 x 18

| KT NO.    | Size mm | Capacity mm | Maximum Torque N·m | Lw* mm | L mm | kg     | 1 / 20  |
|-----------|---------|-------------|--------------------|--------|------|--------|---------|
| 34504236M | 36      | 28-36       | 354                | 77     | 121  | 248.20 | 12 / 72 |
| 34504245M | 45      | 40-45       | 377                | 77     | 129  | 274.00 | 12 / 72 |
| 34504255M | 55      | 50-55       | 398                | 77     | 129  | 263.20 | 12 / 72 |
| 34504262M | 62      | 58-62       | 421                | 77     | 134  | 278.20 | 12 / 72 |
| 34504275M | 75      | 68-75       | 444                | 77     | 139  | 294.60 | 12 / 72 |
| 34504290M | 90      | 80-90       | 465                | 77     | 142  | 288.80 | 12 / 72 |



### 3452407MR

- Suitable for tightening round nuts with radial notches
- Applied with interchangeable torque wrench
- Widely used in automobile, machine tool building and petroleum industries

Contents

2.48 kg / 1 / 6

|                                                                                     |           |                        |
|-------------------------------------------------------------------------------------|-----------|------------------------|
|  | 34505102R | 9 x 12(F) → 14 x 18(M) |
|  | 345042M   | 36, 45, 55, 62, 75, 90 |



7 PC.

