

Socket Set

9063MR

9563MR

Metal case size (mm) :
476 x 282 x 57 (0.27 cuft)

9063MR01

9563MR01

1/4"+3/8"+1/2"



9063MR/9563MR



9063MR01/9563MR01

62
PC.


KT NO.	Contents			Kg 7.4	1/2
9063MR	4330MR	3330M	4768-10F	2335M	4, 4.5, 5, 6, 7, 8, 9, 10, 11, 12
	3330M		3769-08F	3023	T20, T25, T27, T30, T40
9563MR	4335MR	4330MR / 4335MR 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 27, 30, 32	363521	3235M	H4, H5, H6, H8, H10
	3335M			12, 14, 17, 19	
9063MR01	4330MR	3330M / 3335M 8, 9, 10, 11, 12, 13, 14, 15, 17, 19	4755-10G	2571-45	2221-04
	3330M		3779-08G	3571-08	3221-06
9563MR01	4335MR	3330M / 3335M 8, 9, 10, 11, 12, 13, 14, 15, 17, 19	363521	4572-12	4251-06R
	3335M				
				3792	4791R
					3812

9033CR

1/4"+3/8"+1/2"

Metal case size (mm) :
450 x 370 x 56 (0.329 cuft)

Contents	Kg 12.3	1/2
2335M	4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13	
2335S	5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2	
2235M	4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13	
2235S	5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2	
3330M	8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22	
4330MR	8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 25, 26, 27, 28, 30, 32	
4330SR	3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1, 1-1/8, 1-3/16, 1-1/4	
2015MX	H3, H4, H5, H6, H8, H10	
2015SX	1/8, 3/16, 7/32, 1/4, 5/16, 3/8	
2011X	PH1, PH2, PH3, PH4	
1115-03	H1.5, H2, H2.5	



135
PC.

Contents			
463516RC	463021RC	2179DF	2452-05F
3769-08F	4768-10F	2571-45	4572-10
2221-02	3221-03	4251-05R	3812
2221-04	3221-06	4251-10R	3792
			4791R
2561	3840	4840	

cross bar. 4-1/2"L 3/8" drive spin disc. 1/2" drive spin disc.