

Socket Set

9063MR

9563MR

Metal case size (mm) :
476 x 282 x 57 (0.27 cuft)

9063MR01

9563MR01

1/4"+3/8"+1/2"



9063MR/9563MR



9063MR01/9563MR01

62
PC.


KT NO.	Contents			Kg 7.4	1/2
9063MR	4330MR		363021	4768-10F	2335M 4, 4.5, 5, 6, 7, 8, 9, 10, 11, 12
	3330M			3769-08F	
9563MR	4335MR	4330MR / 4335MR 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 27, 30, 32	363521	3235M 12, 14, 17, 19	3023 T20, T25, T27, T30, T40
	3335M				
9063MR01	4330MR	3330M / 3335M 8, 9, 10, 11, 12, 13, 14, 15, 17, 19	363021	4755-10G	3025 H4, H5, H6, H8, H10
	3330M			3779-08G	
9563MR01	4335MR		363521	3235M 10, 13, 17, 19	2571-45 2221-04
	3335M				
				3571-08 3221-06	
				4572-12 4251-06R	
				3792 4791R 3812	

9033CR

1/4"+3/8"+1/2"

Metal case size (mm) :
450 x 370 x 56 (0.329 cuft)

Contents	Kg 12.3	1/2
2335M 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13		
2335S 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2		
2235M 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13		
2235S 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2		
3330M 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22		
4330MR 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 25, 26, 27, 28, 30, 32		
4330SR 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1, 1-1/8, 1-3/16, 1-1/4		
2015MX H3, H4, H5, H6, H8, H10		
2015SX 1/8, 3/16, 7/32, 1/4, 5/16, 3/8		
2011X PH1, PH2, PH3, PH4		
1115-03 H1.5, H2, H2.5		



135
PC.

Contents			
463516RC	463021RC	2179DF	2452-05F
3769-08F	4768-10F	2571-45	4572-10
2221-02	3221-03	4251-05R	3812
2221-04	3221-06	4251-10R	3792
			4791R
2561	3840	4840	

cross bar. 4-1/2"L 3/8" drive spin disc. 1/2" drive spin disc.