



Qoltec Uninterruptible Power Supply | Monolith | 2000VA | 1200W | LCD | USB

Product code: 53771

The Qoltec Line Interactive UPS is a modern and economical device that ensures stable operation of the computer even in the event of a power cut.

It's perfect for anyone who wants to have control over the stable operation of their devices regardless of fluctuations in the power supply.

DISCOVER SAFE ENERGY



Each of us has more than once had to deal with voltage drops at home or at work. Sometimes their only result is the need to restart the computer. But how many times, as a result of such an event, have you lost important data not saved on the disk or encountered a device crash? If you are not familiar with the above situations, we have a solution for you, thanks to which the problems of power outages or voltage drops will not concern you. Uninterruptible power supply UPS from Qoltec, is a solution that provides a constant supply of energy necessary for stable operation of your computer.

FUNCTIONAL LCD DISPLAY



The built-in LCD display ensures you can freely manage the operation of the device. You get status and parameter information in real time, making your work with the power supply easy, fast and reliable.

EFFICIENT AND STABLE OPERATION



The UPS is equipped with a maintenance-free battery, guaranteeing you stable operation during an emergency power supply to your computer. During this time you will save important data on the disk or finish the next level of your game. The process of charging the battery to 90% capacity, is 6 hours.

A SOLUTION WORTH YOUR ATTENTION



Our solution additionally offers:

- automatic voltage regulation (AVR) - it is not only a stable power supply and less battery consumption, but most importantly it protects your device from too high/low voltage,
- cold start - you are able to turn on, for example, a computer by plugging into the UPS itself. This allows you to quickly, for example, copy important files to a USB flash drive at any time,
- overload and short circuit protection,
- USB port - thanks to the power supply management software, you monitor the power supply in real time and adjust it to your needs,

CONFIDENCE BACKED BY WARRANTY

Do you care about the high quality of the product you buy? Our solutions will meet your expectations. Each Line Interactive UPS we offer comes with a 24-month warranty valid from the date of purchase.

TECHNICAL DATA

Producer	Qoltec
Power	1200W/2000 VA
UPS type	Line Interactive
Type of load device	PC, terminal, small security devices
Wave form	Simulated sine wave
Transfer time	2 - 6 ms
Input voltage	140 ~300V
Range voltage	Input voltage: 140 Vac ~ 290 Vac (50 Hz ~ 5 Hz); Output voltage: - battery mode: 220 Vac ~ 230 Vac ~ 5% (50 Hz ~ 60 Hz ~ 1 Hz); - wired mode: 220 Vac ~ 10% (50 Hz ~ 60 Hz ~ 1 Hz)
Built-in battery	Yes
Capacity	9Ah
Battery voltage	2 x 12V
Number of batteries	2
EAN code	5901878537719