

VDE SCREWDRIVERS

and / or

► VDE Screwdrivers

BERNSTEIN VDE screwdrivers are under the control of the VDE test centre. Each screwdriver in this series is individually tested in accordance with VDE guidelines DIN IEC 60900 / EN 60900, IEC 900. The test guarantees the highest level of safety for all work up to 1000 V.w

Blade: hardened over the entire length, burnished with protective coating
Handle: impact-resistant, two-colour multi-component insulation, with anti-slip protection and practical suspension hole

SLOT



CROSS-RECESS



SOCKET WRENCH



The following types are available, specifications in mm:


Art.-No.	Symbol	Size / drive	Blade length	Blade width	Blade thickness	Blade diameter	Handle length	Total length	Weight in g
14-651 VDE		Slot	75	2.5	0.4	–	100 x 21	175	26
14-652 VDE		Slot	100	3.5	0.6	–	100 x 21	200	34
14-653 VDE		Slot	100	4	0.8	–	100 x 21	200	37
14-654 VDE		Slot	125	5.5	1	–	107 x 27	232	75
14-656 VDE		Slot	150	6.5	1.2	–	114 x 32	264	112
14-658 VDE		Slot	175	8	1.2	–	121 x 35	296	175
14-681 VDE		PH0	60	–	–	3	100 x 21	160	27
14-682 VDE		PH1	80	–	–	4.5	107 x 27	187	57
14-683 VDE		PH2	100	–	–	6	114 x 32	214	92
14-684 VDE		PH3	150	–	–	8	121 x 35	271	166
14-685 VDE		PH/S1	80	–	–	4.5	107 x 27	187	57
14-686 VDE		PH/S2	100	–	–	6	114 x 32	214	92
14-692 VDE		PZ1	80	–	–	4.5	107 x 27	187	57
14-693 VDE		PZ2	100	–	–	6	114 x 32	214	92
14-694 VDE		PZ3	150	–	–	8	121 x 35	271	166
14-695 VDE		PZ/S1	80	–	–	4.5	107 x 27	187	57
14-696 VDE		PZ/S2	100	–	–	6	114 x 32	214	92
16-298 VDE		3	125	–	–	–	100 x 21	225	40
16-299 VDE		4	125	–	–	–	100 x 21	225	45
16-301 VDE		5	125	–	–	–	100 x 21	225	55
16-302 VDE		5.5	125	–	–	–	107 x 27	232	85

► 14-650 VDE

VDE screwdriver set 7 pcs

Weight: 450 g

Art.-No.	Content
14-651 VDE	VDE screwdriver slot blade 2.5 x 75 mm
14-652 VDE	VDE screwdriver slot blade 3.5 x 100 mm
14-654 VDE	VDE screwdriver slot blade 5.5 x 125 mm
14-656 VDE	VDE screwdriver slot blade 6.5 x 150 mm
14-681 VDE	VDE screwdriver cross-recess PH0 Ø 3.0 mm
14-682 VDE	VDE screwdriver cross-recess PH1 Ø 4.5 mm
4-343 VDE	VDE voltage tester slot blade 3.0 x 0.7 x 60 mm



14-650 VDE