

RULES

- Stainless steel for corrosion protection
- Permanent indented markings for wear resistance
- Fine graduations for accurate measurements



Steel rules -
Metric/imperial

Item Number			
T3530 06	150mm 6"	18mm	6
T3530 12	300mm 12"	25mm	6

- High quality construction with brass hinges & end caps for durability
- Four fold design for compact storage
- Permanent indented markings for wear resistance



Wooden rule -
Metric/imperial

Item Number		
T3510	1m 3ft	6

- Anodised aluminium construction with a strong plastic handle - lightweight, easy clean
- Metric graduations
- Ideal for cutting, measuring and marking out



Straight edge/rule

Item Number		
T3531 100	1000mm 40"	1

SPIRIT LEVELS

- Powder coated, box section aluminium - strong, light & durable
- Shockproof, unbreakable vials, guaranteed leakproof for three years
- Luminous horizontal vial for low light conditions
- Precision manufactured, accurate to +/- 0.5mm per metre
- Metric measurement graduations for convenience
- 16" (400m) & 24" (600mm) feature 1 vertical & 1 horizontal vial
- 32" (800mm) and above feature 2 vertical & 1 horizontal vials



Aluminium box levels

Item Number		i	
T3494 16	400mm 16"	2 vial with rule	1
T3494 24	600mm 24"	2 vial with rule	1
T3494 32	800mm 32"	3 vial with rule	1
T3494 40	1000mm 40"	3 vial with rule	1
T3494 48	1200mm 48"	3 vial	1
T3494 70	1800mm 70"	3 vial	1

- Tough ABS plastic body for damage protection
- V-groove base for pipework
- Magnetic base for steelwork
- Patented detachable mini level with magnetic base, ideal for setting patress boxes
- Also features string slots for use as line level
- 1 vertical & 1 horizontal vial



Pocket level

Item Number		
T3482	210mm 8 1/4"	5

CHALK, LINES & ACCESSORIES

- Die cast aluminium construction - strong & lightweight
- Fold away winding handle for convenient storage
- Self chalking line with end attachment hook for ease of use
- Supplied with 60g of blue chalk



Chalk line reel & chalk -
Heavy duty

Item Number		
T3520A	30m 100ft	6

- Tough plastic construction - strong & lightweight
- Fold away winding handle for convenient storage
- Self chalking line with end attachment hook for ease of use
- Supplied with 60g of blue chalk



Chalk line reel & chalk

Item Number		
T3522	30m 100ft	6

- Strong & absorbent cotton for effective retention of marking chalk



Chalk line - Cotton

Item Number		
T3517	18m 60ft	12

- Braided nylon construction - extra strong & durable



Chalk line - Nylon

Item Number		
T3519	18m 60ft	12

- High density chalk for clear marking results
- Plastic refill container with re-sealable dispenser cap



Chalk powders

Item Number		i	
T3521B 100	100g 4oz	blue	6
T3521R 100	100g 4oz	red	6

- Forged steel nickel plated for strength & corrosion resistance
- Suitable for use in wet & dry mortar



Line pins

Item Number		i	
T3490	170mm 6 1/2"	set of 2	10

- Conical, fully polished bob complete with screwed brass cord fitting



Plumb bob

Item Number		
T3492 11	300g 11oz	3