


DIFFUSERS KLOSZE ABDECKUNG DIFFUSEURS

A

diffuser A slide
klosz A wsuwany
Abdeckung A einschiebbar
diffuseur A coulissant

SLIM8 AC2/Z → 32 UP-TILE10 A → 162
SMART10 AC2/Z → 34 BACK10 A/UX → 176
SMART-IN10 AC2/Z → 88 UP-MINI10 A → 182
OMNI10 AC2 → 136 SKIRT10 AC2/Q9 → 186



material / materiał / Material / matériel:


PC	PP	PP
transparent transparentny transparent transparent	frosted szron satinert givré	opal mleczny opal opaque
1000 mm 89000616	89000639	89000638
2000 mm 89000716	89000739	89000738
3000 mm -	89000839	-

A1

NEW

diffuser A1 slide
klosz A1 wsuwany
Abdeckung A1 einschiebbar
diffuseur A1 coulissant

GROOVE10.v2 A1C/U → 94
CORNER10.v2 A1C/U1 → 128
GLOW12 UP A1C → 140
GLOW12 DOWN A1C → 142




material / materiał / Material / matériel:

PC	PP	PP
transparent transparentny transparent transparent	frosted szron satinert givré	opal mleczny opal opaque
1000 mm J6000816	J6000839	J6000838
2000 mm J6000916	J6000939	J6000938
3000 mm -	J6001039	-

A9

diffuser A9 slide
klosz A9 wsuwany
Abdeckung A9 einschiebbar
diffuseur A9 coulissant

VARIO30-01 ACDE-9/TY → 59
VARIO30-02 ACDE-9/TY → 60
VARIO30-03 ACDE-9/TY → 63
COMBO30-01 ACDE-9 → 71
VARIO30-06 ACDE-9/U9 → 111
VARIO30-07 ACDE-9/U9 → 112
VARIO30-04 ACDE-9 → 153
VARIO30-05 ACDE-9 → 154




material / materiał / Material / matériel:

PC	PP	PP
transparent transparentny transparent transparent	frosted szron satinert givré	opal mleczny opal opaque
1000 mm V3000116	V3000139	V3000138
2000 mm V3000216	V3000239	V3000238
3000 mm -	V3000339	-

B

diffuser B slide
klosz B wsuwany
Abdeckung B einschiebbar
diffuseur B coulissant

UNI12 BCD/U → 38
SURFACE10 BC/UX → 40
SURFACE10.v2 BC/U → 42
SMART16 BC3/U4 → 48
GROOVE10 BC/UX → 92
GROOVE14.v2 BC3/Y → 98
DEEP10 BC/UX → 102
SMART-IN16 BC3/U4 → 104
QUARTER10 BD/U6 → 120
CORNER10 BC/UX → 126
FRAME14 BC/Q → 144
SMOOTH12 BC/Q9 → 146
WALLE12 BCD → 180



material / materiał / Material / matériel:

PC	PP	PP
transparent transparentny transparent transparent	frosted szron satinert givré	opal mleczny opal opaque
1000 mm 76000116	76000139	76000138
2000 mm 76000216	76000239	76000238
3000 mm -	76000339	-