




Technical manual  
Instrukcja techniczna  
Technische Anleitung  
Manuel technique



LED profile SKIRT10  
profil LED SKIRT10  
LED Profil SKIRT10  
profilé LED SKIRT10



white painted  
biały malowany  
weiß lackiert  
peint en blanc



anodized  
anodowany  
eloxiert  
surface anodisée



raw aluminium  
surowe aluminium  
Rohaluminium  
aluminium brut

|         |          |          |          |
|---------|----------|----------|----------|
| 1000 mm | J2000101 | J2000120 | J2000100 |
| 2000 mm | J2000201 | J2000220 | J2000200 |
| 3000 mm | J2000301 | J2000320 | J2000300 |
| 4050 mm | J2000401 | J2000420 | J2000400 |

complementary profile SKIRT10  
profil uzupełniający SKIRT10  
Ergänzungsprofil SKIRT10  
cache SKIRT10



white painted  
biały malowany  
weiß lackiert  
peint en blanc



anodized  
anodowany  
eloxiert  
surface anodisée



raw aluminium  
surowe aluminium  
Rohaluminium  
aluminium brut

|         |          |          |          |
|---------|----------|----------|----------|
| 1000 mm | J2000501 | J2000520 | J2000500 |
| 2000 mm | J2000601 | J2000620 | J2000600 |
| 3000 mm | J2000701 | J2000720 | J2000700 |
| 4050 mm | J2000801 | J2000820 | J2000800 |

## Q9<sup>1</sup> → 203

connector Q9 90 deg bent  
łącznik Q9 90 st gięty  
Verbinder Q9 90 Grad gebogen  
connecteur Q9 90 degrés pliable

## Q9<sup>2</sup> → 203

connector Q9 180 deg  
łącznik Q9 180 st  
Verbinder Q9 180 Grad  
connecteur Q9 180 degrés

## Q9<sup>3</sup> → 203

connector Q9 135 deg  
łącznik Q9 135 st  
Verbinder Q9 135 Grad  
connecteur Q9 135 degrés

## Q9<sup>4</sup> → 203

connector Q9 120 deg  
łącznik Q9 120 st  
Verbinder Q9 120 Grad  
connecteur Q9 120 degrés

## Q9<sup>5</sup> → 203

connector Q9 90 deg  
łącznik Q9 90 st  
Verbinder Q9 90 Grad  
connecteur Q9 90 degrés

## Q9<sup>6</sup> → 203

connector Q9 60 deg  
łącznik Q9 60 st  
Verbinder Q9 60 Grad  
connecteur Q9 60 degrés

## Q9<sup>7</sup> → 203

connector Q9 45 deg  
łącznik Q9 45 st  
Verbinder Q9 45 Grad  
connecteur Q9 45 degrés


## A → 194

diffuser A slide  
klosz A wsuwany  
Abdeckung A einschiebbar  
diffuseur A coulissant

## C2 → 196

diffuser C2 click  
klosz C2 klik  
Abdeckung C2 einclipsbar  
diffuseur C2 clic

end cap SKIRT10  
zaślepka SKIRT10  
Endkappe SKIRT10  
embout SKIRT10



white  
biały  
weiß  
blanc

silver  
srebrny  
silbern  
argent

grey  
szary  
grau  
gris

J2998901

J2998940

J2998922