



COMBO30-01 ACDE-9



sling
zawiesie
Abhängung
suspension
→ 209



2* → 198 end cap D9
zaślepka D9
Endkappe D9
embout D9

3* → 199 end cap E9
zaślepka E9
Endkappe E9
embout E9

7* → 203 holder Q9 for sling
uchwyt Q9 do zawiesia
Halter Q9 für Abhängung
fixation Q9 pour suspension

8* → 73 COMBO30-0203 holder
uchwyt COMBO30-0203
Halter COMBO30-0203
fixation COMBO30-0203

Technical manual
Instrukcja techniczna
Technische Anleitung
Manuel technique



white painted
biały malowany
weiß lackiert
peint en blanc



anodized
anodowany
eloxiert
surface anodisée




black anodized
czarny anodowany
schwarz eloxiert
noir anodisé



raw aluminium
surowe aluminium
Rohaluminium
aluminium brut

1000 mm	V6000101	V6000120	V6000121	V6000100
2000 mm	V6000201	V6000220	V6000221	V6000200
3000 mm	V6000301	V6000320	V6000321	V6000300
4050 mm	V6000401	V6000420	V6000421	V6000400

end cap COMBO30-01A
zaślepka COMBO30-01A
Endkappe COMBO30-01A
embout COMBO30-01A



white
biały
weiß
blanc

V6998901

silver
srebrny
silbern
argent

V6998940

black
czarny
schwarz
noir

V6998902

grey
szary
grau
gris

V6998922

end cap COMBO30-01A-D9
zaślepka COMBO30-01A-D9
Endkappe COMBO30-01A-D9
embout COMBO30-01A-D9



white
biały
weiß
blanc

V6999001

silver
srebrny
silbern
argent

V6999040


black
czarny
schwarz
noir

V6999002

grey
szary
grau
gris

V6999022

end cap COMBO30-01A-E9
zaślepka COMBO30-01A-E9
Endkappe COMBO30-01A-E9
embout COMBO30-01A-E9



white
biały
weiß
blanc

V6999101

silver
srebrny
silbern
argent

V6999140

black
czarny
schwarz
noir

V6999102

grey
szary
grau
gris

V6999122

C4 → 196

diffuser C4 click
klosz C4 klik
Abdeckung C4 einclipsbar
diffuseur C4 clic

Q9¹ → 203

connector Q9 90 deg bent
łącznik Q9 90 st gięty
Verbinder Q9 90 Grad gebogen
connecteur Q9 90 degrés suspendus

Q9² → 203

connector Q9 180 deg
łącznik Q9 180 st
Verbinder Q9 180 Grad
connecteur Q9 180 degrés

Q9³ → 203

connector Q9 135 deg
łącznik Q9 135 st
Verbinder Q9 135 Grad
connecteur Q9 135 degrés

Q9⁴ → 203

connector Q9 120 deg
łącznik Q9 120 st
Verbinder Q9 120 Grad
connecteur Q9 120 degrés

Q9⁵ → 203

connector Q9 90 deg
łącznik Q9 90 st
Verbinder Q9 90 Grad
connecteur Q9 90 degrés

Q9⁶ → 203

connector Q9 60 deg
łącznik Q9 60 st
Verbinder Q9 60 Grad
connecteur Q9 60 degrés

Q9⁷ → 203

connector Q9 45 deg
łącznik Q9 45 st
Verbinder Q9 45 Grad
connecteur Q9 45 degrés

A9 → 194

diffuser A9 slide
klosz A9 wsuwany
Abdeckung A9 einschiebbar
diffuseur A9 coulissant

C9 → 197

diffuser C9 click
klosz C9 klik
Abdeckung C9 einclipsbar
diffuseur C9 clic

D9 → 198

diffuser D9 click
klosz D9 klik
Abdeckung D9 einclipsbar
diffuseur D9 clic

E9 → 199

diffuser E9 click
klosz E9 klik
Abdeckung E9 einclipsbar
diffuseur E9 clic