



IFF1A004

3/3 Foam Inlays Sockets & Screwdrivers - 60 Pcs



PRODUCT DETAILS

- 3/3 foam with tools - 60 pieces
- Composition: 1/2" & 1/4" hex socket set; Phillips, slotted and Pozidriv screwdrivers; Ratchets and accessories
- - 1/4" sockets: Regular and deep sockets. Both 4 mm to 13 mm
- - 1/2" sockets: 10 mm to 32 mm
- - 1/4" and 1/2" reversible ratchets
- - Socket accessories
- - Slotted screwdrivers: engineer's (4x100, 5.5x125, 6.5x150, 8x175) and stubby (6.5x25)
- - Phillips screwdrivers: engineer's (1x100, 2x125, 3x150) and stubby (2x25)
- - Pozidriv screwdrivers (1x100, 2x125)

PRODUCT ATTRIBUTES

Product		
IFF1A004	40 x 543 x 445 mm	4 kg

SET CONTENT



Socket 1/4" Hex 4 mm
101-04-1



Socket 1/4" Hex 5 mm
101-05-1



Socket 1/4" Hex 6 mm
101-06-1



Socket 1/4" Hex 8 mm
101-08-1



Socket 1/4" Hex 10 mm
101-10-1



Socket 1/4" Hex 12 mm
101-12-1



Socket 1/4" Deep Hex 4 mm
103-04-1



Socket 1/4" Hex 4.5 mm
101-045-1



Socket 1/4" Hex 5.5 mm
101-055-1



Socket 1/4" Hex 7 mm
101-07-1



Socket 1/4" Hex 9 mm
101-09-1



Socket 1/4" Hex 11 mm
101-11-1



Socket 1/4" Hex 13 mm
101-13-1



Socket 1/4" Deep Hex 5 mm
103-05-1



Socket 1/4" Deep Hex 6 mm
103-06-1



Socket 1/4" Deep Hex 7 mm
103-07-1



Socket 1/4" Deep Hex 8 mm
103-08-1



Socket 1/4" Deep Hex 9 mm
103-09-1



Socket 1/4" Deep Hex 10 mm
103-10-1



Socket 1/4" Deep Hex 11 mm
103-11-1



Socket 1/4" Deep Hex 12 mm
103-12-1



Socket 1/4" Deep Hex 13 mm
103-13-1



Extension 1/4" 50 mm
105-22-1



Extension 1/4" 100 mm
105-24-1



Universal Joint 1/4"
105-40-1



Sliding T-Handle 1/4"
105-42-1



Bit Holder Square 1/4" with Hex 1/4"
105-48-1



Spinner Handle 1/4"
105-50-1



Ratchet 1/4" Pear Type, 72 Teeth,
150 mm
105-70-1



Extension 1/2" 125 mm
125-23-1



Extension 1/2" 250 mm
125-25-1



Universal Joint 1/2"
125-40-1



Sliding T-Handle 1/2"
125-42-1



Bit Holder 1/2" to Hex 5/16"
125-48-1



Spark Plug 1/2" Size 13/16"
125-54-1



Ratchet 1/2" Pear Type, 72 Teeth,
250 mm
125-70-1



Screwdriver Engineer's Slotted
0.8x4x100
407-4-100



Screwdriver Engineer's Slotted
1x5.5x125
407-5.5-125



Screwdriver Engineer's Slotted
1.2x6.5x150
407-6.5-150



Screwdriver Engineer's Slotted
1.6x8x175
407-8-175



Screwdriver Stubby Slotted 6x25
408-6.5-25



Screwdriver Phillips PH1x100
409-1-100



Screwdriver Phillips PH2x125
409-2-125



Screwdriver Stubby Phillips PH2x25
409-2-25



Screwdriver Phillips PH3x150
409-3-150



Screwdriver Pozidriv PZ1x100
413-1-100



Screwdriver Pozidriv PZ2x125
413-2-125



Socket 1/2" Hex 10 mm
121-10-1



Socket 1/2" Hex 11 mm
121-11-1



Socket 1/2" Hex 12 mm
121-12-1



Socket 1/2" Hex 13 mm
121-13-1



Socket 1/2" Hex 14 mm
121-14-1



Socket 1/2" Hex 15 mm
121-15-1



Socket 1/2" Hex 17 mm
121-17-1



Socket 1/2" Hex 19 mm
121-19-1



Socket 1/2" Hex 22 mm
121-22-1



Socket 1/2" Hex 24 mm
121-24-1



Socket 1/2" Hex 27 mm
121-27-1



Socket 1/2" Hex 30 mm
121-30-1



Socket 1/2" Hex 32 mm
121-32-1