




HOT AIR GUN ACCESSORIES


Reduction nozzles



Concentrates the air flow for precision.

Main application: Desoldering, bending plastic pipes, precision welding.

Wide-slot nozzles



Enlarges and flattens the air flow for efficiency on specific applications.

Main application: Applying ski wax, paint removing

ISABERG RAPID AB, BOX 115
SE-335 03 HESTRA, SWEDEN
www.rapid.com

Rapid®
SVENSK EFFIXITY



Glass protection nozzles



Enlarges the airflow and protect sensitive surfaces from heat (E.g., glass).
Main application: Paint removing with sensitive material in the heating area

Paint scraper set



For paint removal. Includes 3 cutting blades with different shapes to fit more surfaces.

ISABERG RAPID AB, BOX 115
SE-335 03 HESTRA, SWEDEN
www.rapid.com

Rapid®
SVENSK EFFIXITY



Reflector nozzle and Shrink tubing



Reflects the airflow to heat all around the material.
Main application: Used with shrink tubing to repair cable breaks, strengthen cable terminals etc.

Shrink tubing are available in 4 kits with mixed sizes and colours (black, yellow and red). One includes a reflector nozzle.

	Pieces Per Kit			
Size (mm)	Reflector kit	Kit 1	Kit 2	Kit 3
Ø1.5	16	20		
Ø2.5	16	20		
Ø3	16	20		6
Ø5	16	12	18	6
Ø7	12		12	6
Ø10	4		4	12
Ø12	3			12
Total	83	72	34	42



ISABERG RAPID AB, BOX 115
SE-335 03 HESTRA, SWEDEN
www.rapid.com

Rapid®
SVENSK EFFIXITY



Description	Packaging	Art. No	Dimensions	EAN	Outer
Reflector nozzle	Box	212150	50*50*110 mm	7313462121507	100 pcs
Reduction nozzle 9 mm	Box	24928500	50*50*110 mm	7313469285004	100 pcs
Reduction nozzle 14 mm	Box	5000207	50*50*110 mm	4051661008115	100 pcs
Reduction nozzle 20 mm	Box	212148	50*50*110 mm	7313462121484	100 pcs
Glass Protection nozzle 50 mm	Box	212149	50*50*110 mm	7313462121491	100 pcs
Glass Protection nozzle 75 mm	Box	24928600	75*50*120 mm	7313469286001	100 pcs
Wide-Slot nozzle 40 mm	Box	212151	50*50*110 mm	7313462121514	100 pcs
Wide-Slot nozzle 75 mm	Box	24928700	75*50*120 mm	7313469287008	100 pcs
Shrink Tubing Kit 1: 1,5-5 mm	Box	24947400	50*50*110 mm	7313469474002	100 pcs
Shrink Tubing Kit 2: 5 -10 mm	Box	24947500	50*50*110 mm	7313469475009	100 pcs
Shrink Tubing Kit 3: 3-12 mm	Box	5000208	50*50*110 mm	4051661008122	100 pcs
Reflector nozzle + Shrink Tubing	Box	5000209	75*50*120 mm	4051661008139	100 pcs
Paint Scraper Set	Box	5000210	70*40*295 mm	4051661008146	40 pcs

ISABERG RAPID AB, BOX 115
SE-335 03 HESTRA, SWEDEN
www.rapid.com

Rapid®
SVENSK EFFIXITY