

# DIGITUS DisplayPort Connection Cable

AK-340106-030-S  
EAN 4016032450306



## DisplayPort connection cable, DP M/M, 3.0m, w/lock, UHD 8K, Vers. 1.3/1.4, bl

With this cable standard, this DisplayPort cable supports all of today's requirements - from the playback of high-resolution UHD 8K content through 8-channel audio transmission to the support of HDCP and DPCP encryptions. Mirror your laptop desktop on a large monitor or extend your desktop with another DisplayPort display. This high-quality cable allows rapid data transfer without jerking, even in demanding graphics applications or games. Gold-plated contacts and double shielding of the cable ensure maximum conductivity and trouble-free transmission.

### Ideal for CAD/CAM, GIS, 3D modeling, real time simulation, and more.

- Transmission Rate: up to 32,4 GBit/s
- Support up to 4K/2K@120Hz (Ultra HD) resolution
- Support up to 5K@60Hz (Ultra HD) resolution
- Support up to 8K@30Hz (Ultra HD) resolution

- Supported Video Resolution: 7680 x 4320 dpi; 5120 x 2880 dpi; 3840 x 2160 dpi
- Color depth: 24bit RGB
- Support of 1-8 audio channels for audio transmission
- Audio sampling rate: 32-192 kHz by max. bitrate of 4.608 kB/s
- Support of HDCP and DPCP
- Plug & Play installation
- Color cable: black
- Connector 1: DP, plug
- Connector 2: DP, plug
- Connector surface: nickel-plated
- DisplayPort standard: DisplayPort 1.4
- HDTV Resolution max.: 7680 x 4320 Pixel, 60Hz
- HDTV Standard: Ultra HD 8K
- Hoods: molded
- Length: 3 m
- AOC - Active Optical Cable: no

## Logistics

|                              | Number<br>(pcs) | Weight<br>(kg) | Depth<br>(cm) | Width<br>(cm) | Height<br>(cm) | cm <sup>3</sup> |
|------------------------------|-----------------|----------------|---------------|---------------|----------------|-----------------|
| Packaging Unit Carton        | 50              | 10.50          | 44.00         | 33.00         | 22.00          | 31,944.00       |
| Packaging Unit Inside        | 5               | 1.05           | 33.00         | 39.00         | 10.00          | 12,870.00       |
| Packaging Unit Single        | 1               | 0.21           | 26.00         | 2.50          | 27.00          | 1,755.00        |
| Net single without Packaging | 1               | 0.20           | 26.00         | 2.50          | 27.00          | 1,755.00        |

More images:

