






- Ⓓ Anschluss **ausschließlich** durch ausgebildete Elektro-Fachkräfte.
 ⒼⒸ Electrical connection is to be made by trained electrical specialists **only**.
 Ⓕ Le branchement doit **uniquement** être effectué par des professionnels.
 Ⓘ Il collegamento deve essere eseguito **solo** da elettricisti specializzati.
 Ⓔ La conexión **sólo** debe ser realizada por electricistas debidamente formados.
 Ⓟ A ligação deve ser feita **exclusivamente** por profissional eléctrico especializado.
 ⓃⓁ De aansluiting mag **enkel** gebeuren door erkende vakmensen.
 ⒸⓏ Připojení smí **provádět** pouze kvalifikovaný personál.
 Ⓟ Podłączenie **wyłącznie** przez specjalistów-elektryków.
 Ⓕ Liittäminen kuuluu **ainoastaan** koulutettujen sähköalan ammattilaisten tehtäviin.
 ⓇⓊⓈ Подключение проводится только специа-листом-электриком.
 ⓉⓇ Bağlantı **sadece** eğitimli elektrik teknisyenleri tarafından yapılmalıdır.
 ⒸⓃ 布线需由专业电工执行




	640 840 00 Ø 70 x 36 mm 24 V=, ≤ 90 mA		
	649 000 05 Ø 70 x 36 mm 24 V=, ≤ 90 mA		
LED Permanent	644 x00 75	24 V≈	35 mA
LED Blinking	644 x10 75	24 V≈	30 mA
LED Flash	644 x20 55	24 V=	35 mA
LED Rotating	644 x30 75	24 V≈	40 mA
 < 85 dB	645 800 75	24 V≈	25 mA
 < 100 dB	645 850 55	24 V≈	80 mA
WIN slave	860 640 02	24 V≈	40 mA
WIN slave performance	860 640 12	24 V≈	40 mA
TwinLIGHT	647 x10 75 647 x30 75	24 V≈ 24 V≈	< 80 mA < 80 mA
TwinFLASH	647 x20 55 647 x40 55	24 V= 24 V=	< 80 mA < 80 mA
 95 - 105 dB	645 x70 75	24 V≈	< 40 mA
 < 102 dB	645 x90 75	24 V≈	< 30 mA



- Ⓓ Systemanforderungen im Handbuch
 ⒼⒸ System requirements in the manual
 Ⓕ Les données du système sont dans la notice



- Ⓓ Administratorrechte erforderlich
 ⒼⒸ Administration rights are necessary
 Ⓕ Les droits administrateur sont nécessaires







1

1a - 975 840 91
1b - 960 000 01
1c - 960 000 41


1a




1b




1c




2




3



4




5




6a

647 x10 75
647 x30 75




6b

647 x20 55
647 x40 55




7



7a

645 x70 75



7b

645 800 xx



310.640.012.0518_AB

© D

WERMA