

6 in 1

Multifunctional USB-C Hub

Refuse onefold interface on Ultrabook/MacBook



PD 87W

USB 3.0
interface

HDMI+VGA

Driver
free



Widen Your Vision

Two video interfaces for large screen extension



PD fast charge

Superior Charging Ability

Support PD 87W power supply, fast charge for MacBook



Note: All data are from Vention Lab



USB3.0

Offer the Solution to Interface Lackness

With 3 USB 3.0 ports, support simultaneous connection for mouse, keyboard, flash disk and mobile HDD, etc.



mouse



keyboard



flash disk



mobile HDD

5Gbps



Note: All data are from Vention Lab



HDMI interface

Compatible with Switch

Nintendo Switch connects to TV
enjoy 4K visual experience



Note: the picture of Mario Kart is from Internet,
All rights reserved by the original author, All data are from Vention Lab



VGA Interface

Efficient Business Demonstration


Laptop connects to projector
support up to 1080P resolution and screen synchronization



Note: All data are from Vention Lab

HDMI+VGA 2-in-1

Simultaneous output 1080P resolution in two screens,
convenient for officing and learning




Note: All data are from Vention Lab

High Performance Chip

Upgraded independent chip,
stable operation for multiple function use

HUB chip:
VL817

HDMI+VGA+PD chip:
LT8712X



Note: The chip/circuit board is a rendering, please in kind prevail

Driver Free in Various Systems

Compatible with Mainstream OS



Designed for **USB-C** Interface

Suitable for USB 3.1-C interface extension,
screen projection and USB peripherals
connection of notebook, mobile phone and tablet



Laptop



Mobile
phone



Tablet



Nintendo
Switch

.....

Applicable USB-C Devices

	Laptop	Cellphone
Apple	MacBook12", MacBook Pro 2019 Mac Mini, MacBook Air 2020	Huawei Nova5/6/7 Mate20/30, Mate20/30 Pro Mate20/30 RS P20/30/40 P20/30/40 Pro
Huawei	MateBook, MateBook X/E MateBook 13/14	
Honor	MagicBook, MagicBook 2019	
Xiaomi	Air12.5"/13.3", GTX version 15.6" Xiaomi game book 8 generation	
HP	Pavilion x2, Spectre 13 EliteBook Folio G1, Envy 13 Shadow Wizard 4 Pro	Honor 30, 30S, V30 V20, Magic2 Note 10, V10
ASUS	Ling Yao 3, Ling Yao 3 Pro Ling Yao X series, U306, U321 U4100UN, U5100UQ, ROG	Microsoft Microsoft 950XL Microsoft 950
Dell	XPS13/15, Latitude 5285, G+C22 G3/G5/G7, Lingyue 5000/7000	Xiaomi 9/10 Pro, 9/10 8/9se, 8, 8 Lite Redmi Note7 Redmi K20/K30 (Only supports data transmission & charging)
Lenovo	Xiaoxin Air 12", Yoga5/6 Pro ThinkPad_X1 Carbon 2017 Saver Y7000/Y7000P/Y9000K	
SAMSUNG	NoteBook series GalaxyBook series	LG G5, V300L
Google	ChromeBook Pixels PixelBook Pen	Samsung S10, S10+, S10e A9s, A9 Stat Note8/9/10
Razer	Blade Stealth Spirit Blade Spirit Blade Sneak Edition	
Microsoft	Surface Book 2, Surface GO	Meizu 16/17th, X8
HTC	HTC 10	vivo Z5, iQOO, X27
Tablet	Apple iPad Pro 2018/2020	OPPO R17 Pro
	Huawei MediaPad M5	Smartisan Nut Pro 2S
	Xiaomi MI PAD 4	BlackShark BlackShark 2
More USB-C models will be continuously updated ...		

Premium Aluminum Alloy Shell

Metal texture, wear resistance,
good heat dissipation, strong and durable



Anti-fingerprint



Aluminum alloy



Good heat dissipation



Travelling Convenient

Easily fits in briefcase without any burden



Product Parameters

Brand: Vention

Name: USB-C to HDMI+VGA+USB3.0*3+PD Hub

Model: TGSHB

Color: Gray

Interface: USB-C/HDMI/VGA/USB 3.0*3/PD

Interface Technics: Nickel-plated

Transmission Speed: 5Gbps

Resolution: 4K@30Hz(HDMI)/1080P@60Hz(VGA)/1080P@60Hz(Simultaneous output)

Rated Power: 87W

Conductor: Tinned-copper

Shell: Aluminum Alloy+ABS

Chip: LT8712X(HDMI+VGA+PD)+VL817(HUB)

Shielding: Aluminum Foil+Metal Braided

Jacket: PVC


AWG: 26AWG+30AWG

OD: 4.5mm

Length: 0.15

Warranty: 1 Year

Packing: Color Box+Kraft Box



Note: All data are from Vention Lab.
Sizes above are manually measured. There might be slight tolerance.



Note: Packing difference exists for different meters or batches.
The photo is for reference only



6-in-1 USB-C Docking Station

Technical Features	
Color	Gray
Interface	USB-C/HDMI/VGA/USB 3.0 x 3/PD
Connector Process	Nickel-Plated
Material	Aluminum alloy + ABS
Data transfer rates	5Gbps (USB 3.0)
Power supply	100W PD
Resolution	4K@30Hz (HDMI)/1080p@60Hz (VGA)/1080p@60Hz (HDMI + VGA)

Length	Art.No.	EAN Code
0.15m	TGSHB	6922794749290



Package Contents
6-in-1 USB-C Docking Station x 1

Packaging Information	
Packing Dimension	17.25*9.25*2.75cm
Packing Weight	0.107kg
Carton Dimension	50*37*34cm
Carton Qty	100pcs
Carton Weight	11.7kg