

USB-C 9-in-1 Multifunctional Adapter

Large screen
expansion

Data
transmission

Card
reading

RJ45
1000Mbps

3.5mm
audio

PD
fast charge



USB-C 9 in 1

Multiple device connections



Connect Nintendo to TV

Wider vision, you can charge while playing games



Note: Mario Kart screenshots are from the Internet and are copyrighted by the original author



Premium 4K UHD Video

HDMI port provides MAX 4K*2K

Note: Both laptop and TV equipment are required to support 4K
All data are from Vention lab.

Transfer 1GB Movie in 5 Seconds

3*USB3.0 ports



Hard disk



U disk



Keyboard



Mouse



Note: All data are from Vention lab

TF/SD Card Reader

Solve the problem of MacBook/Super Book reader



Note: Only one card can be read at a time, the maximum capacity is 256G.

Gigabit Network Stable Transmission

Video viewing, working is more efficient



A silver VENTION USB-C to 3.5mm audio adapter is shown connected to a laptop. The adapter has a USB-C port on one end, a 3.5mm audio port on the other, and an Ethernet port on the side. A blue callout box points to the 3.5mm audio port.

3.5mm Audio Port

Independent 3.5mm Audio Port

Solve the problem that the laptop has no audio port or the audio port is damaged

Fully Charged Within 1.5h for MacBook


87W fast charge, can quickly supply
power to PD-enabled devices



Note: All data are from Vention lab.

Mobile Phone Becomes Computer

Huawei Mate30 Pro/P30 Pro to large-screen TV



Applicable Devices List

Suitable for computer and cellphone with full function USB-C ports

	Laptop	Mobile Phone
Apple	MacBook12" MacBook Pro2016/2017/2018 Mac Mini, MacBook Air 2018	SAMSUNG Note8 Note9
Huawei	MateBook, MateBook X MateBook X Pro, MateBook E MateBook 13, MateBook 14	S8/S8+ S9/S9+S10/ S10+
Honor	MagicBook	Huawei
Xiaomi	Air12.5"/ 13.3", Pro15.6" GTX version 15.6" Xiaomi game book 8 generation	Mate10, Mate10 Pro, Mate20, Mate20 Pro, Mate20 X
HP	Pavilion x2, Spectre 13 EliteBook Folio G1 Elite Book 1050 G1 Envy 13 Shadow Wizard 4 Pro	Mate20 RS, P20 P20 Pro, Mate X P30, P30 Pro
ASUS	Ling Yao 3, Ling Yao 3 Pro U306, U321 U4100UN, U5100UQ, ROG	Honor Glory Note 10, Glory V20
Dell	XPS13/15, Latitude 5285, G+C22 G3/G5/G7, Lingyue 5000/7000	Microsoft Microsoft 950XL Microsoft 950

Lenovo	Xiaoxin Air 12", Yoga5 Pro Yoga6 Pro, Yoga 900 13" Miix 720 ThinkPad_X1, Carbon 2017/ Saver Y7000/Y7000P/Y9000K	LG G5, V300L
SAMSUNG	NoteBook series GalaxyBook series	Smartisan Nut R1, Nut Pro 2S
Google	ChromeBook Pixels PixelBook Pen	OPPO R17 Pro
Razer	Blade Stealth Spirit Blade Spirit Blade Sneak Edition	BlackShark BlackShark 2
Microsoft	Surface Book 2, Surface GO	iPad
HTC	HTC 10	Apple ipad Pro 2018 11"/12.9"
More USB-C models will be continuously updated		

Compatible with Multiple Systems



Beautiful&Practical



01

**Alloy casing+surface
anodizing process**

Good heat dissipation,
comfortable touch

02

Durable Connector
Compatible with USB-C



High Performance Chip

LT8711HE

HDMI

VL817

PD

RTL8153B

RJ45

GL823K


SD/TF

FE8.1

USB3.0

SSS1530

3.5mm Audio



Product Parameters

Brand: Vention	Shell: Aluminum Alloy + ABS
Name: USB-C to HDMI/USB3.0*3/TF/SD/ RJ45/3.5mm/PD Converter	Chip: LT8711HE+VL817+TRL8153B +GL823K+FE8.1+SSS1530
Model: THAHB	Shielding: Aluminum Foil
Color: Grey	Jacket: PVC
Version: HDMI 1.4, USB3.0, Gigabit Network	AWG: 30AWG+24AWG
Interface Technics: Nickel-plated	OD: 4.5mm
Resolution: 4K@30Hz	Length: 0.15m
Transmission Speed: 5Gbps	Power: 87W
Conductor: Tinned Copper	Warranty: 1 Year
Interface: USB-C, HDMI, USB3.0*3、 TF/SD, RJ45, 3.5mm, PD	
Transmission Direction: USB-C to HDMI/USB3.0/TF/SD/RJ45/3.5mm/PD	
Packing: Color Box	



Note: All data are from Vention Lab.
Sizes above are manually measured. There might be slight tolerance.



Note: Packing difference exists for different meters or batches.
The photo is for reference only.



9-in-1 USB-C Docking Station

Technical Features		
Color	Gray	
Interface	USB-C/HDMI/USB 3.0 x 3/RJ45/SD/TF/3.5mm TRRS/PD	
Connector Process	Nickel-Plated	
Material	Aluminum alloy + ABS	
Power supply	100W PD	
Resolution	4K@30Hz	
Data transfer rates	5Gbps (USB 3.0)	
Transmission rate	10/100/1000Mbps	
Card slot type	SD/TF 1-LUN (Read/Write only one card at a time)	
Card slot speed	USB 2.0	
Compatible audio standard	OMTP&CTIA	
Length	Art.No.	EAN Code
0.15m	THAHB	6922794742611
Package Contents		
9-in-1 USB-C Docking Station x 1		
Packaging Information		
Packing Dimension	17.25*9.25*2.75cm	
Packing Weight	0.114kg	
Carton Dimension	50*37*34cm	
Carton Qty	100pcs	
Carton Weight	12.4kg	

