


USB-C 5-in-1 Docking Station

Multifunction extension



5 Multiple Ports

5 in 1, cater to various functions



USB 3.0

USB Peripherals Connection

Three USB 3.0 ports for
USB peripherals connection

5Gbps



Flash
disk



Card
reader



Printer



Cooler



Graphics
drawing tablet



Mouse



U-KEY



USB
desk fan



USB
desk lamp



Keyboard

Note: All data are from Vention Lab

1GB File within 3 Seconds

Standard USB3.0 interface with
5Gbps theoretical transmission rate



Note: All data are from Vention Lab

PD port

100W Fast Charging

Offer charging solution to single-port laptop

Around 1.5 hours

Full of MacBook Pro13"

Around 2 hours

Full of MateBook 13



Note: All data are from Vention Lab

HDMI port

Switch Supported

Enjoy home video game in large screen



4K High Resolution


Support up to 4K@30Hz via HDMI port



Note: the display devices should also support 4K resolution,
all data are from Vention Lab

Large Screen Extension

Turns your phone to PC, charging,
USB peripheral connection in Sync



HDMI



USB



PD

Driver Free in Various Systems

Compatible with Mainstream OS



Windows10



Windows8



Windows7



WindowsXP



Mac OS



Vista



Linux



Android OS



iOS

Universal Compatibility

Fully compatible with Apple M1 chip series,
unlock chip performance



M1

Note: Support Apple M1 models
(MacBook Air 2020, MacBook Pro 13/16 2020)

Designed for USB-C Interface

Laptop



MacBook



Lenovo



MateBook



HP



ASUS



Xiaomi



Dell



Other devices...

Tablet



iPad



MatePad



Surface



Other devices...

Mobile Phone



Huawei Mate40
Mate 40 Pro/20 X



Huawei P40
P40 Pro



Samsung S20/S10+
Note20



OPPO Reno 3
R17 Pro



Smartisan R1
Pro 2S



Other devices...



Part of Supported Models

Laptop

Apple	MacBook12", MacBook Pro2016/2017/2018/2019, Mac Mini, MacBook Air 2018/2019/2020
Huawei	MateBook, MateBook X, MateBook X Pro, MateBook X Pro 2019, MateBook E, MateBook E 2019, MateBook 13, MateBook 14
Honor	MagicBook, MagicBook 2019
Xiaomi	Air12.5"/ 13.3", Pro15.6", GTX version 15.6", Xiaomi game book 8 generation
HP	Pavilion x2, Spectre 13, EliteBook Folio G1, Elite Book1050 G1, Envy 13, Shadow Wizard 4 Pro
ASUS	Ling Yao 3, Ling Yao 3 Pro, Ling Yao X series, U306, U321, U4100UN, U5100UQ, ROG
Dell	XPS13/15, Latitude 5285, G+C22, G3/G5/G7, Lingyue 5000/7000
Lenovo	Xiaoxin Air 12", Yoga5 Pro, Yoga6 Pro, Yoga 900 13", Miix 720, ThinkPad_X1 Carbon 2017, Saver Y7000/Y7000P/Y9000K
SAMSUNG	NoteBook series, GalaxyBook series
Google	ChromeBook Pixels, PixelBook Pen
Razer	Blade Stealth Spirit Blade, Spirit Blade Sneak Edition
Microsoft	Surface Book 2, Surface GO
HTC	HTC 10

Mobile Phone

SAMSUNG	Note8, Note9, S8/S8+, S9/S9+, S10/S10+, S20, Note10, Note10+
Huawei	Mate10, Mate10 Pro, Mate20, Mate20 Pro, Mate20 X, Mate20 RS, P20, P20 Pro, Mate X, P30, P30 Pro, Mate30, Mate30 Pro, P40, P40Pro
Microsoft	Microsoft 950XL, Microsoft 950
LG	G5, V300L
Smartisan	Nut R1, Nut Pro 2S
OPPO	R17 Pro, Reno 10x Zoom
BlackShark	BlackShark 2

iPad

Apple	iPad Pro 2018/2020
Huawei	MatePad 10.4/10.8", MatePad Pro, MediaPad M6
Microsoft	Surface Pro7, Surface Go/Go2, Surface Book 2

More USB-C models will be continuously updated
Note: not applicable to Xiaomi / Redmi USB-C mobile phones

OTG Function

Connect I/O devices with phone/tablet



Note: The phone/tablet must support OTG function

More Details

01

Aluminum alloy shell
Good heat dissipation



02

Nickel-plated interface
Wear resistance

03

Small and portable
Easy to carry around



Product Parameters

Brand: Vention

Name: USB-C to HDMI/USB 3.0x3/PD Docking Station Aluminum Alloy Type

Model: TOD

Color: Gray

Interface: USB-C/HDMI/USB 3.0/PD

Interface Technics: Nickel-plated

Resolution: 4K@30Hz

Transmission Speed: 5Gbps

Conductor: Tinned-copper

Shell: Aluminum Alloy

Shielding: Aluminum Foil+Metal Braided+GND

Jacket: TPE

AWG: 34+26AWG

OD: 4.2mm

Length: 0.15m

Power Supply: 100W

Warranty: 1 Year

Packing: PE Bag



Note: All data are from Vention Lab.
Sizes above are manually measured. There might be slight tolerance.



Note: Packing difference exists for different meters or batches.
The photo is for reference only



5-in-1 USB-C Hub

Technical Features	
Color	Gray
Interface	USB-C/HDMI/USB 3.0 x 3/PD
Connector Process	Nickel-Plated
Material	Aluminum alloy + ABS
Data transfer rates	5Gbps (USB 3.0)
Power supply	100W PD
Resolution	4K@30Hz

Length	Art.No.	EAN Code
0.15m	TODHB	6922794754720



Package Contents
5-in-1 USB-C Hub x 1

Packaging Information	
Packing Dimension	17.25*9.25*2.75cm
Packing Weight	0.121kg
Carton Dimension	40*30*30cm
Carton Qty	60pcs
Carton Weight	8.26kg