

6-in-1
USB-C Docking Station
Extension for office life



SS
5Gbps
Fast transmission

PD
PD 100W
Fast charging

RJ45
1000Mbps
RJ45 interface

4K
4K UHD
HDMI

6 Multiple Ports

6 in 1, cater to various functions



USB 3.0

USB Peripherals Connection

Three USB 3.0 ports for USB peripherals connection



Flash disk



Card reader



Printer



Cooler



Graphics
drawing tablet



Mouse



U-KEY



USB
desk fan



USB
desk lamp



Keyboard

Note: All data are from Vention Lab

1GB File within 3 Seconds

Standard USB3.0 interface
with 5Gbps theoretical transmission rate

Note: all data are from Vention Lab



PD port

100W Fast Charging

Offer charging solution to single-port laptop

1.5h ⚡

Full of MacBook Pro13"

2h ⚡

Full of MateBook 13



Note: All data are from Vention Lab

Gigabit Ethernet

No lag in officing/gaming/movie-watching



Note: All data are from Vention Lab

HDMI interface

4K UHD Resolution

Connect your laptop with larger screen
for cinematic audio&visual experience



Note: all data are from Vention Lab

iPad Supported

Turns your iPad Pro/Air4 into computer
for more variabilities



Flash disk



Keyboard




Mouse



Large Screen Extension

Turns your phone to PC for USB peripheral connection



HDMI



USB



PD

Driver Free in Various Systems

Compatible with Mainstream OS



Windows10



Windows8



Windows7



WindowsXP



Mac OS



Vista



Linux



Android



iOS



Designed for USB-C Interface

Laptop



MacBook



Lenovo



MateBook



HP



ASUS



Xiaomi



Dell



Other devices...

Tablet



iPad



MatePad



Surface



Other devices...

Mobile Phone



Huawei Mate40
Mate 40 Pro/20 X



Huawei P40
P40 Pro



Samsung S20/S10+
Note20



OPPO Reno 3
R17 Pro



Smartisan R1
Pro 2S



Other devices...



Part of Supported Models

Laptop

Apple	MacBook12", MacBook Pro2016/2017/2018/2019, Mac Mini, MacBook Air 2018/2019/2020
Huawei	MateBook, MateBook X, MateBook X Pro, MateBook X Pro 2019, MateBook E, MateBook E 2019, MateBook 13, MateBook 14
Honor	MagicBook, MagicBook 2019
Xiaomi	Air12.5" / 13.3", Pro15.6", GTX version 15.6", Xiaomi game book 8 generation
HP	Pavilion x2, Spectre 13, EliteBook Folio G1, Elite Book1050 G1, Envy 13, Shadow Wizard 4 Pro
ASUS	Ling Yao 3, Ling Yao 3 Pro, Ling Yao X series, U306, U321, U4100UN, U5100UQ, ROG
Dell	XPS13/15, Latitude 5285, G+C22, G3/G5/G7, Lingyue 5000/7000
Lenovo	Xiaoxin Air 12", Yoga5 Pro, Yoga6 Pro, Yoga 900 13", Miix 720, ThinkPad_X1 Carbon 2017, Saver Y7000/Y7000P/Y9000K
SAMSUNG	NoteBook series, GalaxyBook series
Google	ChromeBook Pixels, PixelBook Pen
Razer	Blade Stealth Spirit Blade, Spirit Blade Sneak Edition
Microsoft	Surface Book 2, Surface GO
HTC	HTC 10

Mobile Phone

SAMSUNG	Note8, Note9, S8/S8+, S9/S9+, S10/S10+, S20, Note10, Note10+
Huawei	Mate10, Mate10 Pro, Mate20, Mate20 Pro, Mate20 X, Mate20 RS, P20, P20 Pro, Mate X, P30, P30 Pro, Mate30, Mate30 Pro, P40, P40Pro
Microsoft	Microsoft 950XL, Microsoft 950
LG	G5, V300L
Smartisan	Nut R1, Nut Pro 2S
OPPO	R17 Pro, Reno 10x Zoom
BlackShark	BlackShark 2

iPad

Apple	iPad Pro 2018/2020
Huawei	MatePad 10.4/10.8", MatePad Pro, MediaPad M6
Microsoft	Surface Pro7, Surface Go/Go2, Surface Book 2

More USB-C models will be continuously updated
Note: not applicable to Xiaomi / Redmi USB-C mobile phones

High Performance Chips

Stable and fast operation

AG9311

HDMI+PD chip

GL3510

HUB chip

RTL8153

Network Card chip

Note: All data are from Vention Lab



More Details

01

Aluminum alloy shell

Good heat dissipation



02

Nickel-plated interface

Wear resistance



03

Small and portable

Easy to carry around



Product Parameters

Brand: Vention

Name: USB-C to HDMI/USB3.0x3/RJ45/PD Docking Station

Model: TOHHB

Color: Gray

Interface: USB-C/HDMI/USB3.0/RJ45/PD

Interface Technics: Nickel-plated

Resolution: 4K@30Hz

Transmission Speed: USB3.0: 5Gbps; RJ45: 10/100/1000Mbps

Conductor: Tinned-copper

Shell: Aluminum Alloy

Chip: AG9311/RTL8153/GL3510

Shielding: Aluminum Foil+Metal Braided+GND

Jacket: TPE

AWG: 32AWG+26AWG

OD: 4.2mm

Length: 0.15m

Power Supply: 100W

Warranty: 1 Year

Packing: PE Bag



Note: All data are from Vention Lab.
Sizes above are manually measured. There might be slight tolerance.



6-in-1 USB-C Docking Station

Technical Features	
Color	Gray
Interface	USB-C/HDMI/USB 3.0 x 3/RJ45/PD
Connector Process	Nickel-Plated
Material	Aluminum alloy + ABS
Data transfer rates	5Gbps (USB 3.0)
Power supply	100W PD
Resolution	4K@30Hz
Transmission rate	10/100/1000Mbps

Length	Art.No.	EAN Code
0.15m	TOHHB	6922794754737



Package Contents
6-in-1 USB-C Docking Station x 1

Packaging Information	
Packing Dimension	17.25*9.25*2.75cm
Packing Weight	0.123kg
Carton Dimension	48*29*30cm
Carton Qty	75pcs
Carton Weight	10.225kg