

9 in 1 USB-C Docking Station

Expand multiple possibilities



PD
100W



1000M
RJ45



USB3.0
HUB



HDMI



3.5mm
Audio



Card
Reader

Extend 9 ports for your laptop

Meets Every Need of Almost All USB C Devices





U disk



Mobile Hard disk



Keyboard



Mouse

USB 3.0 HUB

Designed for connecting any device with USB3.0 male port

Instant Internet

Instant access to the internet with the gigabit ethernet port



Nintendo Switch to TV

Large screen content extension, enjoy gaming as long as charging the Switch



Note: this product support Nintendo Switch, but network port is not supported. The picture of Mario Kart is from Internet all rights reserved by original author.

4K@30Hz UHD Resolution

Stream media to a large monitor or TV

* Both laptops and TV need to support 4K resolution
The above data comes from Vention lab.




USB-C Power Delivery

Playing as well as charging, get rid of low battery situation



Note: All data are from Vention Lab



3.5mm Audio Output

External audio equipment connection for enhanced music listening experience



Card Reader Slot


External memory card reading, convenient for camera/mobile phone file sharing

Support card type: Micro SD/Micro SDHC/Micro SDXC SD/SDHC/MMCII/RSMMC

PS: only one card can be read at a time, with a capacity limit of 128G

High Efficient Demonstration

Huawei Mate10/P20 connects to a large screen TV



VENTION

VENTION

Wide Compatibility

USB C
Laptop



Apple
MacBook



HUAWEI
MateBook



XIAOMI
Laptop



ASUS
Laptop

USB C
Phone



HUAWEI
Mate10 Pro



HUAWEI
P20 Pro



HUAWEI
Mate20/20Pro/20X



SAMSUNG
S8/S8+/S9/S9+

Widely Compatible



Windows 7



Windows 8



Windows 10



Mac OS

Aluminum Alloy Shell

Keep cool during operation



Heat-dissipation



Aluminum alloy shell



Wear-resistant



Easy to Carry

Compact and slim, ideal for carrying, commuting and travelling


Make Your MacBook More Easy to Use



[SHOP NOW >>](#)

Product Parameters

Brand	Vention
Name	USB-C Docking Station
Model	CGN
Color	Gray
Interface	USB-C/HDMI/RJ45/USB/TF/SD/3.5mm
Interface Technics	Nickel-plated
Resolution	4K@30Hz
Direction	USB-C Input, HDMI Output
Conductor	Tinned-copper
Shell	Aluminum Alloy
Shielding	Aluminum Foil+Metal Braided
Jacket	TPE
AWG	32AWG+24AWG
OD	4.5mm
Length	10cm
Power Supply	PD 100W
Warranty	1 Year
Packing	Color Box







9-in-1 USB-C Docking Station

Technical Features	
Color	Gray
Interface	USB-C/HDMI/USB 3.0 x 3/RJ45/SD/TF/3.5mm TRRS/PD
Connector Process	Nickel-Plated
Material	Aluminum alloy + ABS
Power supply	100W PD
Resolution	4K@30Hz
Data transfer rates	5Gbps (USB 3.0)
Transmission rate	10/100/1000Mbps
Card slot type	SD/TF 1-LUN (Read/Write only one card at a time)
Card slot speed	USB 2.0
Compatible audio standard	OMTP&CTIA

Length	Art.No.	EAN Code
0.1m	CGNHA	6922794735163



Package Contents
9-in-1 USB-C Docking Station x 1

Packaging Information	
Packing Dimension	19.1*9.7*2.3cm
Packing Weight	0.116kg
Carton Dimension	48*29*30cm
Carton Qty	70pcs
Carton Weight	9.12kg