


USB-C to VGA HD Adapter

Mobile phone / laptop connect to large screen



HD
1080P

Double
modes

Gold-plated
interface

Mobile Phone Connect to TV

Large screen watch TV shows more shocking



Laptop Connect to Monitor

Switch between work and entertainment at any time



Laptop Connect to Projector

Large screen work more efficiently



1080P HD

Support 1920*1080@60Hz,video picture more delicate



Double Modes

01

Mirror mode

Show the same picture, larger screen is more exciting



02

Expansion mode

Display the different picture, work as well as play



Upgraded Chip Anti-splash


Realtek 2169 chip, stable and
smooth data transmission



Note: The chip/PCB is a rendering, the internal structure is not fully displayed, please refer to the actual product

Double Shielding

Tinned-copper core +Aluminum foil +Metal braided
multiple protection,shielding interference




Excellent Details

01

Gold-plated Interface

Anti-oxidation,
anti-corrosion, rustless,
more durable



02

ABS shell

Arc concave design,
easier to handle

Suit for USB-C Interface Mobile Phone /Laptop

Suit for MacBook, Matebook, Xiaomi notebook
and Huawei P30, Mate20, Samsung S9, S10 mobile phones



Please check your device interface before buying

USB-C interface
Output device



VGA interface
Display device



Mobile phone



Tablet



Laptop



TV



Projector



Monitor

Note: USB-C to VGA (unsupported bi-directional conversion)

Applicable Devices List

Suitable for computer and cellphone with full function USB-C ports

	Laptop	Mobile Phone
Apple	MacBook12" MacBook Pro2016/2017/2018/2019 Mac Mini, MacBook Air 2018/2019 /2020	SAMSUNG Note8 Note9 S8/S8+ S9/S9+ S10/S10+ Note10 Note10+
Huawei	MateBook, MateBook E/E 2019 MateBook X/X Pro/X Pro 2019 MateBook 13, MateBook 14	
Honor	MagicBook, MagicBook 2019	Huawei Mate10 Mate10 Pro Mate20 Mate20 Pro Mate20 X Mate20 RS, P20 P20 Pro, Mate X P30, P30 Pro Mate30 Mate30 Pro P40, P40 Pro
Xiaomi	Air12.5"/ 13.3", Pro15.6" GTX version 15.6" Xiaomi game book 8 generation	
HP	Pavilion x2, Spectre 13 EliteBook Folio G1 Elite Book 1050 G1, Envy 13 Shadow Wizard 4 Pro	
ASUS	Ling Yao 3, Ling Yao 3 Pro Ling Yao X series, U306, U321 U4100UN, U5100UQ, ROG	Honor Glory Note 10 Glory V20
Dell	XPS13/15, Latitude 5285, G+C22 G3/G5/G7, Lingyue 5000/7000	Microsoft Microsoft 950XL Microsoft 950
Lenovo	Xiaoxin Air 12", Yoga5 Pro Yoga6 Pro, Yoga 900 13" Miix 720 ThinkPad_X1 Carbon 2017 Saver Y7000/Y7000P/Y9000K	LG G5, V300L
SAMSUNG	NoteBook series GalaxyBook series	Smartisan Nut R1 Nut Pro 2S
Google	ChromeBook Pixels PixelBook Pen	OPPO R17 Pro
Razer	Blade Stealth Spirit Blade Spirit Blade Sneak Edition	BlackShark BlackShark 2
Microsoft	Surface Book 2, Surface GO	iPad
HTC	HTC 10	Apple iPad Pro 2018/ 2019/2020
More USB-C models will be continuously updated ...		

Note: Recommend use 45W charger to charge the MacBook 12"

Small Size

Easy to carry around

Wire length

15cm



Product Parameters

Brand: Vention	Chip: Realtek 2169
Name: USB-C to VGA Adapter	Shielding: Aluminum Foil+Metal Braided
Model: TDDBB	Jacket: TPE
Color: Black	AWG: 34AWG
Interface: USB-C,VGA	OD: 4.2mm
Interface Technics: Gold-plated	Length: 0.15m
Resolution: 1080P@60HZ	Warranty: 1 Year
Conductor: Tinned-copper	Packing: PE Bag
Shell: ABS	



Note: All data are from Vention Lab.
Sizes above are manually measured. There might be slight tolerance



Note: Packing difference exists for different meters or batches.
The photo is for reference only

High Definition Image Quality





USB-C to VGA Converter

Technical Features	
Color	Black
Interface	USB-C Male/VGA Female
Connector Process	Gold-Plated
Casing	ABS
Transmission direction	USB-C to VGA
Resolution	1080p@60Hz

Length	Art.No.	EAN Code
0.15m	TDDBB	6922794746114



Package Contents
USB-C to VGA Converter x 1

Packaging Information	
Packing Dimension	22*15*/cm
Packing Weight	0.03kg
Carton Dimension	40*30*30cm
Carton Qty	200pcs
Carton Weight	7kg