

Package Display



Note: Packing difference exists for different meters or batches.
The photo is for reference only



4 in 1

USB-C Multifunctional Adapter



PD
fast charge



Data
transmission



Large screen
expansion



USB-C 4 in 1

Multiple device connections

Connect to A Large Screen TV


HDMI + VGA dual interfaces,
suitable for different display devices



Note: 1080P VGA/4K*2K HDMI
When HDMI and VGA output simultaneously, the resolution is 1080P@60Hz

VGA Connects to A Projector

More convenient for working/ speech



Transfer 1GB Movie in 5 Seconds

USB3.0 port



Note: All data are from Vention lab

Fully Charged within 1.5h for Macbook


87W fast charge, can quickly
supply power to PD-enabled devices



Note: All data are from Vention Lab.

Mobile Phone Changes Computer

HUAWEI P30 / Mate30 is connected to a large screen TV, charging at the same time, and connected to a U disk, making mobile working more convenient



Applicable Devices List

Suitable for computer and cellphone with full function USB-C ports

	Laptop	Mobile Phone
Apple	MacBook12" MacBook Pro2016/2017/2018 Mac Mini, MacBook Air 2018	SAMSUNG Note8 Note9 S8/S8+ S9/S9+S10/ S10+
Huawei	MateBook, MateBook X MateBook X Pro, MateBook E MateBook 13, MateBook 14	
Honor	MagicBook	Huawei Mate10, Mate10 Pro, Mate20, Mate20 Pro, Mate20 X Mate20 RS, P20 P20 Pro, Mate X P30, P30 Pro
Xiaomi	Air12.5"/ 13.3", Pro15.6" GTX version 15.6" Xiaomi game book 8 generation	
HP	Pavilion x2, Spectre 13 EliteBook Folio G1 Elite Book 1050 G1 Envy 13 Shadow Wizard 4 Pro	
ASUS	Ling Yao 3, Ling Yao 3 Pro U306, U321 U4100UN, U5100UQ, ROG	Honor Glory Note 10, Glory V20
Dell	XPS13/15, Latitude 5285, G+C22 G3/G5/G7, Lingyue 5000/7000	Microsoft Microsoft 950XL Microsoft 950
Lenovo	Xiaoxin Air 12", Yoga5 Pro Yoga6 Pro, Yoga 900 13" Miix 720 ThinkPad_X1, Carbon 2017/ Saver Y7000/Y7000P/Y9000K	LG G5, V300L
SAMSUNG	NoteBook series GalaxyBook series	Smartisan Nut R1, Nut Pro 2S
Google	ChromeBook Pixels PixelBook Pen	OPPO R17 Pro
Razer	Blade Stealth Spirit Blade Spirit Blade Sneak Edition	BlackShark BlackShark 2
Microsoft	Surface Book 2, Surface GO	iPad
HTC	HTC 10	Apple ipad Pro 2018 11"/12.9"
More USB-C models will be continuously updated		

Compatible with Multiple Systems





Good Heat Dissipation

Aluminum alloy + anodized dual process



Anti-fingerprint




Good heat dissipation



Wear-resistant and anti-corrosion

High Performance Chip

Multi-functional stable and
smooth use at the same time




Small and Portable

Easy to carry



Product Parameters

Brand: Vention	Shell: Aluminum Alloy + ABS
Name: USB-C to HDMI/VGA/ USB3.0/PD Converter	Chip: LT8712X
Model: TFAHB	Shielding: Aluminum Foil
Color: Grey	Jacket: PVC
Interface: USB-C, HDMI, VGA, USB3.0, PD	AWG: 30AWG+24AWG
Interface Technics: Nickel-plated	OD: 4.5mm
Transmission Speed: 5Gbps	Length: 0.15m
Conductor: Tinned Copper	Power: 87W
	Warranty: 1 Year
	Packing: Color Box



Note: All data are from Vention Lab.
Sizes above are manually measured. There might be slight tolerance.



4-in-1 USB-C Docking Station

Technical Features

Color	Gray
Interface	USB-C/HDMI/VGA/USB 3.0/PD
Connector Process	Nickel-Plated
Material	Aluminum alloy + ABS
Data transfer rates	5Gbps (USB 3.0)
Power supply	100W PD
Resolution	4K@30Hz (HDMI)/1080p@60Hz (VGA)/1080p@60Hz (HDMI + VGA)

Length	Art.No.	EAN Code
0.15m	TFAHB	6922794742567



Package Contents

4-in-1 USB-C Docking Station x 1

Packaging Information

Packing Dimension	17.25*9.25*2.75cm
Packing Weight	0.092kg
Carton Dimension	50*37*34cm
Carton Qty	100pcs
Carton Weight	10.2kg

www.vention.cn