

6 in 1

Multifunctional USB-C Hub

Support USB-C interface on
Ultrabook/MacBook



PD
100W



USB 3.0
interface



HDMI+
VGA



Driver
free

Widen Your Vision

Two video interfaces for
large screen extension






PD fast charge

Superior Charging Ability

Support PD 87W power supply, fast
charge for MacBook



Note: All data are from Vention Lab

SS 
USB3.0

USB Interface Extension

With 3 USB 3.0 ports, supports
simultaneous connection for mouse, keyboard,
flash disk and mobile HDD, etc.



Note: All data are from Vention Lab



HDMI interface

Compatible with Switch

Nintendo Switch connects to TV,
enjoy 4K visual experience




Note: the picture of Mario Kart is from Internet,
All rights reserved by the original author, all data are from Vention Lab



VGA Interface

Efficient Business Demonstration

Laptop connects to projector, support up to 1080P resolution and screen synchronization



Note: All data are from Vention Lab

HDMI+ VGA 2-in-1

Simultaneous output 1080P resolution
in two screens, convenient for officing and learning



Note: All data are from Vention Lab

Driver Free in Various Systems

Compatible with Mainstream OS



Windows10



Windows8



Windows7



Vista



Windows XP



Linux



Android



iOS

Exclusive to USB-C Interface

Laptop



MacBook



Lenovo



MateBook



HP



ASUS



Xiaomi



Dell



Other devices...

Tablet



iPad



MatePad



Surface



Other devices...

Mobile Phone



Huawei Mate40
Mate 40 Pro/20 X



Huawei P40
P40 Pro



Samsung S20/S10+
Note20



OPPO Reno 3
R17 Pro



Smartisan R1
Pro 2S



Honor V30
20 Pro



Other devices...



Part of Supported Models

Laptop

Apple	MacBook12", MacBook Pro2016/2017/2018/2019, Mac Mini, MacBook Air 2018/2019/2020
Huawei	MateBook, MateBook X, MateBook X Pro, MateBook X Pro 2019, MateBook E, MateBook E 2019, MateBook 13, MateBook 14
Honor	MagicBook, MagicBook 2019
Xiaomi	Air12.5"/ 13.3", Pro15.6", GTX version 15.6", Xiaomi game book 8 generation
HP	Pavilion x2, Spectre 13, EliteBook Folio G1, Elite Book1050 G1, Envy 13, Shadow Wizard 4 Pro
ASUS	Ling Yao 3, Ling Yao 3 Pro, Ling Yao X series, U306, U321, U4100UN, U5100UQ, ROG
Dell	XPS13/15, Latitude 5285, G+C22, G3/G5/G7, Lingyue 5000/7000
Lenovo	Xiaoxin Air 12", Yoga5 Pro, Yoga6 Pro, Yoga 900 13", Miix 720, ThinkPad_X1 Carbon 2017, Saver Y7000/Y7000P/Y9000K
SAMSUNG	NoteBook series, GalaxyBook series
Google	ChromeBook Pixels, PixelBook Pen
Razer	Blade Stealth Spirit Blade, Spirit Blade Sneak Edition
Microsoft	Surface Book 2, Surface GO

iPad

Apple	ipad Pro 2018/2020
Huawei	MatePad 10.4/10.8B235444;MatePad Pro, MediaPad M6
Microsoft	Surface Pro7, Surface Go/Go2, Surface Book 2


Mobile Phone

SAMSUNG	Note8, Note9, S8/S8+, S9/S9+, S10/S10+, S20, Note10, Note10+
Huawei	Mate10, Mate10 Pro, Mate20, Mate20 Pro, Mate20 X, Mate20 RS, P20, P20 Pro, Mate X, P30, P30 Pro, Mate30, Mate30 Pro, P40, P40Pro
OPPO	R17 Pro, Reno 10x Zoom
nut	R1、Pro25R1、Pro25

More USB-C models are continuously updated

High Performance Chips

Stable and fast operation



Note: The internal structure is a rendering. Please refer to the actual product.

More Details

Enhanced details for longer service time

1

Aluminum alloy shell
Good heat dissipation



2

Nickel-plated interface
Wear resistance

3

Small and portable
Easy to carry around



Product Parameters

Brand: Vention

Name: Multi-function USB-C 6-in-1 Docking Station

Model: TOIHB

Color: Gray

Interface: USB-C/HDMI/VGA/USB 3.0*3/PD

Interface Technics: Nickel-plated

Transmission Speed: 5Gbps

Resolution: 4K@30Hz(HDMI)/1080P@60Hz(VGA)/1080P@60Hz
(Simultaneous output)

Rated Power: PD 100W

Conductor: Tinned-copper

Shell: Aluminum Alloy

Shielding: Aluminum Foil+Metal Braided+GND

Jacket: TPE

AWG: 34AWG+26AWG

OD: 4.2mm

Length: 0.15m

Warranty: 1 Year

Packing: Color Box



Note: All data are from Vention Lab.

Sizes above are manually measured. There might be slight tolerance



Note: Packing difference exists for different meters or batches.
The photo is for reference only



6-in-1 USB-C Docking Station

Technical Features	
Color	Gray
Interface	USB-C/HDMI/VGA/USB 3.0 x 3/PD
Connector Process	Nickel-Plated
Material	Aluminum alloy + ABS
Data transfer rates	5Gbps (USB 3.0)
Power supply	100W PD
Resolution	4K@30Hz (HDMI)/1080p@60Hz (VGA)/1080p@60Hz (HDMI + VGA)

Length	Art.No.	EAN Code
0.15m	TOIHB	6922794754751



Package Contents
6-in-1 USB-C Docking Station x 1

Packaging Information	
Packing Dimension	17.25*9.25*2.75cm
Packing Weight	0.121kg
Carton Dimension	40*30*30cm
Carton Qty	60pcs
Carton Weight	8.26kg