

9-in-1 USB-C Docking Station

Seamlessly Expand Your Computer's Capabilities.



4K@60Hz
3D Visual Effects

Transfer Files
in Seconds


1000Mbps
Gigabit Ethernet

PD100W
Charge & Use
Simultaneously

SD/TF
Card Slots

3.5mm TRRS
Microphone/Audio

9 Ports Expansion



Ultra HD 4K Visual Experience

4K@60Hz

3D Video

HDR



4K@60Hz

VS



4K@30Hz

Note: The resolution and refresh rate are determined by the performance of your devices. If you intend to display 4K content, please make sure that both your input and output devices can support 4K. All data are from Vention Lab.

Transfer Files in Seconds at 5Gbps

5 Gbps
USB 3.2 Gen 1-C

5 Gbps
USB 3.0 * 2



5Gbps



Keyboard



Mouse



External
Hard Drive



USB Drive

1000Mbps Faster and More Stable than Wi-Fi



Smooth Gaming
Experience



Fluid Video
Playing



Download
Files Faster



Stable
Transmission



Note: All data are from Vention Lab.

PD 100W Quick Charging




Note: All data are from Vention Lab.

Efficient SD/TF Card Slots




Note: Compatible Memory Cards:
Micro SD/Micro SDHC/Micro SDXC/SDHC/SDXC.
All data are from Vention Lab.

3.5mm Audio Combo Jack



Note: Support OMTP & CTIA earphones.

Cutting-edge Chip



Note: The internal structure is a rendering.
Please refer to the actual product.

Superior Aluminum Alloy Shell



Compact & Portable



Suitable for Various Scenarios

Connect Phone

Expand your workplace



Connect Tablet

E-learning helper



Connect Switch

Immersive gaming experience




Note: You need to connect both the HDMI and power ports simultaneously.

Universal Compatibility Plug-and-Play

Devices



HDMI Port



Operating Systems



Compatibility List

Laptop

Apple	MacBook 12", MacBook Air 2018/2019/2020/2021 M1/M2, MacBook Pro 2016/2017/2018/2019/2020 2021/M1/M1 Pro/M1 Max/M2
Huawei	MateBook X/X Pro 19/20/21/22, MateBook E/E 2019 MateBook 13/13s/14/14s
Honor	MagicBook Pro 2019/2020, MagicBook 16/16 Pro
Xiaomi	Air12.5/13.3", Pro15.6", RedmiBookPro15 RedmiBook Pro 14, RedmiG, Xiaomi Pro14/15
HP	Pavilion x2, Spectre 13, EliteBook Folio G1, EliteBook 1050 G1, Envy 13, Omen 4/5/6/7, ProBook, EliteBook
ASUS	ZenBook 3/3 Pro, ZenBook X, U4100UN/U5100UQ ROG series, ProArt 16, TUF series
Dell	XPS13/15/17, G3/G5/G7/G15, Inspiron 5000/7000 Inspiron16 Plus, Alienware series
Lenovo	YOGA 6 Pro, ThinkPad X1 Carbon, Y7000/Y7000P Y9000K
Google	Pixelbook
Razer	Blade/Blade Stealth
Microsoft	Surface Book 2, Surface GO

Mobile Phone

Samsung	Note8/9/20/20U, S8/S8+/S9/S9+/S10/S10+/S20/S20+ S21/S21U/FOLD3/FLIP3/S22/S22 Ultra
Huawei	Mate 10/10 Pro/20/20 Pro/20 X/20 RS/30/30 Pro Mate 30E Pro/Mate 30 RS/40/Mate 40E/40 Pro/40 Pro+ Mate 40 RS/Mate X2/Mate Xs, P20/P20 Pro/P30/P30 Pro P40/P40 Pro/P50/P50 Pro/P50 Pocket
Smartisan	Nut R1/Pro 2S/R2
BlackShark	BlackShark 2/3/4/4 Pro/4S Pro/5/5 RS/5 Pro
OnePlus	7 Pro/8/8 Pro/9/9 Pro/10Pro
Asus	7 Pro/8/8 Pro/9/9 Pro/10Pro
Lenovo	Y90

Tablet

Apple	iPad Pro 2018/2020/2021, iPad Air 4 and Newer Model
Huawei	MatePad Pro 12.6" 2021, MatePad Pro 10.8" 2021 MatePad 11 2021
Microsoft	Surface Pro 7, Surface Pro X, Surface Go 2
Lenovo	Xiaoxin Pad2021/2022, Xiaoxin Pad Pro2021/2022 Yoga Pad Pro, Legion Y700

Game Console

Nintendo	Switch
----------	--------

Tips: Only full-featured USB-C devices can handle data to its full function. Non-full-featured USB-C devices only support some extended functions.

Specifications

Brand	Vention
Name	9-in-1 USB-C Docking Station
Model	TQM
Color	Gray
Output Interface	
HDMI	4K@60Hz
USB 3.2 Gen 1-C	5Gbps
2 x USB 3.0	5Gbps
Ethernet Port	Gigabit RJ45
Card Slot Type	SD/TF 1-LUN (Dual Cards Single Read)
Slot Rate Standard	USB 2.0
3.5mm TRRS	Connects headphones, microphone, speakers and etc.
PD Charge	100W (Max)
Electroplating Process	Nickel-Plated
Conductor	Tinned Copper
Shell	Aluminum Alloy
Length	0.15 m (Net cable length)
Warranty	1 Year
Packing	Color Box



Note: All data are from Vention Lab.
Sizes above are manually measured.
There might be slight tolerance.

Packaging Display



Note: Packing difference exists for different meters or batches.
The photo is for reference only.



9-in-1 USB-C Docking Station

Technical Features		
Color	Gray	
Interface	USB-C/HDMI/USB 3.2 Gen 1 Type-C/USB 3.0 x 2/RJ45/SD/TF/3.5mm TRRS/PD	
Connector Process	Nickel-Plated	
Material	Aluminum alloy + ABS	
Data transfer rates	5Gbps (USB 3.2 Gen 1 Type-C/USB 3.0)	
Power supply	100W PD	
Resolution	4K@60Hz	
Transmission rate	10/100/1000Mbps	
Card slot type	SD/TF 1-LUN (Read/Write only one card at a time)	
Card slot speed	USB 2.0	
Compatible audio standard	OMTP&CTIA	
Length	Art.No.	EAN Code
0.15m	TQMHB	6922794775138
Package Contents		
9-in-1 USB-C Docking Station x 1		
Packaging Information		
Packing Dimension	19*9.5*2cm	
Packing Weight	0.114kg	
Carton Dimension	48*29*30cm	
Carton Qty	90pcs	
Carton Weight	11.26kg	

