

44428278	DATA SHEET	
Valid from: 30.10.2024	EPIC® SOLAR 4 GEN2 FEMALE CONNECTOR	

Description

- Low contact-resistance for efficient power transmission
- Crimp connection for field mounting

General Characteristics

Series	EPIC® SOLAR 4 GEN2
Rated voltage	1500 V DC
Rated impulse voltage	16 kV
Contact resistance	< 0.5 mOhm
Flammability Class	V-0
Protection	IP 65 / IP 68, (1m/ 1h)
Protection class	II
Temperature range	-40°C to +85°C



Materials and Surfaces

Insulating Body	Polycarbonate
Cap nut	Polyamid
Contact	Copper alloy, tin plated


Article Number	Article	Description	Cross section [mm²]	Cable clamping range [mm]	Rated current [A]
EPIC® SOLAR 4 GEN2, female field-mountable, inclusive contacts					
44428278	EPIC® SOLAR 4 GEN2 F 4-6 5.2-7.0mm	female connector incl. contacts 4-6mm² (100 pcs)	4 - 6	5,2 - 7,0	50
381166811	EPIC® SOLAR 4 GEN2 F 4-6 5.2-7.0mm	female connector incl. contacts 4-6mm² (10 pcs)	4 - 6	5,2 - 7,0	50
44428269	EPIC® SOLAR 4 GEN2 F 10mm²	female connector incl. contacts 10mm² (100 pcs)	10	7,0 - 7,4	55
EPIC® SOLAR 4 GEN2, female field-mountable, exclusive contacts					
44428271	EPIC SOLAR 4 GEN2 F 5.2-7.0mm	female connector without contacts (100 pcs)	-	5,2 - 7,0	50
381166462	EPIC SOLAR 4 GEN2 F 5.2-7.0mm	female connector without contacts (700 pcs)	-	5,2 - 7,0	50
EPIC® SOLAR 4 GEN2, female contacts					
44428273	EPIC SOLAR 4 GEN2 PIN F 4-6mm²	female contacts on reel (2500 pcs)	4 - 6	-	-

Article Number	Cross section [mm²]	Max. permitted current [A]
44428278	4	40
	6	50
381166811	4	40
	6	50

Creator: TODV1/BU EPIC Released: VACH1/BU EPIC	Document: DB44428278EN Version: 02	Page 1 of 2
---	---------------------------------------	-------------

44428278	DATA SHEET	
Valid from: 30.10.2024	EPIC® SOLAR 4 GEN2 FEMALE CONNECTOR	

Technical Drawings



Solar Energy



UV-resistant



Waterproof



Info

4 mm connector system with double hook
Field-mountable solar connector

Application range

Photovoltaic plants
Crystalline and thin-film constructions
Solartracker

Product features

TÜV SÜD certified
Inclusive contacts

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: TODV1/BU EPIC Released: VACH1/BU EPIC	Document: DB44428278EN Version: 02	Page 2 of 2
---	---------------------------------------	-------------