

Specifications

Eaton FWC-6A10F

Eaton Bussmann series FWC high speed cylindrical fuse, 500 Vac/dc (35-800A only), 6A, 200 kAIC Vac, 50 kAIC at 700 Vdc, Non Indicating, High speed fuse, Ferrule end X ferrule end

General specifications

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWC-6A10F
UPC	051712796415
EAN	5027590499415
PRODUCT LENGTH/DEPTH	38 mm
PRODUCT HEIGHT	11 mm
PRODUCT WIDTH	11 mm
PRODUCT WEIGHT	9 g
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized CSA Certified
GLOBAL CATALOG	FWC-6A10F



Powering Business Worldwide

Product specifications

AMPERAGE RATING	6 A
ACCESSORIES	- BMM Fuse block - CHM modular fuse holder
BREAKING CAPACITY	200 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
FUSE INDICATOR	Other
RELEASE CHARACTERISTIC	Other
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	10 x 38 mm
RATED VOLTAGE AC	600 V
RATED VOLTAGE DC	700 V
CLASS	Class aR
CLEARING (I ₂ T)	30
WATT LOSSES	1.5 W
FUSE SHAPE	Cylindrical
PRE ARC (I ₂ T)	4
INTERRUPT RATING	200 kAIC Vac
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	10 x 38 mm 10 mm x 38 mm
MATERIAL	Ceramic
PACKAGING TYPE	Standard
VOLTAGE RATING	600 V
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWC-A10F
BREAKING CAPACITY AT NOMINAL VOLTAGE, AC	200 kA
BREAKING CAPACITY AT NOMINAL VOLTAGE, DC	10 kA

Resources

CATALOGS	eaton-bussmann-series-iec-high-speed-fuses-catalogue-ca135001en-en-gb.pdf Bussmann series complete full line catalog no. 1007
DECLARATIONS OF CONFORMITY	DA-DC-00005071.pdf DA-DC-00005070.pdf
INSTALLATION VIDEOS	Eaton's Switch disconnectors and Bussmann series fuses for MOEM Applications (brightcove.net)
MCAD MODEL	eaton-hs-round-body-fuses-mcad-3d-models-fwc-1-32a-10f.stp
TECHNICAL DATA SHEETS	720011 FWC

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

