





















Chisels		GT90		GT120	
GT4	GT6/GTC	GT4 - Tip	GT6 - Tip	GTC - Cartridge	Dimension A x Length
		GT4-CH0010S	GT6-CH0010S	GTC-CH0010S	1.0 mm x 10.0 mm
		GT4-CH0014S	GT6-CH0014S	GTC-CH0014S	1.4 mm x 10.0 mm
		GT4-CH0018S	GT6-CH0018S	GTC-CH0018S	1.8 mm x 10.0 mm
		GT4-CH0025S	GT6-CH0025S	GTC-CH0025S	2.5 mm x 10.0 mm
		GT4-CH0032S	GT6-CH0032S	GTC-CH0032S	3.2 mm x 10.0 mm
		GT4-CH0040S	GT6-CH0040S	GTC-CH0040S	4.0 mm x 10.0 mm
			GT6-CH0050S	GTC-CH0050S	5.0 mm x 10.0 mm
			GT6-CH0060S	GTC-CH0060S	6.0 mm x 10.0 mm
		GT4-CH0010P	GT6-CH0010P	GTC-CH0010P	Power, 1.0 mm x 10.0 mm
		GT4-CH0014P	GT6-CH0014P	GTC-CH0014P	Power, 1.4 mm x 10.0 mm
		GT4-CH0018P	GT6-CH0018P	GTC-CH0018P	Power, 1.8 mm x 10.0 mm
		GT4-CH0025P	GT6-CH0025P	GTC-CH0025P	Power, 2.5 mm x 10.0 mm
		GT4-CH0032P	GT6-CH0032P	GTC-CH0032P	Power, 3.2 mm x 10.0 mm
		GT4-CH0040P	GT6-CH0040P	GTC-CH0040P	Power, 4.0 mm x 10.0 mm
			GT6-CH0050P	GTC-CH0050P	Power, 5.0 mm x 10.0 mm
			GT6-CH0060S	GTC-CH0060P	Power, 6.0 mm x 10.0 mm
				GTC-CH0070P	Power, 7.0 mm x 10.0 mm
Conicals		GT90	GT120		
		GT4-CN0005P	GT6-CN0005P	GTC-CN0005P	Power, (Ø x L) 0.5 mm x 6.0 mm
		GT4-CN0010P	GT6-CN0010P	GTC-CN0010P	Power, (Ø x L) 1.0 mm x 6.0 mm
		GT4-CN0005S	GT6-CN0005S	GTC-CN0005S	(Ø x L) 0.5 mm x 10.0 mm
		GT4-CN0005A	GT6-CN0005A	GTC-CN0005A	Access, (Ø x L) 0.5 mm x 14.0 mm
		GT4-CN0010A	GT6-CN0010A	GTC-CN0010A	Access, (Ø x L) 1.0 mm x 14.0 mm
		GT4-CN1502A	GT6-CN1502A	GTC-CN1502A	Sharp, (Ø x L) 0.2 mm x 15.0 mm
		GT4-CN1505A	GT6-CN1505A	GTC-CN1505A	Sharp, (Ø x L) 0.5 mm x 15.0 mm
		GT4-CN2213R	GT6-CN2213R	GTC-CN2213R	Bent, Reach, (Ø x L) 1.3 mm x 22.0 mm
		GT4-CN1608R	GT6-CN1608R	GTC-CN1608R	Bent, Access, (Ø x L) 0.8 mm x 16.0 mm
		GT4-CN0002R	GT6-CN0002R	GTC-CN0002R	Bent, (Ø x L) 0.2 mm x 8.0 mm
		GT4-CN0004R	GT6-CN0004R	GTC-CN0004R	Bent, (Ø x L) 0.4 mm x 8.0 mm
		GT4-CN1505R	GT6-CN1505R	GTC-CN1505R	Bent, Reach (Ø x L) 0.5 mm x 15.0 mm
		GT4-CN0002S	--	--	Sharp (Ø x L) 0.2 mm x 10.0 mm

For our complete selection of tips & cartridges, visit www.metcal.com