










ACCESSORIES




Contacts, crimping systems, accessories > [Contacts](#)





Type	RBC 162/1 Ag	RBCB 162/1 Ag
Order No.	733 383-021	733 385-001
		
	rolled engaging crimp contact (socket), BO crimp	rolled engaging crimp contact (socket), BO crimp
Product description Conductor size	0.14 mm ² to 0.5 mm ²	0.14 mm ² to 0.5 mm ²
Drawing		
Technical data Type of termination Pin dimensions	crimping 1.6 mm	crimping 1.6 mm
Material Contact material Contact surface material	Cu Zn Ag	Cu Zn Ag
Packing unit Packaging unit	100 pieces	2000 pieces coiled
Scope of delivery and accessories Accessories to order separately	suitable for NR-series and ST-series (5 pole) connectors suitable crimping tool: crimping pliers XZC 0701 suitable ejection tool: XWA 164	suitable for NR-series and ST-series (5 pole) connectors suitable ejection tool: XWA 164

RBC 162 Ag	RBCB 162 Ag	RBCB 162 Ag
731 724-221	731 726-202	731 726-201
		
rolled engaging crimp contact (socket), BO crimp	rolled engaging crimp contact (socket), BO crimp	rolled engaging crimp contact (socket), BO crimp
0.5 mm ² to 1.5 mm ²	0.5 mm ² to 1.5 mm ²	0.5 mm ² to 1.5 mm ²
		
crimping 1.6 mm	crimping 1.6 mm	crimping 1.6 mm
Cu Zn Ag	Cu Zn Ag	Cu Zn Ag
100 pieces	200 pieces coiled	2000 pieces coiled
suitable for NR-series and ST-series (5 pole) connectors suitable crimping tool: crimping pliers XZC 0701 suitable ejection tool: XWA 164	suitable for NR-series and ST-series (5 pole) connectors suitable ejection tool: XWA 164	suitable for NR-series and ST-series (5 pole) connectors suitable ejection tool: XWA 164

ACCESSORIES


Contacts, crimping systems, accessories > Contacts

Type	RSC 162/1 Ag	RSC 162 Ag
Order No.	733 384-021	731 725-021
		
	rolled engaging crimp contact (pin contact), BO crimp	rolled engaging crimp contact (pin contact), BO crimp
Product description		
Conductor size	0.14 mm ² to 0.5 mm ²	0.5 mm ² to 1.5 mm ²
Drawing		
Technical data		
Type of termination	crimping	crimping
Pin dimensions	1.6 mm	1.6 mm
Material		
Contact material	Cu Zn	Cu Zn
Contact surface material	Ag	Ag
Packing unit		
Packaging unit	100 pieces	100 pieces
Scope of delivery and accessories		
Accessories to order separately	suitable for NR-series and ST-series (5 pole) connectors suitable crimping tool: crimping pliers XZC 0701 suitable ejection tool: XWA 164	suitable for NR-series and ST-series (5 pole) connectors suitable crimping tool: crimping pliers XZC 0701 suitable ejection tool: XWA 164

RSCB 162 Ag	RMC 280	RMC 480
731 727-001	731 991-021	731 470-021
		
rolled engaging crimp contact (pin contact), BO crimp	engaging crimp contact (blade contact), suitable for G-series connectors	flat crimping contact (blade contact), according to connector of GSC-Series
0.5 mm ² to 1.5 mm ²	0.5 mm ² to 1 mm ² (BO crimp)	0.5 mm ² to 1.5 mm ² (B crimps)
		
crimping 1.6 mm		
Cu Zn Ag	CuZn Sn	CuZn Sn
2000 pieces coiled	100 pieces	100 pieces
suitable for NR-series and ST-series (5 pole) connectors suitable ejection tool: XWA 164	suitable for G-series; suitable crimping tool (pliers): XZC 0702, Order-no. 932 507-003	suitable for GDM-series; suitable crimping tool (pliers): XZC 0702, Order No. 932 507-003

ACCESSORIES

Contacts, crimping systems, accessories > **Contacts**


Type		RMCB 480
Order No.		731 468-001
		
		Flat crimping contact (blade contact), according to connector of GSC-Series
Product description		
Conductor size		0.5 mm ² to 1.5 mm ² (B crimps)
Drawing		
Technical data		
Type of termination		
Pin dimensions		
Material		
Contact material		CuZn
Contact surface material		Sn
Packing unit		
Packaging unit		3000 pieces coiled
Scope of delivery and accessories		
Accessories to order separately		suitable crimping tool (pliers): XZC 0702, Order No. 932 507-003

ACCESSORIES

Contacts, crimping systems, accessories > Crimping tools

Type	XZC 0701	XZC 0702
Order No.	932 507-002	932 507-003
	 crimping tool for NR-series and ST-series contacts, color: blue	 crimping tool for GDM-series contacts and G-series contacts, color: red
Product description Conductor size	for contacts: RBC 162/1, 0.14 mm ² to 0.25 mm ² , Profil I; RSC 162/1, 0.14 mm ² to 0.25 mm ² , Profil I; RBC 162, 0.5 mm ² to 1.5 mm ² , Profil II; RSC 162, 0.5 mm ² to 1.5 mm ² , Profil II; RBC 162/1, 0.32 mm ² to 0.5 mm ² , Profil III	for contacts: RMC 280, 0.5 mm ² to 1 mm ² , Profil I; order no.: 731 991-021; RMC 480, 0.5 mm ² bis 1.5 mm ² , Profil II, order no.: 731 470-021
Technical data Type of termination	crimping	crimping
Packing unit Packaging unit	1 pieces	1 pieces
Scope of delivery and accessories Scope of delivery	1 crimping pliers	1 crimping pliers

Contacts, crimping systems, accessories > Ejector tools

Type	XWA 164
Order No.	931 812-001
	 ejection tool for NR-series and ST-series contacts (5 pole) crimp contacts 1.6 mm (diameter)
Packing unit Packaging unit	1 pieces