


UT-CK01测试套件

UT-CK01是优利德公司射频类产品的测试辅助套件。本说明列出该套件所包含的元件清单。
套件包的示意图如下图所示：



编号	名称	数量	型号	规格	特征
1	N-SMA线缆	1	UT-W02-6GHz	外径5.3mm/0.7米	黑色DC-6G VSWR≤1.25:1@6GHz IL≤1.8dB@6GHz
2	N-N线缆	1	UT-W01-6GHz	外径5.3mm/0.7米	黑色DC-6G VSWR≤1.25:1@6GHz IL≤1.8dB@6GHz
3	N-SMA转接器	2	UT-C01-6GHz	- - -	DC-6GHz VSWR≤1.15:1@6GHz 1L≤0.2dB@6GHz
4	N-BNC转接器	2	UT-C02-6GHz	- - -	DC-4GHz VSWR≤1.15:1@4GHz 1L≤0.2dB@4GHz
5	天线	2	UTS-T01	110*10mm	工作频率2400MHz-2500MHz,增益>2dBi
6	天线	2	UTS-T02	110*10mm	工作频率824-960MHz/1710-1990MHz/增益>2dBi
7	配件包	1	UTS-BAG01	230*180*45mm	UTS3000B系列配件布包cloth Bag 黑色

线缆指标（典型值）



UT-CK01 Test Kit

UT-CK01 is UNI-T test auxiliary kit for radio frequency product. This sheet is listed the component of test kit. The test kit pouch is shown as the following figure.



No	Name	Quantity	Model	Specification	Characteristic
1	N-SMA cable	1	UT-W02-6GHz	Outer diameter 5.3mm/0.7 meter	Black DC-6G VSWR ≤1.25:1@6GHz 1L ≤1.8dB@6GHz
2	N-N cable	1	UT-W01-6GHz	Outer diameter 5.3mm/0.7 meter	Black DC-6G VSWR ≤ 1.25:1@6GHz 1L ≤ 1.8dB@6GHz
3	N-SMA adaptor	2	UT-C01-6GHz	- - -	DC-6GHz VSWR ≤ 1.15:1@6GHz 1L≤ 0.2dB@6GHz
4	N-BNC adaptor	2	UT-C02-6GHz	- - -	DC-4GHz VSWR ≤ 1.15:1@4GHz 1L≤ 0.2dB@4GHz
5	Antennae	2	UTS-T01	110*10mm	Working frequency 2400MHz-2500MHz, Gain < 2dBi
6	Antennae	2	UTS-T02	110*10mm	Working frequency 824-960MHz/Gain > 2dBi
7	Pouch	1	UTS-BAG01	230*180*45mm	UTS3000B series black pouch

Cable Index (typical value)

