

DIGITUS USB 3.0 dual SATA HDD docking station 2.5"/3.5

DA-71540-2
EAN 4016032498414



SATA Docking Station USB 3.0, 2-port, 2.5"/3.5" SSD/HDD, clone function

Experience a convenient and powerful solution for your storage needs with the DN-71540-2 Dual Bay HDD Clone Station. This versatile device makes it easy to read, clone and back up your data from 2.5" and 3.5" hard drives and other external storage devices. With USB 3.0 high-speed connectivity and support for SATA3 hard drives, the Clone Station offers impressive transfer speeds and reliability.

The Dual Bay HDD Clone Station with USB 3.0 is ideal for quick and easy data backup, migration and management. It offers advanced features and user-friendly design for your storage needs

- Connections: USB 3.0
- Compatibility: 2.5" and 3.5" SATA HDDs and SSDs

- Status indicators: LED lights for operating and cloning status
- Maximum capacity: Supports hard disks with large storage capacity
- Simultaneous reading: Can read and write to two hard disks simultaneously
- SATA support: SATA3 for fast data transfer
- Plug-and-play: no additional software or drivers required
- Dimensions: Compact size for easy transportation and storage
- Operating system compatibility: Windows, macOS, Linux

Package contents

- Dual Bay HDD Clone Station
- USB 3.0 cable
- Power supply unit
- User manual

Logistics

	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm ³
Packaging Unit Carton	20	1.50	40.00	40.00	35.00	56,000.00
Packaging Unit Inside	1	0.08	0.00	0.00	0.00	0.00
Packaging Unit Single	1	0.08	15.00	15.50	12.50	2,906.25
Net single without Packaging	1	-0.23	15.00	15.50	12.50	2,906.25

More images:





Safety notes

- Overloading can lead to overheating and damage to the appliance or the connected peripherals.
- If necessary, use an external power supply to ensure stable performance.
- If devices such as external hard disks or printers that require a high power consumption are connected, the device should be used with an external power supply. Otherwise, the device could be overloaded or functional problems could occur.
- Do not expose the device to rain, moisture, vapors or liquids.
- Do not insert any objects into the device.
- Do not attempt to repair the unit or open the housing without authorization. You risk an electric shock!
- Ensure adequate ventilation to prevent damage due to overheating.
- Dust, moisture, vapors and strong cleaning agents or solvents can cause damage to the device.
- Disconnect the appliance from the power supply and the connected devices before cleaning.
- Clean the device with a dust-free cloth.

EU responsible person

EU based economic operator ensuring the product complies with the required regulations.

ASSMANN Electronic GmbH
Auf dem Schöffel 3
Lüdenscheid, Germany
<https://www.assmann.com>
info@assmann.com