



Qoltec Cable Patchcord FTP | CAT5e | 2 x RJ-45 | 2m | High speed | Gold | Shielded

Product code: 54527

Qoltec Patchcord FTP Cat5e cable with a length of 2m, terminated with two gold-plated RJ-45 type connectors in a sealed sheath. Used for Ethernet connections such as in offices, data centers, or even home computer networks. Allows data transfer at speeds of up to 10Gb/s. The cable have an additional protective shield.


HIGH-SPEED TRANSMISSION AND STABLE CONNECTION



Quickly transfer data at speeds of up to 10 G/s

Qoltec's FTP CAT5e cable is a 2m shielded cable designed to support data transfer speeds of up to 10 Gb/s on Ethernet networks. Suitable for high-speed data transfer applications such as file transfer, video streaming, video conferencing requiring high network bandwidth . Particularly used in data communication networks, computer networks, power transmission, data transmission and monitoring systems.

ACHIEVE A NEW LEVEL OF NETWORK EFFICIENCY



Eight pairs of twisted wires, gold-plated terminals covered with a plastic sheath

- It consists of eight twisted pairs of wires,
- The cable sheath is made of PVC,
- Each pair of wires is **covered with an insulating layer** to protect against interference,
- **Shielded** - does not have an additional protective screen,
- At both ends of the cable are **RJ-45 connectors** - standard modular connector equipped with **8 pins**,
- **The ends of the cables are gold-plated for better signal conduction**,
- The ends of the RJ-45 connectors are **covered with a plastic shield**, which helps protect the ends from mechanical damage and maintains a **stable connection**,
- **High quality** construction confirmed by warranty.

CONFIDENCE CONFIRMED BY A WARRANTY



Quality Guarantee - Your Secure Connection

Do you care about the high quality of the product you are buying? Our solutions will meet your expectations. **Product is covered by a 24-month guarantee valid from the date of purchase.**

TECHNICAL DATA

Producer	Qoltec
Type patchcord	Shielded
Category	CAT5e
Class	FTP
Type connectors	2 x RJ-45
Transmission speed	10Gb/s
Coating	PCV
Conductor diameter	0.405 mm
Conductor cross-sectional area	0,129 mm
AWG cross section	26AWG
Cross-section of a vein	CU
Cable length	2m
Colour	Grey
Additional information	Gold-plated plugs
Package	Blister
Package contents	1 x Cable Patchcord
Package depth / length [mm]	246
Package width [mm]	205
Package height [mm]	10
Net weight [kg]	0.079
Gross weight [kg]	0.083
Warranty	24 month
EAN code	5901878545271