


1 HOODED SWEATSHIRT

260 g/m²







Kat. I
Cat. I



MATERIAL: 100% polyester, 260 g/m². Reflective tape on shoulders and sleeves. Contrast inserts made of yellow fabric. 2 pockets. Zipper. Practical hood with lining and width adjustment. Cuffs and jacket bottom with a drawstring.


Code	Size	H [cm]	C [cm]	
L4015101	S	158-164	84-88	20
L4015102	M	164-170	94-100	20
L4015103	L	170-176	100-106	20
L4015104	XL	176-182	106-112	20
L4015105	2XL	182-188	112-116	20
L4015106	3XL	188-194	116-122	20



2 PADDED SWEATSHIRT

210 g/m²








Kat. I
Cat. I



MATERIAL: Coating: 100% polyester 210 g/m², Insulation: 160 g/m². 2 pockets with a zipper. Zipper. Zipper cover. Quilted body provides comfort on cool days. Flexible thumbhole cuffs.

Size	Code	Colour	Code	Colour	Code	Colour	Code	Colour	Code	Colour	H [cm]	C [cm]	
S	L4012201		L4012301		L4013201		L4013301		L4014301		158-164	84-88	20
M	L4012202		L4012302		L4013202		L4013302		L4014302		164-170	92-96	20
L	L4012203		L4012303		L4013203		L4013303		L4014303		170-176	100-104	20
XL	L4012204		L4012304		L4013204		L4013304		L4014304		176-182	108-112	20
2XL	L4012205		L4012305		L4013205		L4013305		L4014305		182-188	116-120	20
3XL	L4012206		L4012306		L4013206		L4013306		L4014306		188-194	126-130	20


1 HOODED SWEATSHIRT WITH ZIP

210
g/m²Kat. I
Cat. I

MATERIAL: 100% polyester 210 g/m². 3 zipped pockets. Zipper. Zipper cover. Practical, cotton-lined hood with strings for adjustment. Flexible thumbhole cuffs.

Size	Code	Colour	Code	Colour	Code	Colour	Code	Colour	H [cm]	C [cm]	
S	L4013401		L4013501		L4014101		L4014201		158-164	84-88	20
M	L4013402		L4013502		L4014102		L4014202		164-170	92-96	20
L	L4013403		L4013503		L4014103		L4014203		170-176	100-104	20
XL	L4013404		L4013504		L4014104		L4014204		176-182	108-112	20
2XL	L4013405		L4013505		L4014105		L4014205		182-188	116-120	20
3XL	L4013406		L4013506		L4014106		L4014206		188-194	126-130	20


2 SWEATSHIRT

260
g/m²Kat. I
Cat. I

MATERIAL: 100% polyester 260 g/m². 3 zipped pockets. Cuffs and jacket bottom finished with a drawstring. Made of 3D structure fabric.

Rozmiar	Kod	Kolor	Kod	Kolor	H [cm]	C [cm]	
S	L4015201		L4015301		173-176	90-96	20
M	L4015202		L4015302		176-179	96-102	20
L	L4015203		L4015303		179-182	102-108	20
XL	L4015204		L4015304		182-184	108-114	20
2XL	L4015205		L4015305		184-186	114-120	20
3XL	L4015206		L4015306		186-188	120-126	20

3 HOODED SWEATSHIRT WITH ZIP

280
g/m²Kat. I
Cat. I

MATERIAL: 60% cotton, 38% polyester, 2% elastane, 280 g/m². 2 pockets. Zipper. Practical hood with lining and width adjustment. Cuffs and jacket bottom with a thick drawstring. Fashionable and interesting design.


Code	Size	H [cm]	C [cm]	
L4014001	S	158-164	84-88	20
L4014002	M	164-170	94-100	20
L4014003	L	170-176	100-106	20
L4014004	XL	176-182	106-112	20
L4014005	2XL	182-188	112-116	20
L4014006	3XL	188-194	116-122	20

1 HOODED SWEATSHIRT

320
g/m²



Kat. I
Cat. I



MATERIAL: 60% cotton, 30% polyester, 10% viscose, 320 g/m². Made of French terry: one of its sides flat, the other one with cross loops, which can absorb large amounts of water, providing comfort of use. Ring-spun cotton, characterised by high density, combined with softness and smoothness, guarantees durability and abrasion resistance. Big, front kangaroo pocket. Practical, lined hood with strings for adjustment. Cuffs and jacket bottom finished with a drawstring.


Size	Code	Colour	Code	Colour	H [cm]	C [cm]	
S	L4013001		L4013101		158-164	84-88	20
M	L4013002		L4013102		164-170	92-96	20
L	L4013003		L4013103		170-176	100-104	20
XL	L4013004		L4013104		176-182	108-112	20
2XL	L4013005		L4013105		182-188	116-120	20
3XL	L4013006		L4013106		188-194	126-130	20

2 HOODED SWEATSHIRT

320
g/m²



Kat. I
Cat. I



MATERIAL: 60% cotton, 35% polyester, 5% viscose, 320 g/m², anti-pilling and padded inside. Ring-spun cotton, characterised by high density, combined with softness and smoothness, guarantees strength and abrasion resistance as well as provide comfort of wearing. Big, front kangaroo pocket. Practical, cotton-lined hood with strings for adjustment provides perfect protection form cold and wind. Cuffs and jacket bottom finished with a drawstring.


Size	Code	Colour	Code	Colour	H [cm]	C [cm]	
S	L4010701		L4010401		158-164	84-88	20
M	L4010702		L4010402		164-170	92-96	20
L	L4010703		L4010403		170-176	100-104	20
XL	L4010704		L4010404		176-182	108-112	20
2XL	L4010705		L4010405		182-188	116-120	20
3XL	L4010706		L4010406		188-194	126-130	20

3 HOODED SWEATSHIRT WITH ZIP

320
g/m²



Kat. I
Cat. I



MATERIAL: 60% cotton, 35% polyester, 5% viscose, 320 g/m², anti-pilling and padded inside. Ring-spun cotton, characterised by high density, combined with softness and smoothness, guarantees strength and abrasion resistance as well as provide comfort of wearing. 2 pockets. Zipper. Practical, cotton-lined hood with strings for adjustment and high collar provide perfect protection from cold and wind. Cuffs and jacket bottom finished with a drawstring.


Size	Code	Colour	Code	Colour	H [cm]	C [cm]	
S	L4011201		L4010801		158-164	84-88	20
M	L4011202		L4010802		164-170	92-96	20
L	L4011203		L4010803		170-176	100-104	20
XL	L4011204		L4010804		176-182	108-112	20
2XL	L4011205		L4010805		182-188	116-120	20
3XL	L4011206		L4010806		188-194	126-130	20

4 SWEATSHIRT

320
g/m²




Kat. I
Cat. I



MATERIAL: 60% cotton, 30% polyester, 10% viscose, 320 g/m². Made of French terry: one of its sides flat, the other one with cross loops, which can absorb large amounts of water, providing comfort of use. Ring-spun cotton, characterised by high density, combined with softness and smoothness, guarantees durability and abrasion resistance. Cuffs and jacket bottom finished with a drawstring.

Size	Code	Colour	Code	Colour	H [cm]	C [cm]	
S	L4012801		L4012901		158-164	84-88	20
M	L4012802		L4012902		164-170	92-96	20
L	L4012803		L4012903		170-176	100-104	20
XL	L4012804		L4012904		176-182	108-112	20
2XL	L4012805		L4012905		182-188	116-120	20
3XL	L4012806		L4012906		188-194	126-130	20

1 SWEATSHIRT

320
g/m²Kat. I
Cat. I

MATERIAL: 60% cotton, 35% polyester, 5% viscose, 320 g/m², anti-pilling and padded inside. Ring-spun cotton, characterised by high density, combined with softness and smoothness, guarantees strength and abrasion resistance as well as provide comfort of wearing. Cuffs and jacket bottom finished with a drawstring.

Size	Code	Colour	Code	Colour	H [cm]	C [cm]	
S	L4011701		L4011301		158-164	84-88	20
M	L4011702		L4011302		164-170	92-96	20
L	L4011703		L4011303		170-176	100-104	20
XL	L4011704		L4011304		176-182	108-112	20
2XL	L4011705		L4011305		182-188	116-120	20
3XL	L4011706		L4011306		188-194	126-130	20



PROLINE


MEGA

TRYTON

VULCAN

LAHTI PRO

2 SWEATSHIRT WITH ZIP

310
g/m²Kat. I
Cat. I

MATERIAL: 60% cotton, 40% polyester 310 g/m². Made of French terry: one of its sides flat, the other one with cross loops, which can absorb large amounts of water, providing comfort of use. 2 pockets with a zipper. Zipper. Zipper cover. Cuffs and jacket bottom with a thick drawstring.


Size	Code	Colour	Code	Colour	Code	Colour	H [cm]	C [cm]	
S	L4014601		L4014701		L4014801		158-164	84-88	20
M	L4014602		L4014702		L4014802		164-170	94-100	20
L	L4014603		L4014703		L4014803		170-176	100-106	20
XL	L4014604		L4014704		L4014804		176-182	106-112	20
2XL	L4014605		L4014705		L4014805		182-188	112-116	20
3XL	L4014606		L4014706		L4014806		188-194	116-122	20

1 SWEATPANTS

320
g/m²



Knee pads
for protective
trousers and
bibpants, p.




MATERIAL: 60% cotton, 38% polyester, 2% elastane, 320 g/m². Made of French terry: one of its sides flat, the other one with cross loops, which can absorb large amounts of water, providing comfort of use. 3 zipped pockets. Practical holster pockets made from rip-stop material, hidden and zipped. Knee pad pockets made from rip-stop material. Innovative waist adjustment with a drawstring and strings. Legs finished with a drawstring.

Code	Size	H [cm]	W [cm]	
L4052301	S	158-164	74-78	20
L4052302	M	164-170	82-86	20
L4052303	L	170-176	90-94	20
L4052304	XL	176-182	98-102	20
L4052305	2XL	182-188	106-110	20
L4052306	3XL	188-194	116-120	20

2 SWEATPANTS

320
g/m²




MATERIAL: 60% cotton, 38% polyester, 2% elastane, 320 g/m². Made of French terry: one of its sides flat, the other one with cross loops, which can absorb large amounts of water, providing comfort of use. 3 pockets. Innovative waist adjustment with a drawstring and strings. Legs finished with a drawstring.

Size	Code	Colour	Code	Colour	H [cm]	W [cm]	
S	L4053001		L4053101		158-164	74-78	20
M	L4053002		L4053102		164-170	82-86	20
L	L4053003		L4053103		170-176	90-94	20
XL	L4053004		L4053104		176-182	98-102	20
2XL	L4053005		L4053105		182-188	106-110	20
3XL	L4053006		L4053106		188-194	116-120	20

3 STRETCH FLEECE JACKET

290
g/m²



MATERIAL: 95% polyester, 5% elastane. Fleece material with elastane provides perfect fit and high comfort of use. Additional elbows reinforcement made of rip-stop material. Flat stitches increase comfort of use. 2 pockets with a zipper. Zipper. Zipper cover. Flexible thumbhole cuffs.


Code	Size	H [cm]	C [cm]	
L4015001	S	158-164	84-88	20
L4015002	M	164-170	92-96	20
L4015003	L	170-176	100-104	20
L4015004	XL	176-182	108-112	20
L4015005	2XL	182-188	116-120	20
L4015006	3XL	188-194	126-130	20

4 FLEECE JACKET WITH REINFORCEMENTS

420
g/m²




Abrasion-resistant fabric reinforcements



MATERIAL: Fleece 100% polyester 420 g/m², short-cut, brushed on both sides, and anti-pilling. Inserts: 600D Oxford 100% polyester 180g/m². 5 pockets, including 4 with a zipper. Zipper. Zipper cover. Reflective elements. Keychain hole. 3 holders for accessories. Sleeves with velcro adjustment. Width adjustment at the jacket bottom with a special drawstring. Sleeves, yoke, collar, and pockets reinforced with an abrasion-resistant material.

Code	Size	H [cm]	C [cm]	
L4013901	S	158-164	84-88	20
L4013902	M	164-170	92-96	20
L4013903	L	170-176	100-104	20
L4013904	XL	176-182	108-112	20
L4013905	2XL	182-188	116-120	20
L4013906	3XL	188-194	126-130	20


1 FLEECE JACKET WITH REINFORCEMENTS

290
g/m²Abrasion-
resistant fabric
reinforcementsKat. I
Cat. I

MATERIAL: Fleece 100% polyester 290 g/m², short-cut, brushed on both sides, and anti-pilling. Inserts: 300D Oxford 100% polyester 150 g/m². 3 zipped pockets. Zipper. Zipper cover. Width adjustment at the jacket bottom with a special drawstring. Sleeves and yoke reinforced with an abrasion-resistant material.

Size	Code	Colour	Code	Colour	Code	Colour	Code	Colour	Code	Colour	H [cm]	C [cm]	
S	L4011401		L4011501		L4011901		L4013701		L4013801		158-164	84-88	20
M	L4011402		L4011502		L4011902		L4013702		L4013802		164-170	92-96	20
L	L4011403		L4011503		L4011903		L4013703		L4013803		170-176	100-104	20
XL	L4011404		L4011504		L4011904		L4013704		L4013804		176-182	108-112	20
2XL	L4011405		L4011505		L4011905		L4013705		L4013805		182-188	116-120	20
3XL	L4011406		L4011506		L4011906		L4013706		L4013806		188-194	126-130	20


2 FLEECE JACKET

290
g/m²Kat. I
Cat. I

MATERIAL: Fleece 100% polyester 290g/m², short-cut, brushed on both sides, and anti-pilling. 3 zipped pockets. Zipper. Zipper cover. Width adjustment at the jacket bottom with a special drawstring.

Code	Size	H [cm]	C [cm]	
LPBP1XS	XS	170-173	84-90	20
LPBP1S	S	173-176	90-96	20
LPBP1M	M	176-179	96-102	20
LPBP1L	L	179-182	102-108	20
LPBP1XL	XL	182-184	108-114	20
LPBP12XL	2XL	184-186	114-120	20
LPBP13XL	3XL	186-188	120-126	20
LPBP14XL	4XL	188-190	126-132	20
LPBP15XL	5XL	190-192	132-140	20

3 FLEECE JACKET

290
g/m²Kat. I
Cat. I


MATERIAL: Fleece 100% polyester 290g/m², short-cut, brushed on both sides, and anti-pilling. 3 zipped pockets. Zipper. Zipper cover. Width adjustment at the jacket bottom with a special drawstring.

Code	Size	H [cm]	C [cm]	
L4011601	S	158-164	84-88	20
L4011602	M	164-170	92-96	20
L4011603	L	170-176	100-104	20
L4011604	XL	176-182	108-112	20
L4011605	2XL	182-188	116-120	20
L4011606	3XL	188-194	126-130	20

1 FLEECE JACKET



290
g/m²




MATERIAL: Fleece 100% polyester 290g/m², short-cut, brushed on both sides, and anti-pilling. 3 zipped pockets. Zipper. Zipper cover. Width adjustment at the jacket bottom with a special drawstring.

Size	Code	Colour	Code	Colour	Code	Colour	Code	Colour	H [cm]	C [cm]	
S	LPBP2S		L4010201		L4010101		L4011801		158-164	84-88	20
M	LPBP2M		L4010202		L4010102		L4011802		164-170	92-96	20
L	LPBP2L		L4010203		L4010103		L4011803		170-176	100-104	20
XL	LPBP2XL		L4010204		L4010104		L4011804		176-182	108-112	20
2XL	LPBP22XL		L4010205		L4010105		L4011805		182-188	116-120	20
3XL	LPBP23XL		L4010206		L4010106		L4011806		188-194	126-130	20

2 FLEECE JACKET



290
g/m²




MATERIAL: Fleece 100% polyester 290g/m², short-cut, brushed on both sides, and anti-pilling. 3 pockets. Zipper. Zipper cover.

Size	Code	Colour	Code	Colour	H [cm]	C [cm]	
S	L4012001		L4012101		158-164	84-88	20
M	L4012002		L4012102		164-170	92-96	20
L	L4012003		L4012103		170-176	100-104	20
XL	L4012004		L4012104		176-182	108-112	20
2XL	L4012005		L4012105		182-188	116-120	20
3XL	L4012006		L4012106		188-194	126-130	20

3 FLEECE JACKET



250
g/m²




MATERIAL: Fleece 100% polyester 250g/m², short-cut, brushed on both side, and anti-pilling. 2 pockets. Zipper.

Size	Code	Colour	Code	Colour	H [cm]	C [cm]	
S	L4014401		L4014501		158-164	84-88	20
M	L4014402		L4014502		164-170	92-96	20
L	L4014403		L4014503		170-176	100-104	20
XL	L4014404		L4014504		176-182	108-112	20
2XL	L4014405		L4014505		182-188	116-120	20
3XL	L4014406		L4014506		188-194	126-130	20

1 WOMEN'S FLEECE JACKET


290
g/m²


Kat. I
Cat. I


MATERIAL: Fleece 100% polyester 290g/m², short-cut, brushed on both sides, and anti-pilling. 2 pockets with a zipper. Zipper. Zipper cover.

Code	Size	H [cm]	C [cm]	
L4010301	S	158-164	82-86	20
L4010302	M	164-170	88-92	20
L4010303	L	170-176	94-98	20
L4010304	XL	170-176	100-104	20
L4010305	2XL	176-182	106-110	20
L4010306	3XL	176-182	112-116	20

2 WOMEN'S FLEECE JACKET


290
g/m²

Kat. I
Cat. I


MATERIAL: Fleece 100% polyester 290g/m², short-cut, brushed on both sides, and anti-pilling. 2 pockets with a zipper. Zipper. Zipper cover.

Code	Size	H [cm]	C [cm]	
L4010601	S	158-164	82-86	20
L4010602	M	164-170	88-92	20
L4010603	L	170-176	94-98	20
L4010604	XL	170-176	100-104	20
L4010605	2XL	176-182	106-110	20
L4010606	3XL	176-182	112-116	20



PROLINE

MEGA

TRYTON

VULCAN


LAHTI PRO

1 SOFT-SHELL JACKET WITH HOOD AND DETACHABLE SLEEVES



310
g/m²


2in1



CE



Kat. I
Cat. I




MATERIAL: Coating: soft-shell textile, 96% polyester, 4% elastane 310 g/m². Lining: microfleece 160 g/m². Special 3-ply soft-shell textile with TPU membrane, waterproof (8000 mm), breathable (3000 g/m²/24 h), guaranteeing high comfort of use. Elastane in the fabric makes it flexible, soft, and durable. 6 pockets (3 outer with a zipper, 1 with a press stud and 2 inner). Detachable sleeves. Detachable hood with double adjustment (depth and width). Zipper with an additional flap attached with a press stud and a velcro fastener. Zipper cover. Reflective elements. Sleeves with velcro adjustment. Width adjustment at the jacket bottom with a special drawstring.

Code	Size	H [cm]	C [cm]	
L4093001	S	158-164	84-88	20
L4093002	M	164-170	92-96	20
L4093003	L	170-176	100-104	20
L4093004	XL	176-182	108-112	20
L4093005	2XL	182-188	116-120	20
L4093006	3XL	188-194	126-130	20

2 SOFT-SHELL JACKET WITH HOOD




310
g/m²



CE




Kat. I
Cat. I



MATERIAL: Coating: soft-shell fabric with rip-stop softshell gussets, 96% polyester, 4% elastane, 310 g/m². Lining: microfleece, 160 g/m². Special 3-ply soft-shell textile with TPU membrane, waterproof (8000 mm), breathable (3000 g/m²/24 h), guaranteeing high comfort of use. Elastane in the fabric makes it flexible, soft, and durable. 6 pockets (3 outer with a zipper, 1 with a velcro and 2 inner). Detachable hood with width adjustment. High-quality YKK zipper. Zipper cover. Reflective elements increasing occupational safety. Sleeves with velcro adjustment. The cuffs finished with an internal elastic band with a thumb hole provide protection against wind. Width adjustment at the jacket bottom with a special drawstring.

Code	Size	H [cm]	C [cm]	
L4094601	S	173-176	90-96	20
L4094602	M	176-179	96-102	20
L4094603	L	179-182	102-108	20
L4094604	XL	182-184	108-114	20
L4094605	2XL	184-186	114-120	20
L4094606	3XL	186-188	120-126	20

SOFTSHELL JACKETS – stay warm and stay fit



Detachable hood with width adjustment.

300
g/m²

Coating: soft-shell textile, 100% polyester 300 g/m². Lining: microfleece 160 g/m².

Special 3-ply soft-shell textile with TPU membrane, waterproof (8000 mm), breathable (3000 g/m²/24 h), guaranteeing high comfort of use.

Reflective material increasing visibility in the dark.




DZIEŃ

NOC

1 SOFT-SHELL JACKET WITH HOOD



Kat. I
Cat. I



MATERIAL: Coating: soft-shell textile, 100% polyester 300 g/m². Lining: microfleece 160 g/m²

Code	Size	H [cm]	C [cm]	
L4092301	S	158-164	84-88	20
L4092302	M	164-170	92-96	20
L4092303	L	170-176	100-104	20
L4092304	XL	176-182	108-112	20
L4092305	2XL	182-188	116-120	20
L4092306	3XL	188-194	126-130	20