




1 PROTECTIVE JACKET

270
g/m²Stretch fabric inserts
on the backstretch fabric inserts
on elbowsKat. I
Cat. I

MATERIAL: 60% cotton, 40% polyester / 90% nylon, 10% elastane. Durable CANVAS fabric. Inserts made of stretch fabric provides flexibility and comfort during use. Yellow fabric elements increasing safety during work. 5 pockets, including 1 with a zipper. Double seams. Cuffs finished with a drawstring with velcro adjustment. Bottom of the sweatshirt with adjustable studs. Fashionable and interesting design.

Code	Size	H [cm]	C [cm]	
L4042401	S	173-176	90-96	20
L4042402	M	176-179	96-102	20
L4042403	L	179-182	102-108	20
L4042404	XL	182-184	108-114	20
L4042405	2XL	184-186	114-120	20
L4042406	3XL	186-188	120-126	20

2 TROUSERS PROTECTIVE TO THE WAIST

270
g/m²Stretch fabric inserts
on the backStretch fabric inserts
under the kneesKnee pads
for protective
trousers and
bibpants, p.Kat. I
Cat. I

MATERIAL: 60% cotton, 40% polyester / 90% nylon, 10% elastane. Durable CANVAS fabric. Inserts made of stretch fabric provides flexibility and comfort during use. Yellow fabric elements increasing safety during work. 10 pockets including 3 pockets with velcro. Triple seams. Belt loops. Waist adjustment with a drawstring. Fashionable and interesting design. Knee pad pockets with a velcro fastener.

Code	Size	H [cm]	W [cm]	
L4054801	S	173-176	80-86	20
L4054802	M	176-179	86-92	20
L4054803	L	179-182	92-98	20
L4054804	XL	182-184	98-104	20
L4054805	2XL	184-186	104-110	20
L4054806	3XL	186-188	116-122	20

Definitely a Good Pattern

The LAHTI PRO brand product, i.e. a sweatshirt (L40415) and trousers (L40522), won the main prize in the WORK/OFFICE category and received the Good Design 2023 Emblem of the Institute of Industrial Design.



1 PROTECTIVE JACKET, SLIM FIT




270
g/m²



Kat. I
Cat. I

CE



MATERIAL: 98% cotton, 2% elastane. 5 pockets, including 2 with a zipper. Fabric with elastane provides elasticity and the comfort of use. Double seams. Zipper. Zipper cover. Reflective inserts increasing occupational safety. Adjustment at the jacket bottom with a velcro fastener. Sleeves finished with a thick drawstring. Practical hood with adjustable width. Fashionable and interesting design. Slim fit. ID tag.


2 TROUSERS PROTECTIVE TO THE WAIST, SLIM FIT



270
g/m²



Knee pads
for protective
trousers and
bibpants, p.



Kat. I
Cat. I

CE

MATERIAL: 98% cotton, 2% elastane. 13 pockets, including 1 with a zipper. Fabric with elastane provides elasticity and the comfort of use. Double seams. Reflective inserts increasing occupational safety. Practical holster pockets. Keychain hole. Belt loops. Knee pad pockets reinforced with an abrasion-resistant material (600D polyester). Slim fit. Fashionable and interesting design. ID tag.


Size	Code	Colour	Code	Colour	H [cm]	C [cm]	
S	L4041501		L4041801		158-164	84-88	20
M	L4041502		L4041802		164-170	92-96	20
L	L4041503		L4041803		170-176	100-104	20
XL	L4041504		L4041804		176-182	108-112	20
2XL	L4041505		L4041805		182-188	116-120	20
3XL	L4041506		L4041806		188-194	126-130	20

Size	Code	Colour	Code	Colour	H [cm]	W [cm]	
S	L4052201		L4052701		158-164	74-78	20
M	L4052202		L4052702		164-170	82-86	20
L	L4052203		L4052703		170-176	90-94	20
XL	L4052204		L4052704		176-182	98-102	20
2XL	L4052205		L4052705		182-188	106-110	20
3XL	L4052206		L4052706		188-194	116-120	20

1 PROTECTIVE JACKET WITH DETACHABLE SLEEVES

240
g/m²

2in1

Kat. I
Cat. I

MATERIAL: 65% polyester, 35% cotton. Durable CANVAS fabric. 7 pockets, including 4 with a velcro fastener. Side pockets with zippers. Pocket for a mobile phone. Zipper. Zipper cover. Yoke reinforced with material (600D polyester). Sleeves and width adjustment at the jacket bottom with press studs. Detachable sleeves. ID tag.

Code	Size	H [cm]	C [cm]	
L4042001	S	158-164	84-88	10
L4042002	M	164-170	92-96	10
L4042003	L	170-176	100-104	10
L4042004	XL	176-182	108-112	10
L4042005	2XL	182-188	116-120	10
L4042006	3XL	188-194	126-130	10

2 PROTECTIVE TROUSERS WITH REMOVABLE LEGS

240
g/m²


2in1



Abrasion-resistant fabric reinforcements



Knee pads for protective trousers and bibpants, p.

Kat. I
Cat. I

MATERIAL: 65% polyester, 35% cotton. Durable CANVAS fabric. 7 pockets, including 4 with a velcro fastener. Pocket for a mobile phone. Knee pad pockets with a velcro fastener. Pockets, knee pad pockets, back and trousers bottom reinforced with an abrasion-resistant material (600D polyester). Detachable legs. Waist width adjustment with an elastic band. Additional holder for accessories with a velcro fastener. Belt loops. ID tag.

Code	Size	H [cm]	W [cm]	
L4053201	S	158-164	74-78	10
L4053202	M	164-170	82-86	10
L4053203	L	170-176	90-94	10
L4053204	XL	176-182	98-102	10
L4053205	2XL	182-188	106-110	10
L4053206	3XL	188-194	116-120	10

PROLINE

MEGA

TRYTON


VULCAN

LAHTIPRO

1 LADIES' JACKET, SLIM FIT



260
g/m²



MATERIAL: 100% polyester 260 g/m². Soft fabric with microfleece lining. 6 pockets (2 inner and 4 outer, including one with a zipper). Zipper. Zipper cover. Reflective inserts increasing occupational safety. Sleeve cuffs with elastic trim. Fashionable and interesting design. Slim fit. ID tag.

Code	Size	H [cm]	C [cm]	W [cm]	
L4042201	S	162-164	88-94	70-76	10
L4042202	M	164-166	94-100	76-82	10
L4042203	L	166-168	100-106	82-88	10
L4042204	XL	168-170	106-112	88-94	10
L4042205	2XL	170-172	112-118	94-100	10
L4042206	3XL	172-174	118-124	100-106	10

2 LADIES' PROTECTIVE TROUSERS, SLIM FIT




270
g/m²




Knee pads for protective trousers and bibpant, p.



Abrasion-resistant fabric reinforcements



Possibility of lengthening the legs



MATERIAL: 98% cotton, 2% elastane, 270 g/m². Fabric with elastane ensures flexibility and comfort during use. 9 pockets, including 1 zipped. Mobile phone pocket. Reflective inserts increasing occupational safety. Triple seams. Additional seams reinforcement in the crotch. Waist width adjustment with an elastic drawstring insert. Optional legs extension (+3 cm). 3 accessory pockets. Belt loops. Reinforced knee pad pockets with abrasion-resistant material (600D polyester). Slim fit. Fashionable and interesting design. ID tag.

Code	Size	H [cm]	W [cm]	
L4054301	S	162-164	70-76	20
L4054302	M	164-166	76-82	20
L4054303	L	166-168	82-88	20
L4054304	XL	168-170	88-94	20
L4054305	2XL	170-172	94-100	20
L4054306	3XL	172-174	100-106	20

THE ONLY JEANS THAT REALLY DO THE JOB



Electromagnetic radiation protection



Elastic material with stretch




Innovative waist width regulation



Abrasion-resistant fabric reinforcements



Knee pads for protective trousers and bibpants, p. 553

Kat. I
Cat. I

MATERIAL: 70% cotton, 28% polyester, 2% elastane. 12 pockets, including 2 with a press stud. Pocket for a mobile phone protected with an EMF shield fabric. Fabric with stretch provides elasticity and comfort of use. Double seams. Additional seams reinforcement in the crotch. Innovative waist width adjustment with a special construction with an elastic band. Keychain hole. Hammer holder. Belt loops. Pockets and knee pad pockets reinforced with an abrasion-resistant material (600D polyester). Slim fit. Fashionable and interesting design. ID tag.

Size	Code	Colour	Code	Colour	Code	Colour	H [cm]	W [cm]	
S	L4051001		L4051701		L4054201		158-164	74-78	20
M	L4051002		L4051702		L4054202		164-170	82-86	20
L	L4051003		L4051703		L4054203		170-176	90-94	20
XL	L4051004		L4051704		L4054204		176-182	98-102	20
2XL	L4051005		L4051705		L4054205		182-188	106-110	20
3XL	L4051006		L4051706		L4054206		188-194	116-120	20