



Aluminium P-Clips

- ALU-P-Clip with / without chloroprene Insert

TYPE	Width (W)	Width (W2)	Wall (WT)	Wall (WT2)	Hole Ø (FH)	Bundle Ø max.	Fixing Hole Centres (F2)	Radius (R)	Material	Colour	Article-No.
ALU12C	16.3	12.7	4.50	1.3	5.2	15.9	19.9	2.8	AL, CR	Black (BK)	211-15120
ALU13C	16.3	12.7	4.50	1.3	5.2	17.5	20.7	2.8	AL, CR	Black (BK)	211-15130
ALU14C	16.3	12.7	4.50	1.3	5.2	19.1	21.5	2.8	AL, CR	Black (BK)	211-15140
ALU15C	16.3	12.7	4.50	1.3	5.2	20.6	22.3	2.8	AL, CR	Black (BK)	211-15150
ALU16C	16.3	12.7	4.50	1.3	5.2	22.2	23.1	2.8	AL, CR	Black (BK)	211-15160
ALU17C	16.3	12.7	4.50	1.3	5.2	23.8	23.9	2.8	AL, CR	Black (BK)	211-15170
ALU18C	16.3	12.7	4.50	1.3	5.2	25.4	24.6	2.8	AL, CR	Black (BK)	211-15180
ALU19C	16.3	12.7	4.50	1.3	5.2	27.0	25.5	2.8	AL, CR	Black (BK)	211-15190
ALU20C	16.3	12.7	4.50	1.6	5.2	28.6	27.0	3.2	AL, CR	Black (BK)	211-15200
ALU22C	16.3	12.7	4.50	1.6	5.2	31.8	28.6	3.2	AL, CR	Black (BK)	211-15220
ALU23C	16.3	12.7	4.50	1.6	5.2	33.3	29.4	3.2	AL, CR	Black (BK)	211-15230
ALU25C	16.3	12.7	4.50	1.6	5.2	36.5	30.8	3.2	AL, CR	Black (BK)	211-15250
ALU26C	16.3	12.7	4.50	1.6	5.2	38.1	31.7	3.2	AL, CR	Black (BK)	211-15260
ALU28C	16.3	12.7	4.50	1.6	5.2	41.3	33.3	3.2	AL, CR	Black (BK)	211-15280
ALU29C	16.3	12.7	4.50	1.6	5.2	42.9	34.1	3.2	AL, CR	Black (BK)	211-15290
ALU30C	16.3	12.7	4.50	1.6	5.2	44.5	34.9	3.2	AL, CR	Black (BK)	211-15300
ALU34C	16.3	12.7	4.50	1.6	5.2	50.8	38.1	3.2	AL, CR	Black (BK)	211-15340
ALU24C	16.3	12.7	4.50	1.6	5.2	34.9	30.2	3.2	AL, CR	Black (BK)	211-15240

All dimensions in mm. Subject to technical changes.