



Product: [9916](#) 

Lead Wire, #16 Str TC, PVC Ins, AWM 1007 AWM 1569

 [Request Sample](#)

Product Description

Low Temp Plastic Lead Wire, 16AWG (26x30) Tinned Copper, PVC Insulation, AWM 1007 AWM 1569 CSA TYPE TR-64 TRSR-64

Technical Specifications

Product Overview

Suitable Applications:	inter-connection circuits, internal wiring of computer and electronic equipments, internal wiring of appliances
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	1	16 AWG	26x30	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
PVC - Polyvinyl Chloride	0.016 in (0.41 mm)	0.092 in (2.3 mm)

Overall Cable Diameter (Nominal):	0.092 in (2.3 mm)
-----------------------------------	-------------------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Max. Current
4.44 Ohm/1000ft	Single conductor in free air @ 30°C: 28.8 A

Voltage

UL Voltage Rating
300 V RMS

Mechanical Characteristics

Temperature

UL Temperature	Operating
105°C	-25°C To +105°C

Bend Radius

Stationary Min.	Installation Min.
0.92 in (23 mm)	0.92 in (23 mm)

Max. Pull Tension:	35 lbs (16 kg)
Bulk Cable Weight:	12 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	VW-1

AWM Compliance:	AWM 1007, AWM 1569
CEC / C(UL) Compliance:	TRSR-64
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

History

Update and Revision:	Revision Number: 0.488 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
9916 010100	Black	Reel	100 ft	612825261988	
9916 0101000	Black	Reel	1,000 ft	612825261995	P
9916 0105000	Black	Reel	5,000 ft	612825262008	P
9916 013100	Blue, Dark	Reel	100 ft	612825262015	
9916 0131000	Blue, Dark	Reel	1,000 ft	612825262022	P
9916 001100	Brown	Reel	100 ft	612825261797	
9916 0011000	Brown	Reel	1,000 ft	612825261803	P
9916 0081000	Gray	Reel	1,000 ft	612825261933	P
9916 005100	Green, Dark	Reel	100 ft	612825261896	
9916 0051000	Green, Dark	Reel	1,000 ft	612825261902	P
9916 0031000	Orange	Reel	1,000 ft	612825261858	P
9916 002100	Red	Reel	100 ft	612825261827	
9916 0021000	Red	Reel	1,000 ft	612825261834	P
9916 0025000	Red	Reel	5,000 ft	612825261841	P
9916 007100	Violet	Reel	100 ft	612825261919	
9916 0071000	Violet	Reel	1,000 ft	612825261926	P
9916 009100	White	Reel	100 ft	612825261940	
9916 0091000	White	Reel	1,000 ft	612825261957	P
9916 0095000	White	Reel	5,000 ft	612825261964	P
9916 004100	Yellow	Reel	100 ft	612825261865	
9916 0041000	Yellow	Reel	1,000 ft	612825261872	P
Footnote:	P - STRIPE COLORS ON STOCK SOLID COLORS. STRIPING ADDER OF \$8.00/M= FOR 1 OR 2 STRIPES. 10,000' MINIMUM ORDER FOR COLOR COMBINATION. PUT-UP WILL BE SUBJECT TO TWO PIECES (+ OR -) 10% PER SPOOL, WITH A MINIMUM LENGTH OF 100'.				

© 2025 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.