



PRODUCT CHANGE NOTIFICATION (PCN)

PCN NO.: 01/2025

Product Type: All products shipped with **SCREWS**


Products Affected: see list below

Description of Change: Powersem GmbH will stop deliveries of screws along with all modules as shown in the list

Reason for change: Procurement of screws not economical due to different sizes, dimensions and customer preference

Customer affected: GENERAL

Effective Date of Change: all deliveries from **January 1st, 2026** onwards (including already existing Purchase Orders)

Authorized by:  

Kavita Soni, CEO, Powersem GmbH

Date: 31.08.2025

Contact:

Powersem GmbH
Walpersdorfer Str. 53
91126 Schwabach, Germany
Email: kavita@powersem.com
Web: www.powersem.com

Customer Acknowledgment of Receipt:

(within 10 days, otherwise automatically acknowledged by customer)

Company: _____

Address: _____

Name: _____

Title: _____

Email: _____

Date: _____

Signature: _____

PRODUCT CHANGE NOTIFICATION (PCN)

PCN NO.: 01/2025

List of modules with screw types and quantities

MODULE	SCREW TYPE A	QUANTITY A	SCREW TYPE B	QUANTITY B
PSB 35	M4x8 mm	4 Pcs.		
PSB 50	M5x10 mm	4 Pcs.		
PSB 55	M5x10 mm	4 Pcs.		
PSB 62	M5x10 mm	4 Pcs.		
PSB 63	M5x10 mm	4 Pcs.		
PSB 75	M5x10 mm	4 Pcs.		
PSB 82	M5x10 mm	4 Pcs.		
PSB 83	M5x10 mm	4 Pcs.		
PSB 95	M5x10 mm	4 Pcs.		
PSB 105	M5x10 mm	4 Pcs.		
PSB 112	M6x12 mm	4 Pcs.		
PSB 125	M5x10 mm	4 Pcs.		
PSB 162	M6x12 mm	4 Pcs.		
PSB 192	M6x12 mm	4 Pcs.		
PSBH 55	M5x10 mm	4 Pcs.	M3x6 mm	2 Pcs.
PSBH 75	M5x10 mm	4 Pcs.	M3x6 mm	2 Pcs.
PSBH 85	M6x12 mm	4 Pcs.		
PSBH 125	M6x12 mm	4 Pcs.		
PSBS 62	M5x10 mm	4 Pcs.		
PSBS 63	M5x10 mm	4 Pcs.		
PSBS 82	M5x10 mm	4 Pcs.		
PSBS 83	M5x10 mm	4 Pcs.		
PSBS 112	M6x10 mm	4 Pcs.		
PSBS 162	M6x10 mm	4 Pcs.		
PSBS 192	M6x10 mm	4 Pcs.		
PSBT 55	M5x10 mm	4 Pcs.	M3x6 mm	4 Pcs.
PSBT 75	M5x10 mm	4 Pcs.	M3x6 mm	4 Pcs.
PSBT 85	M6x12 mm	4 Pcs.		
PSBT 125	M6x12 mm	4 Pcs.		
PSBZ 55	M5x10 mm	4 Pcs.	M3x6 mm	2 Pcs.
PSBZ 75	M5x10 mm	4 Pcs.	M3x6 mm	2 Pcs.
PSBZ 85	M6x12 mm	4 Pcs.		
PSBZ 125	M6x12 mm	4 Pcs.		
PSCH 55	M5x10 mm	4 Pcs.	M3x6 mm	2 Pcs.
PSCH 75	M5x10 mm	4 Pcs.	M3x6 mm	2 Pcs.
PSCH 85	M6x12 mm	4 Pcs.		
PSCH 125	M6x12 mm	4 Pcs.		
PSCT 55	M5x10 mm	4 Pcs.	M3x6 mm	4 Pcs.
PSCT 75	M5x10 mm	4 Pcs.	M3x6 mm	4 Pcs.
PSCT 85	M6x12 mm	4 Pcs.		
PSCT 125	M6x12 mm	4 Pcs.		
PSD 35	M4x8 mm	5 Pcs.		

PRODUCT CHANGE NOTIFICATION (PCN)

PCN NO.: 01/2025

List of modules with screw types and quantities

MODULE	SCREW TYPE A	QUANTITY A	SCREW TYPE B	QUANTITY B
PSD 50	M5x10 mm	5 Pcs.		
PSD 55	M5x10 mm	5 Pcs.		
PSD 62	M5x10 mm	5 Pcs.		
PSD 63	M5x10 mm	5 Pcs.		
PSD 75	M5x10 mm	5 Pcs.		
PSD 82	M5x10 mm	5 Pcs.		
PSD 83	M5x10 mm	5 Pcs.		
PSD 95	M5x10 mm	5 Pcs.		
PSD 105	M5x10 mm	5 Pcs.		
PSD 112	M6x12 mm	5 Pcs.		
PSD 125	M5x10 mm	5 Pcs.		
PSD 162	M6x12 mm	5 Pcs.		
PSD 192	M6x12 mm	5 Pcs.		
PSDH 75	M5x10 mm	5 Pcs.	M3x6 mm	3 Pcs.
PSDH 90	M5x10 mm	5 Pcs.	M3x6 mm	3 Pcs.
PSDH 110	M6x12 mm	5 Pcs.		
PSDH 175	M6x12 mm	5 Pcs.		
PSDS 62	M5x10 mm	5 Pcs.		
PSDS 63	M5x10 mm	5 Pcs.		
PSDS 82	M5x10 mm	5 Pcs.		
PSDS 83	M5x10 mm	5 Pcs.		
PSDS 112	M6x10 mm	5 Pcs.		
PSDS 162	M6x10 mm	5 Pcs.		
PSDS 192	M6x10 mm	5 Pcs.		
PSDT 75	M5x10 mm	5 Pcs.	M3x6 mm	6 Pcs.
PSDT 90	M5x10 mm	5 Pcs.	M3x6 mm	6 Pcs.
PSDT 110	M6x12 mm	5 Pcs.		
PSDT 175	M6x12 mm	5 Pcs.		
PSKD 26	M5x10 mm	3 Pcs.		
PSKD 44	M5x10 mm	3 Pcs.		
PSKD 56	M5x10 mm	3 Pcs.		
PSKD 72	M5x10 mm	3 Pcs.		
PSKD 95	M5x10 mm	3 Pcs.		
PSKD 142	M6x12 mm	3 Pcs.		
PSKD 172	M6x12 mm	3 Pcs.		
PSKD 220	M8x16 mm	3 Pcs.		
PSKD 250	M8x16 mm	3 Pcs.		
PSKD 255	M8x20 mm	3 Pcs.		
PSKD 310	M8x16 mm	3 Pcs.		
PSKD 312	M8x20 mm	3 Pcs.		
PSKD 100E	M6x12 mm	3 Pcs.		
PSKD 150E	M6x12 mm	3 Pcs.		

PRODUCT CHANGE NOTIFICATION (PCN)

PCN NO.: 01/2025

List of modules with screw types and quantities

MODULE	SCREW TYPE A	QUANTITY A	SCREW TYPE B	QUANTITY B
PSKD 200E	M6x12 mm	3 Pcs.		
PSKD 30E	M5x10 mm	3 Pcs.		
PSKD 50E	M5x10 mm	3 Pcs.		
PSKD 75E	M5x10 mm	3 Pcs.		
PSKH 26	M5x10 mm	3 Pcs.		
PSKH 44	M5x10 mm	3 Pcs.		
PSKH 56	M5x10 mm	3 Pcs.		
PSKH 72	M5x10 mm	3 Pcs.		
PSKH 94	M5x10 mm	3 Pcs.		
PSKH 95	M5x10 mm	3 Pcs.		
PSKH 132	M6x12 mm	3 Pcs.		
PSKH 161	M6x12 mm	3 Pcs.		
PSKH 162	M6x12 mm	3 Pcs.		
PSKH 220	M8x16 mm	3 Pcs.		
PSKH 250	M8x16 mm	3 Pcs.		
PSKH 255	M8x20 mm	3 Pcs.		
PSKH 310	M8x16 mm	3 Pcs.		
PSKH 312	M8x20 mm	3 Pcs.		
PSKT 19	M5x10 mm	3 Pcs.		
PSKT 26	M5x10 mm	3 Pcs.		
PSKT 44	M5x10 mm	3 Pcs.		
PSKT 56	M5x10 mm	3 Pcs.		
PSKT 72	M5x10 mm	3 Pcs.		
PSKT 94	M5x10 mm	3 Pcs.		
PSKT 95	M5x10 mm	3 Pcs.		
PSKT 132	M6x12 mm	3 Pcs.		
PSKT 161	M6x12 mm	3 Pcs.		
PSKT 162	M6x12 mm	3 Pcs.		
PSKT 170	M8x20 mm	3 Pcs.		
PSKT 224	M8x20 mm	3 Pcs.		
PSKT 225	M8x20 mm	3 Pcs.		
PSKT 255	M8x20 mm	3 Pcs.		
PSKT 310	M8x16 mm	3 Pcs.		
PSKT 312	M8x20 mm	3 Pcs.		
PSMD 100E	M6x12 mm	3 Pcs.		
PSMD 150E	M6x12 mm	3 Pcs.		
PSMD 200E	M6x12 mm	3 Pcs.		
PSMD 30E	M5x10 mm	3 Pcs.		
PSMD 50E	M5x10 mm	3 Pcs.		
PSMD 75E	M5x10 mm	3 Pcs.		
PSND 100E	M6x12 mm	3 Pcs.		
PSND 150E	M6x12 mm	3 Pcs.		

PRODUCT CHANGE NOTIFICATION (PCN)

PCN NO.: 01/2025

List of modules with screw types and quantities

MODULE	SCREW TYPE A	QUANTITY A	SCREW TYPE B	QUANTITY B
PSND 200E	M6x12 mm	3 Pcs.		
PSND 30E	M5x10 mm	3 Pcs.		
PSND 50E	M5x10 mm	3 Pcs.		
PSND 75E	M5x10 mm	3 Pcs.		
PSTD 82	M5x10 mm	5 Pcs.		
PSTKD 82	M5x10 mm	3 Pcs.		
PSUH 40	M5x10 mm	6 Pcs.	M3x6 mm	3 Pcs.
PSUH 50	M5x10 mm	6 Pcs.	M3x6 mm	3 Pcs.
PSUH 80	M5x10 mm	6 Pcs.	M3x6 mm	3 Pcs.
PSUH 95	M5x10 mm	6 Pcs.	M3x6 mm	3 Pcs.
PSUT 40	M5x10 mm	6 Pcs.	M3x6 mm	6 Pcs.
PSUT 50	M5x10 mm	6 Pcs.	M3x6 mm	6 Pcs.
PSUT 80	M5x10 mm	6 Pcs.	M3x6 mm	6 Pcs.
PSUT 95	M5x10 mm	6 Pcs.	M3x6 mm	6 Pcs.
PSVD 80	M6x12 mm	3 Pcs.		
PSVD 120	M6x12 mm	3 Pcs.		
PSVD 175	M6x12 mm	3 Pcs.		
PSVT 70	M6x12 mm	3 Pcs.		
PSVT 90	M6x12 mm	3 Pcs.		
PSVT 160	M6x12 mm	3 Pcs.		
PSWD 80	M6x12 mm	3 Pcs.		
PSWD 120	M6x12 mm	3 Pcs.		
PSWD 175	M6x12 mm	3 Pcs.		
PSWT 70	M6x12 mm	3 Pcs.		
PSWT 90	M6x12 mm	3 Pcs.		
PSWT 160	M6x12 mm	3 Pcs.		
PSXD 80	M6x12 mm	3 Pcs.		
PSXD 120	M6x12 mm	3 Pcs.		
PSXD 175	M6x12 mm	3 Pcs.		
PSXT 70	M6x12 mm	3 Pcs.		
PSXT 90	M6x12 mm	3 Pcs.		
PSXT 160	M6x12 mm	3 Pcs.		
PSYD 80	M6x12 mm	3 Pcs.		
PSYD 120	M6x12 mm	3 Pcs.		
PSYD 175	M6x12 mm	3 Pcs.		
PSYT 70	M6x12 mm	3 Pcs.		
PSYT 90	M6x12 mm	3 Pcs.		
PSYT 160	M6x12 mm	3 Pcs.		

PRODUCT CHANGE NOTIFICATION (PCN)

PCN NO.: 01/2025

Mounting screw M6x12 with pre-assembled washer (RoHS III compliant)								
	Pozidrive head screw (additional slot for slotted screwdriver) with under-head serration	H1 = 4.6mm	L1 = 12mm	Thread: M6	D1 = 12mm	Zinc-plated Steel (4.8)	DIN7985	
	Flat washer	H2 = 1.5mm	N.A.	N.A.	D2 = 12mm 5.5mm int. Dia.	Zinc-plated Steel	DIN6902A	
Mounting screw M6x10 with pre-assembled washer (RoHS III compliant)								
	Pozidrive head screw (additional slot for slotted screwdriver) with under-head serration	H1 = 4.6mm	L1 = 10mm	Thread: M6	D1 = 12mm	Zinc-plated Steel (4.8)	DIN7985	
	Flat washer	H2 = 1.5mm	N.A.	N.A.	D2 = 12mm 5.5mm int. Dia.	Zinc-plated Steel	DIN6902A	
Mounting screw M5x10 with pre-assembled washer (RoHS III compliant)								
	Pozidrive head screw (additional slot for slotted screwdriver) with under-head serration	H1 = 3.8mm	L1 = 10mm	Thread: M5	D1 = 10mm	Zinc-plated Steel (8.8)	DIN7985	
	Flat washer	H2 = 1mm	N.A.	N.A.	D2 = 10mm 4.6 mm int. Dia.	Zinc-plated Steel	DIN6902A	
Mounting screw M4x8 with pre-assembled washer (RoHS III compliant)								
	Pozidrive head screw with under-head serration	H1 = 3mm	L1 = 8mm	Thread: M4	D1 = 8mm	Zinc-plated Steel (4.8)	DIN7985	
	Flat washer	H2 = 0.8mm	N.A.	N.A.	D2 = 9mm 3.6 mm int. Dia.	Zinc-plated Steel	DIN6902A	
Mounting screw M3x6 with pre-assembled washer (RoHS III compliant)								
	Pozidrive head screw (additional slot for slotted screwdriver) with under-head serration	H1 = 2.4mm	L1 = 6mm	Thread: M3	D1 = 6mm	Zinc-plated Steel	DIN7985	
	Flat washer	H2 = 0.6mm	N.A.	N.A.	D2 = 7mm 2.7 mm int. Dia.	Zinc-plated Steel	DIN6902A	