

CableLine
CLI C 1-3 GE/SW 9 MP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 1429-0

Fax: +49 5231 14292083

www.weidmueller.com



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

Type	CLI C 1-3 GE/SW 9 MP
Order No.	0252611529
Version	CableLine, Conductor and cable markers, 3 - 5 mm, 3 x 4.2 mm, Yellow
GTIN (EAN)	4008190124267
Qty.	200 pc(s).

CableLine
CLI C 1-3 GE/SW 9 MP
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 1429-0

Fax: +49 5231 14292083

www.weidmueller.com

Technical data
Dimensions and weights

Width	4.2 mm	Width (inches)	0.165 inch
Height	3 mm	Height (inches)	0.118 inch
Depth	5 mm	Depth (inches)	0.197 inch
Net weight	0.06 g		

General data

Colour	Yellow	Colour of printing	Black
Insulation cross-section, max.	5 mm	Material	PVC, soft, without Cadmium
Material colour according to resistance code	4	Operating temperature range	-30...80 °C
Orientation of print	horizontal	Printed characters	Numbers
Printing	9	Printing method	Laser print
Recommended industries	Process, Machinery	Type of printing	Standard
UL 94 flammability rating	V-0	Version	MultiPack
Width	4.2 mm		

Conductor and cable markers

Conductor O.D.	3 - 5 mm	Conductor O.D., max.	5 mm
Conductor O.D., min.	3 mm	Conductor cross-section, min.	1.5 mm ²
Halogen	Yes		

Classifications

ETIM 3.0	EC001530	ETIM 4.0	EC001288
ETIM 5.0	EC001530	ETIM 6.0	EC001530
UNSPSC	44-12-17-08	eClass 5.1	27-14-91-03
eClass 6.2	27-40-04-01	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-03	eClass 9.0	27-14-07-08
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
------------------	------------------------------

CableLine CLI C 1-3 GE/SW 9 MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 1429-0

Fax: +49 5231 14292083

www.weidmueller.com

Drawings



Similar to illustration