

Heatshrinkable moulded shapes bulbous 2-Way Outlet Shapes, Breakout Boots - HellermannTyton

DRAWING No.

152167


SHT. 1

OF

1 SHTS.

© THE COPYRIGHT OF THIS DRAWING IS RESERVED BY HELLERMANN TYTON. IT IS ISSUED ON CONDITION THAT IT IS NOT COPIED, REPRODUCED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE CONSENT IN WRITING OF HELLERMANN TYTON.

THIRD ANGLE PROJECTION



BS 8888

DO NOT SCALE
IF IN DOUBT ASK

Q.A.

H/S SETT

H/S Q.A.


REL. INSP.

H/S PROD


EXT.ISS.CODE

4/6

STANDARD PART (AFTER UNRESTRICTED RECOVERY)



EXPANDED (AS SUPPLIED)



HOT MELT ADHESIVE APPLICATION DETAILS

ADHESIVE REFERENCES:

W – ALL INTERNAL SURFACES COATED

W1 – PARALLEL INTERNAL SURFACES
COATED ONLY

PART No.	EXPANDED DIAMETERS (AS SUPPLIED)		RECOVERED DIAMETERS		RECOVERED DIMENSIONS				
	øh	øj	øH	øJ	P	R	S	Hw	Jw
	MIN	MIN	MAX	MAX	±10%	±10%	NOM	±20%	±30%
223-2	33.0 (1.30)	17.5 (0.69)	9.4 (0.37)	4.1 (0.16)	94.0 (3.70)	30.0 (1.18)	20.0 (0.79)	1.5 (0.06)	1.2 (0.05)
223-3	33.0 (1.30)	17.5 (0.69)	9.4 (0.37)	4.1 (0.16)	60.0 (2.36)	30.0 (1.18)	20.0 (0.79)	1.5 (0.06)	1.2 (0.05)

Heatshrinkable moulded shapes bulbous 2-Way Outlet Shapes, Breakout Boots - HellermannTyton

For information only, not subject to technical changes.

HellermannTyton

Pennycross Close, Plymouth, Devon, England

Tel ++44 (0) 1752 701261 Fax ++44 (0) 1752 790058

NAME

G.BASER

SCALE

NTS

ADHESIVE

A3

ORIGINAL SHEET SIZE
420mm x 297mm

SHT. 1

OF

1 SHTS.

DATE

16/09/08

DIMS IN

mm
(in)

TITLE

2 WAY OUT SLEEVE

PART No.

223

DRAWING No.

152167

ISSUE NOTE No. DRAWN DATE