



Price\* : 52.08 GBP



## Main

|                                    |                                                                                                                                                                                                                                                                                                                                                                                             |
|------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range                              | Spacial                                                                                                                                                                                                                                                                                                                                                                                     |
| Product or component type          | Quick entrance plate                                                                                                                                                                                                                                                                                                                                                                        |
| Accessory / separate part category | Cable management accessory                                                                                                                                                                                                                                                                                                                                                                  |
| Device application                 | Multi-purpose                                                                                                                                                                                                                                                                                                                                                                               |
| Range compatibility                | Spacial Spacial CRN compact enclosure<br>Thalassa Thalassa PLM compact enclosure<br>Spacial Spacial S3HD compact enclosure<br>Spacial Spacial S3CM control enclosure<br>Spacial Spacial SBM industrial box<br>Thalassa Thalassa PLA suitable enclosure<br>Spacial Spacial S3D compact enclosure<br>Thalassa Thalassa PHD suitable enclosure<br>Thalassa Thalassa PLS insulating modular box |
| Device composition                 | 1 circular plate                                                                                                                                                                                                                                                                                                                                                                            |
| Quantity per set                   | Set of 10                                                                                                                                                                                                                                                                                                                                                                                   |

## Complementary

|                          |                                        |
|--------------------------|----------------------------------------|
| Mounting support         | Cable gland plate<br>Body of enclosure |
| Material                 | Polyamide                              |
| Fixing mode              | By screws<br>Clipped                   |
| Total cable entry number | 8                                      |
| Cable entry number       | 1 x 6...10 mm<br>7 x 3.6...6.5 mm      |
| Height                   | Real : 33 mm                           |
| Cable outer diameter     | 50.5 mm<br>58 mm                       |
| Product weight           | 0.46 kg                                |

## Environment

|                         |      |
|-------------------------|------|
| IP degree of protection | IP65 |
|-------------------------|------|

## Offer Sustainability

|                                  |                                                                                                                                                                                                                         |
|----------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status         | Green Premium product                                                                                                                                                                                                   |
| RoHS (date code: YYWW)           | Compliant - since 0957 - Schneider Electric declaration of conformity<br><a href="#"> Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                                                                                                  |
| Product environmental profile    | Available<br><a href="#"> Product Environmental Profile</a>                                                                            |
| Product end of life instructions | Need no specific recycling operations                                                                                                                                                                                   |

## Contractual warranty

|                 |                     |
|-----------------|---------------------|
| Warranty period | 18 months 18 months |
|-----------------|---------------------|