

Basic ejector SBP 25 S03 SDA

Part no.:10.02.01.00568

<https://www.schmalz.com/10.02.01.00568>




Homepage > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Basic Ejectors > Basic Ejectors SBP > SBP 25 S03 SDA

Basic ejector for universal use



Nozzle size: 2,5 mm
with: Axial silencer
Degree of evacuation: 85 %
Connection: Hose D8(1)-D10(2)
Pressure optimal: 4.5 bar
Suction rate (max): 215 l/min
Air consumption (during evac.):
311 l/min

Design Data



Attribute	Value
-----------	-------

B	20 mm
d	4.2 mm
d1	8 mm
d2	10 mm
D	20 mm
H	39 mm
H1	45.5 mm
H2	5.2 mm
H3	17 mm
L	86.5 mm
L1	168 mm
L2	24.5 mm
L3	5.5 mm

Basic ejector SBP 25 S03 SDA

Part no.:10.02.01.00568

<https://www.schmalz.com/10.02.01.00568>



Attribute	Value
L4	12.5 mm
X1	20 mm

Technical Data

Attribute	Value
Nozzle diameter	2.5 mm
Degree of evacuation	85 %
Suction rate (max.)	12.9 m³/h
Suction rate (max.)	215 l/min
Air consumption suction	18.7 m³/h
Air consumption suction	311 l/min
Sound level free	78 dB(A)
Sound level suction	70 dB(A)
Pressure range (operating pressure)	3.0 ... 6.0 bar
Pressure optimal	4.5 bar
Recomm. internal hose diameter compressed air	6 mm
Recomm. internal hose diameter vacuum	7 mm
Operating temperature	0 ... 60 °C
Pressure range (operating pressure)	43.5...87.0
Suction rate (max.)	7.592 cfm
Air consumption suction	10.982 cfm
Weight	50 g

Note: Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

Basic ejector SBP 25 S03 SDA

Part no.:10.02.01.00568

<https://www.schmalz.com/10.02.01.00568>



Spare Parts



SD G3/8-AG 20x76 SBP

Part no.10.02.01.00719

Silencer for vacuum generators


Thread G1: G3/8"-M

External diameter D: 20 mm

Length L: 76 mm

for: Basic ejectors SBP

Accessories



BEF-PL 110x44.5x3 SBP

Part no.10.02.01.00511


Mounting plate

Length L: 110 mm

Width B: 44.5 mm

Height H: 3 mm

for: Basic ejectors SBP



SET SBP M4-IG

Part no.10.02.01.00769

Mounting set

for: Basic ejectors SBP

Type: M4-IG

Basic ejector SBP 25 S03 SDA

Part no.:10.02.01.00568

<https://www.schmalz.com/10.02.01.00568>



VFT G3/8-IG 80

Part no.10.07.01.00122

Vacuum cup filter with transparent housing and replaceable filter

Connection: G3/8"-F

Shape: Long filter insert

Nominal flow rate: 14.7 m³/h

Filter pore size: 80 µm



VFT G3/8-IG 100

Part no.10.07.01.00123

Vacuum cup filter with transparent housing and replaceable filter

Connection: G3/8"-F

Shape: Long filter insert

Nominal flow rate: 17.4 m³/h

Filter pore size: 100 µm