

ROCKER SWITCHES

PRODUCT NUMBER 1552.4602



TECHNICAL DATA

Product number	1552.4602	
Business unit	Switches, Sensors & Controls	
Product Manager	-	
Product family	Rocker switches	
Actuation type	direct	
Packing unit	100	
Miscellaneous	lower lying flange	
Weight	7.000 g	
Switch on continuous current (capacitive)	5 A	
Inrush current (capacitive)	100 A	
ROHS conform	yes	
Output	catalog before 2009 / Web-Shop / catalog	
Switching function	ON / OFF switch (DPST)	
Material fixed contact	Ag	
Number of poles	2 - pole	
connections	PCB terminal, angled	
Mechanical life endurance	5E4	
Rating IEC	10 (4) A 250 V AC 5E4 16 (4) A 250 V AC 1E4	
Rating North America	16 A 125 V AC 1 HP 16 A 250 V AC 2 HP	
Contact resistance (new condition)	< 100 (1 A 12 V DC) mOhm	
Insulation resistance (new condition)	> 100 (500 V DC) MOhm	
Voltage strength at 250 V	→ function insulation / basic insulation 1 500 V → reinforced insulation 3 000 V → small contact distance 500 V	
Proof tracking	250 PTI	
Insulation spacing	acc. to EN 61058 for reinforced or double insulation	
Protection type	→ Connection IP 40 → Actuator IP 40	
Ambient temperature	→ connection side -20 °C ... +100 °C	
Ambient temperature	→ Actuation side min. -20 °C ... +55 °C	

Storage temperature	-40 °C ... +80 °C
Flammability	UL 94 V-2
Glow wire test temperature	850 °C
Actuators and additional actuators	rocker: PA, black, identification white
Housing description	housing: PA, black, lower lying flange
Connection surface	→ bearing connection silver plated
Contact material	Ag
Contact distance	≥ 3 mm
Rating Code UL	R 38
Contact type	lifting contact
Plug force of the terminals	≤ 80 N
Operating force	3 - 5 N
Approval marks	CSA / UL / ENEC 05
Suitable for appliances of protection class	II
Additional labeling	site, year, week of manuf. acc. to DIN EN 60062
Type of fastening	Snap fastening
Degree of pollution	3
Rated impulse withstand voltage	2500 V
Stock version	●

Technical changes reserved. Dimensions are not binding.

Detailed specifications available on request.

Marquardt GmbH · Schloss-Straße 16 · 78604 Rietheim-Weilheim · Germany
Phone: +49 (0) 7424 / 99-0 · Fax: +49 (0) 7424 / 99-2399 · www.marquardt.com · marquardt@marquardt.de