




**DIN 7983 C**

**~ISO 7051**

Standard withdrawn



## BN 697

### Phillips oval countersunk head tapping screws

form H, with cone end type C

Stainless steel A2

- ~UNI 6956 AB
- ~ČSN 021239

 [3D Cadenas](#)

| Article# | d <sub>1</sub> | d <sub>2</sub> max. | f~  | k~  |  | m~  | L   |
|----------|----------------|---------------------|-----|-----|-------------------------------------------------------------------------------------|-----|-----|
| 1214292  | ST2,2          | 4,3                 | 0,7 | 1,3 | 1                                                                                   | 2,8 | 6,5 |
| 1214306  |                |                     |     |     |                                                                                     |     | 9,5 |
| 1214314  |                |                     |     |     |                                                                                     |     | 13  |
| 1675656  |                |                     |     |     |                                                                                     |     | 16  |
| 1675664  |                |                     |     |     |                                                                                     |     | 19  |
| 1019120  | ST2,9          | 5,5                 | 0,9 | 1,7 | 1                                                                                   | 3,4 | 6,5 |
| 1263110  |                |                     |     |     |                                                                                     |     | 9,5 |
| 1263129  |                |                     |     |     |                                                                                     |     | 13  |
| 1263137  |                |                     |     |     |                                                                                     |     | 16  |
| 1263145  |                |                     |     |     |                                                                                     |     | 19  |
| 1263153  |                |                     |     |     |                                                                                     |     | 22  |
| 1263161  |                |                     |     |     |                                                                                     |     | 25  |
| 1263188  |                |                     |     |     |                                                                                     |     | 32  |
| 1263196  | ST3,5          | 6,8                 | 1,2 | 2,1 | 2                                                                                   | 4,6 | 9,5 |
| 1263218  |                |                     |     |     |                                                                                     |     | 13  |
| 1263226  |                |                     |     |     |                                                                                     |     | 16  |
| 1263234  |                |                     |     |     |                                                                                     |     | 19  |
| 1263242  |                |                     |     |     |                                                                                     |     | 22  |
| 1263250  |                |                     |     |     |                                                                                     |     | 25  |
| 1263269  |                |                     |     |     |                                                                                     |     | 32  |
| 1263277  |                |                     |     |     |                                                                                     |     | 38  |
| 3059896  |                |                     |     |     |                                                                                     |     | 45  |
| 3059897  |                |                     |     |     |                                                                                     |     | 50  |
| 1263285  | (ST3,9)        | 7,5                 | 1,3 | 2,3 | 2                                                                                   | 4,7 | 9,5 |
| 1263293  |                |                     |     |     |                                                                                     |     | 13  |
| 1263307  |                |                     |     |     |                                                                                     |     | 16  |

| Article# | d <sub>1</sub> | d <sub>2</sub> max. | f~  | k~  |  | m~  | L   |
|----------|----------------|---------------------|-----|-----|-------------------------------------------------------------------------------------|-----|-----|
| 1263315  | (ST3,9)        | 7,5                 | 1,3 | 2,3 | 2                                                                                   | 4,7 | 19  |
| 1263323  |                |                     |     |     |                                                                                     |     | 22  |
| 1263331  |                |                     |     |     |                                                                                     |     | 25  |
| 1263358  |                |                     |     |     |                                                                                     |     | 32  |
| 1263366  |                |                     |     |     |                                                                                     |     | 38  |
| 3059898  |                |                     |     |     |                                                                                     |     | 45  |
| 3059899  |                |                     |     |     |                                                                                     |     | 50  |
| 1263374  | ST4,2          | 8,1                 | 1,4 | 2,5 | 2                                                                                   | 4,9 | 9,5 |
| 1263382  |                |                     |     |     |                                                                                     |     | 13  |
| 1263390  |                |                     |     |     |                                                                                     |     | 16  |
| 1263404  |                |                     |     |     |                                                                                     |     | 19  |
| 1263412  |                |                     |     |     |                                                                                     |     | 22  |
| 1263420  |                |                     |     |     |                                                                                     |     | 25  |
| 1263439  |                |                     |     |     |                                                                                     |     | 32  |
| 1263447  |                |                     |     |     |                                                                                     |     | 38  |
| 1263455  |                |                     |     |     |                                                                                     |     | 45  |
| 1397397  |                |                     |     |     |                                                                                     |     | 50  |
| 1675699  | ST4,8          | 9,5                 | 1,5 | 3   | 2                                                                                   | 5,4 | 9,5 |
| 1263463  |                |                     |     |     |                                                                                     |     | 13  |
| 1263471  |                |                     |     |     |                                                                                     |     | 16  |
| 1263498  |                |                     |     |     |                                                                                     |     | 19  |
| 1263501  |                |                     |     |     |                                                                                     |     | 22  |
| 1263528  |                |                     |     |     |                                                                                     |     | 25  |
| 1263536  |                |                     |     |     |                                                                                     |     | 32  |
| 1263544  |                |                     |     |     |                                                                                     |     | 38  |
| 1263552  |                |                     |     |     |                                                                                     |     | 45  |
| 1263560  |                |                     |     |     |                                                                                     |     | 50  |
| 1263579  | ST5,5          | 10,8                | 1,7 | 3,4 | 3                                                                                   | 7   | 13  |
| 1263587  |                |                     |     |     |                                                                                     |     | 16  |
| 1263595  |                |                     |     |     |                                                                                     |     | 19  |
| 1263609  |                |                     |     |     |                                                                                     |     | 22  |
| 1263617  |                |                     |     |     |                                                                                     |     | 25  |
| 1263625  |                |                     |     |     |                                                                                     |     | 32  |
| 1263633  |                |                     |     |     |                                                                                     |     | 38  |
| 1263641  |                |                     |     |     |                                                                                     |     | 45  |
| 1263668  |                |                     |     |     |                                                                                     |     | 50  |
| 1263684  | ST6,3          | 12,4                | 2   | 3,8 | 3                                                                                   | 7,4 | 19  |
| 1263706  |                |                     |     |     |                                                                                     |     | 25  |
| 1263722  |                |                     |     |     |                                                                                     |     | 38  |
| 1263730  |                |                     |     |     |                                                                                     |     | 45  |
| 1263749  |                |                     |     |     |                                                                                     |     | 50  |