



|                        |               |                               |              |
|------------------------|---------------|-------------------------------|--------------|
| <b>EAN:</b>            | 4013288120670 | <b>Size:</b>                  | 104x44x24 mm |
| <b>Part number:</b>    | 05003605001   | <b>Weight:</b>                | 68 g         |
| <b>Article number:</b> | 8790 HMC      | <b>Country of origin:</b>     | TW           |
|                        |               | <b>Customs tariff number:</b> | 82042000     |

- 1/2 inch Zyklop socket
- For manual and power tool operations (non-impact)
- Knurling at lower end to enable easy gripping when used in manual applications
- Equipped with ball stop groove
- With Take it easy tool finder: colour coding by size

Manual and power tool socket insert (ISO 2725-Part 3) by Wera allows applications both in manual as well as power tools. "Take it easy" Tool Finder with colour coding according to size - for simple and rapid accessing of the required tool. Featuring a good grip to allow easy pick-up even with oily hands. Ball stop groove, for hex head bolts and nuts; chrome vanadium steel, matt chrome-plated.

**Web link**

[https://products.wera.de/en/zyklop\\_ratchets\\_and\\_accessories\\_the\\_zyklop\\_ratchets\\_the\\_zyklop\\_ratchets\\_1\\_2\\_zyklop\\_accessories\\_1\\_2\\_8790\\_hmc.html](https://products.wera.de/en/zyklop_ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_1_2_zyklop_accessories_1_2_8790_hmc.html)

Wera - 8790 HMC  
05003605001 - 4013288120670

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## Take it easy tool finder system

## Manual and machine sockets



Incredibly fast 1/4" Zyklop Speed ratchet with pivoting ratchet head and 5 predefined locking positions



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).



The manual and machine sockets can be used both for hand and power tools use (non-impact). Users need just one socket set for all applications.

## Further versions in this product family:

|                    |             |  |  |  |  |  |  |
|--------------------|-------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|                    |             | mm                                                                                  | inch                                                                                | mm                                                                                  | mm                                                                                    | mm                                                                                    | mm                                                                                    |
| 05003601001        | leuchtgelb  | 10.0                                                                                |                                                                                     | 37.0                                                                                | 15.5                                                                                  | 24.0                                                                                  | 17.0                                                                                  |
| 05003602001        | cyan        | 11.0                                                                                |                                                                                     | 37.0                                                                                | 16.5                                                                                  | 24.0                                                                                  | 17.0                                                                                  |
| 05003603001        | schwarz     | 12.0                                                                                |                                                                                     | 37.0                                                                                | 17.5                                                                                  | 24.0                                                                                  | 17.0                                                                                  |
| 05003604001        | tuerkis     | 13.0                                                                                |                                                                                     | 37.0                                                                                | 19.0                                                                                  | 24.0                                                                                  | 17.0                                                                                  |
| <b>05003605001</b> | <b>pink</b> | <b>14.0</b>                                                                         |                                                                                     | <b>37.0</b>                                                                         | <b>20.0</b>                                                                           | <b>24.0</b>                                                                           | <b>17.0</b>                                                                           |
| 05003606001        | weiss       | 15.0                                                                                |                                                                                     | 37.0                                                                                | 21.0                                                                                  | 24.0                                                                                  | 17.0                                                                                  |
| 05003607001        | violett     | 16.0                                                                                |                                                                                     | 37.0                                                                                | 22.5                                                                                  | 24.0                                                                                  | 17.0                                                                                  |
| 05003608001        | rot         | 17.0                                                                                |                                                                                     | 37.0                                                                                | 24.0                                                                                  | 26.0                                                                                  | 17.0                                                                                  |
| 05003609001        | leuchtgruen | 18.0                                                                                |                                                                                     | 37.0                                                                                | 25.0                                                                                  | 26.0                                                                                  | 17.0                                                                                  |
| 05003610001        | blau        | 19.0                                                                                |                                                                                     | 37.0                                                                                | 26.5                                                                                  | 26.0                                                                                  | 20.0                                                                                  |
| 05003611001        |             | 20.0                                                                                |                                                                                     | 37.0                                                                                | 28.0                                                                                  | 26.0                                                                                  | 20.0                                                                                  |
| 05003612001        |             | 21.0                                                                                |                                                                                     | 37.0                                                                                | 29.0                                                                                  | 26.0                                                                                  | 20.0                                                                                  |
| 05003613001        |             | 22.0                                                                                |                                                                                     | 37.0                                                                                | 30.5                                                                                  | 26.0                                                                                  | 20.0                                                                                  |
| 05003614001        |             | 24.0                                                                                |                                                                                     | 37.0                                                                                | 33.0                                                                                  | 28.0                                                                                  | 20.0                                                                                  |
| 05003615001        |             | 27.0                                                                                |                                                                                     | 40.0                                                                                | 36.5                                                                                  | 32.0                                                                                  | 23.0                                                                                  |
| 05003616001        |             | 30.0                                                                                |                                                                                     | 42.0                                                                                | 40.0                                                                                  | 34.0                                                                                  | 25.0                                                                                  |

## Web link

[https://products.wera.de/en/zyklop\\_ratchets\\_and\\_accessories\\_the\\_zyklop\\_ratchets\\_the\\_zyklop\\_ratchets\\_1\\_2\\_zyklop\\_accessories\\_1\\_2\\_8790\\_hmc.html](https://products.wera.de/en/zyklop_ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_1_2_zyklop_accessories_1_2_8790_hmc.html)

Wera - 8790 HMC

05003605001 - 4013288120670

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)

## Zyklop Accessories, 1/2"

|             |         |      |         |      |      |      |      |
|-------------|---------|------|---------|------|------|------|------|
| 05003617001 |         | 32.0 |         | 42.0 | 42.0 | 36.0 | 25.0 |
| 05003618001 | rot     |      | 3/8"    | 37.0 | 15.5 | 24.0 | 17.0 |
| 05003619001 | violett |      | 7/16"   | 37.0 | 16.5 | 24.0 | 17.0 |
| 05003620001 | tuerkis |      | 1/2"    | 37.0 | 19.0 | 24.0 | 17.0 |
| 05003621001 | pink    |      | 9/16"   | 37.0 | 20.0 | 24.0 | 17.0 |
| 05003622001 | weiss   |      | 19/32"  | 37.0 | 21.0 | 24.0 | 17.0 |
| 05003623001 | schwarz |      | 5/8"    | 37.0 | 22.5 | 24.0 | 17.0 |
| 05003624001 | cyan    |      | 11/16"  | 37.0 | 25.5 | 26.0 | 17.0 |
| 05003625001 | gelb    |      | 3/4"    | 37.0 | 26.5 | 26.0 | 20.0 |
| 05003626001 |         |      | 25/32"  | 37.0 | 28.0 | 26.0 | 20.0 |
| 05003627001 |         |      | 13/16"  | 37.0 | 29.0 | 26.0 | 20.0 |
| 05003628001 |         |      | 7/8"    | 37.0 | 30.5 | 26.0 | 20.0 |
| 05003629001 |         |      | 15/16"  | 37.0 | 33.0 | 28.0 | 20.0 |
| 05003630001 |         |      | 31/32"  | 37.0 | 33.0 | 28.0 | 20.0 |
| 05003631001 |         |      | 1"      | 40.0 | 36.5 | 32.0 | 23.0 |
| 05003632001 |         |      | 1 1/16" | 40.0 | 36.5 | 32.0 | 23.0 |
| 05003633001 |         |      | 1 1/8"  | 40.0 | 40.0 | 34.0 | 23.0 |
| 05003634001 |         |      | 1 3/16" | 42.0 | 40.0 | 34.0 | 25.0 |
| 05003635001 |         |      | 1 1/4"  | 42.0 | 42.0 | 36.0 | 25.0 |

## Web link

[https://products.wera.de/en/zyklop\\_ratchets\\_and\\_accessories\\_the\\_zyklop\\_ratchets\\_the\\_zyklop\\_ratchets\\_1\\_2\\_zyklop\\_accessories\\_1\\_2\\_8790\\_hmc.html](https://products.wera.de/en/zyklop_ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_1_2_zyklop_accessories_1_2_8790_hmc.html)

Wera - 8790 HMC

05003605001 - 4013288120670

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)