



EAN:	4013288120915	Size:	104x44x32 mm
Part number:	05003629001	Weight:	106 g
Article number:	8790 HMC	Country of origin:	TW
		Customs tariff number:	82042000

- 1/2 inch Zyklop socket
- For manual and power tool operations (non-impact)
- Knurling at lower end to enable easy gripping when used in manual applications
- Equipped with ball stop groove
- Chrome vanadium steel, matt chrome-plated

Manual and power tool socket insert (ISO 2725-Part 3) by Wera allows applications both in manual as well as power tools. Featuring a good grip to allow easy pick-up even with oily hands. Ball stop groove, for hex head bolts and nuts; chrome vanadium steel, matt chrome-plated

Web link

https://products.wera.de/en/zyklop_ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_1_2_zyklop_accessories_1_2_8790_hmc.html

Wera - 8790 HMC
05003629001 - 4013288120915

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Take it easy tool finder system

Manual and machine sockets



Incredibly fast 1/4" Zyklop Speed ratchet with pivoting ratchet head and 5 predefined locking positions



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).



The manual and machine sockets can be used both for hand and power tools use (non-impact). Users need just one socket set for all applications.

Further versions in this product family:

							
		mm	inch	mm	mm	mm	mm
05003601001	leuchtgelb	10.0		37.0	15.5	24.0	17.0
05003602001	cyan	11.0		37.0	16.5	24.0	17.0
05003603001	schwarz	12.0		37.0	17.5	24.0	17.0
05003604001	tuerkis	13.0		37.0	19.0	24.0	17.0
05003605001	pink	14.0		37.0	20.0	24.0	17.0
05003606001	weiss	15.0		37.0	21.0	24.0	17.0
05003607001	violett	16.0		37.0	22.5	24.0	17.0
05003608001	rot	17.0		37.0	24.0	26.0	17.0
05003609001	leuchtgruen	18.0		37.0	25.0	26.0	17.0
05003610001	blau	19.0		37.0	26.5	26.0	20.0
05003611001		20.0		37.0	28.0	26.0	20.0
05003612001		21.0		37.0	29.0	26.0	20.0
05003613001		22.0		37.0	30.5	26.0	20.0
05003614001		24.0		37.0	33.0	28.0	20.0
05003615001		27.0		40.0	36.5	32.0	23.0
05003616001		30.0		42.0	40.0	34.0	25.0

Web link

https://products.wera.de/en/zyklop_ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_1_2_zyklop_accessories_1_2_8790_hmc.html

Wera - 8790 HMC

05003629001 - 4013288120915

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

Zyklop Accessories, 1/2"

05003617001		32.0	42.0	42.0	36.0	25.0
05003618001	rot	3/8"	37.0	15.5	24.0	17.0
05003619001	violett	7/16"	37.0	16.5	24.0	17.0
05003620001	tuerkis	1/2"	37.0	19.0	24.0	17.0
05003621001	pink	9/16"	37.0	20.0	24.0	17.0
05003622001	weiss	19/32"	37.0	21.0	24.0	17.0
05003623001	schwarz	5/8"	37.0	22.5	24.0	17.0
05003624001	cyan	11/16"	37.0	25.5	26.0	17.0
05003625001	gelb	3/4"	37.0	26.5	26.0	20.0
05003626001		25/32"	37.0	28.0	26.0	20.0
05003627001		13/16"	37.0	29.0	26.0	20.0
05003628001		7/8"	37.0	30.5	26.0	20.0
05003629001		15/16"	37.0	33.0	28.0	20.0
05003630001		31/32"	37.0	33.0	28.0	20.0
05003631001		1"	40.0	36.5	32.0	23.0
05003632001		1 1/16"	40.0	36.5	32.0	23.0
05003633001		1 1/8"	40.0	40.0	34.0	23.0
05003634001		1 3/16"	42.0	40.0	34.0	25.0
05003635001		1 1/4"	42.0	42.0	36.0	25.0

Web link

https://products.wera.de/en/zyklop_ratchets_and_accessories_the_zyklop_ratchets_the_zyklop_ratchets_1_2_zyklop_accessories_1_2_8790_hmc.html

Wera - 8790 HMC

05003629001 - 4013288120915

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de