

800/1 Z bits, 0.6 x 4.5 x 39 mm

Bits for Slotted Screws



|                        |               |                               |           |
|------------------------|---------------|-------------------------------|-----------|
| <b>EAN:</b>            | 4013288010834 | <b>Size:</b>                  | 39x7x7 mm |
| <b>Part number:</b>    | 05056015001   | <b>Weight:</b>                | 6 g       |
| <b>Article number:</b> | 800/1 Z       | <b>Country of origin:</b>     | CZ        |
|                        |               | <b>Customs tariff number:</b> | 82079030  |

- For slotted screws
- Ductile and tough for hard materials
- 1/4" hexagon drive (Wera connecting series 1)
- Suitable for Bosch, Fein, Holz-Her, Lecloux, Metabo
- Prevents premature breakage of the drive tip

Tough viscous Wera bits for hexagon socket screws and universal use. 1/4" hexagon, suitable for holders as per DIN ISO 1173-D 6.3.

**Web link**

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_the\\_range\\_of\\_bits\\_bits\\_for\\_slotted\\_screws\\_800\\_1\\_z.html](https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_slotted_screws_800_1_z.html)

Wera - 800/1 Z  
05056015001 - 4013288010834

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## Bits for Slotted Screws

## Tough-absorbing bits



Tough-absorbing Wera bits (Z) prevent any premature breakage of the drive tip.

## Further versions in this product family:

|                    | <br>mm | <br>mm | <br>mm | <br>inch | <br>mm |
|--------------------|-----------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------|
| 05056200001        | 0.5                                                                                     | 3.0                                                                                     | 25                                                                                      | 1                                                                                           | 3.0                                                                                       |
| 05056005001        | 0.5                                                                                     | 3.0                                                                                     | 39                                                                                      | 1 17/32                                                                                     | 3.0                                                                                       |
| 05072050001        | 0.5                                                                                     | 4.0                                                                                     | 25                                                                                      | 1                                                                                           | 4.0                                                                                       |
| 05056007001        | 0.5                                                                                     | 4.0                                                                                     | 39                                                                                      | 1 17/32                                                                                     | 4.0                                                                                       |
| 05056010001        | 0.6                                                                                     | 3.5                                                                                     | 39                                                                                      | 1 17/32                                                                                     | 3.5                                                                                       |
| 05072055001        | 0.6                                                                                     | 4.5                                                                                     | 25                                                                                      | 1                                                                                           | 4.5                                                                                       |
| <b>05056015001</b> | <b>0.6</b>                                                                              | <b>4.5</b>                                                                              | <b>39</b>                                                                               | <b>1 17/32</b>                                                                              | <b>4.5</b>                                                                                |
| 05072057001        | 0.8                                                                                     | 5.5                                                                                     | 25                                                                                      | 1                                                                                           | 5.5                                                                                       |
| 05056020001        | 0.8                                                                                     | 4.0                                                                                     | 39                                                                                      | 1 17/32                                                                                     | 4.0                                                                                       |
| 05072059001        | 1.0                                                                                     | 5.5                                                                                     | 25                                                                                      | 1                                                                                           | 5.5                                                                                       |
| 05056025001        | 0.8                                                                                     | 5.5                                                                                     | 39                                                                                      | 1 17/32                                                                                     | 5.5                                                                                       |
| 05072061001        | 1.2                                                                                     | 6.5                                                                                     | 25                                                                                      | 1                                                                                           | 6.2                                                                                       |
| 05056030001        | 1.0                                                                                     | 5.5                                                                                     | 39                                                                                      | 1 17/32                                                                                     | 5.5                                                                                       |
| 05072063001        | 1.2                                                                                     | 8.0                                                                                     | 25                                                                                      | 1                                                                                           | 8.0                                                                                       |
| 05056037001        | 1.2                                                                                     | 6.5                                                                                     | 39                                                                                      | 1 17/32                                                                                     | 6.5                                                                                       |
| 05056040001        | 1.2                                                                                     | 8.0                                                                                     | 39                                                                                      | 1 17/32                                                                                     | 8.0                                                                                       |
| 05072065001        | 1.6                                                                                     | 8.0                                                                                     | 25                                                                                      | 1                                                                                           | 8.0                                                                                       |
| 05056045001        | 1.6                                                                                     | 8.0                                                                                     | 39                                                                                      | 1 17/32                                                                                     | 8.0                                                                                       |

## Web link

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_the\\_range\\_of\\_bits\\_bits\\_for\\_slotted\\_screws\\_800\\_1\\_z.html](https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_slotted_screws_800_1_z.html)

Wera - 800/1 Z

05056015001 - 4013288010834

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)