



EAN:	4013288160867	Size:	50x7x6 mm
Part number:	05160821001	Weight:	15 g
Article number:	867/4 IPR	Country of origin:	CZ
		Customs tariff number:	82079030

- For recessed TORX PLUS® IPR screws with safety pin
- Ductile and tough for hard materials
- TORX PLUS® IPR bit with bore hole on the output side
- 1/4" hexagon drive (Wera connecting series 4)
- Suitable for AEG, ARO, Atlas-Copco, Biax, Black & Decker, Bosch, Buckeye Tools etc.

High quality bits for recessed TORX PLUS® screws with safety pin. A 5-flank TORX PLUS® profile with bore hole. 1/4" hexagon, suitable for holders as per DIN ISO 1173-F 6.3.

Web link

https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_tamper-proof_torx_plus_ipr_screws_with_safety_pin_867_4_ipr.html

Wera - 867/4 IPR
05160821001 - 4013288160867

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Bits for Tamper-proof TORX PLUS® IPR Screws with Safety Pin

For recessed TORX PLUS® IPR screws with safety pin

Tough-absorbing bits



A 5-flank TORX PLUS® profile with a borehole. This drive geometry has only five flanks instead of the usual six and a borehole to protect safety screws against unauthorised unfastening. The screws cannot be turned with conventional, widely available tools.



Tough-absorbing Wera bits (Z) prevent any premature breakage of the drive tip.

Web link

https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_tamper-proof_torx_plus_ipr_screws_with_safety_pin_867_4_ipr.html

Wera - 867/4 IPR
05160821001 - 4013288160867

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Bits for Tamper-proof TORX PLUS® IPR Screws with Safety Pin

Further versions in this product family:

		 mm	 inch	 mm
05134600001 ¹⁾	1 IPR	50	2	2.0
05134601001 ¹⁾	3 IPR	50	2	2.0
05134602001 ¹⁾	5 IPR	50	2	3.0
05134603001 ¹⁾	6 IPR	50	2	3.0
05134604001	8 IPR	50	2	3.0
05160821001	10 IPR	50	2	4.0
05134657001	10 IPR	89	3 1/2	4.0
05134654001	15 IPR	50	2	4.0
05134720001	15 IPR	89	3 1/2	4.0
05204126001	20 IPR	50	2	4.5
05259135001	20 IPR	89	3 1/2	4.5
05134655001	25 IPR	50	2	6.0
05134722001	25 IPR	89	3 1/2	6.0
05134656001	27 IPR	50	2	6.0
05134658001	27 IPR	89	3 1/2	6.0
05134732001	30 IPR	50	2	6.0
05134723001	30 IPR	89	3 1/2	6.0

1) Without bore hole

Web link

https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_tamper-proof_torx_plus_ipr_screws_with_safety_pin_867_4_ipr.html

Wera - 867/4 IPR
 05160821001 - 4013288160867

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de